


Tantalum, Polymer Tantalum, T522, 330 uF, 20%, 6.3 V, 7343, SMD, Polymer, Molded, Low Profile, Low ESR/Leakage, 40 mOhms, 2mm



General Information	
Dielectric:	Polymer Tantalum
Style:	SMD Chip
Series:	T522
Description:	SMD, Polymer, Molded, Low Profile, Low ESR/Leakage
Features:	Low ESR, Low Leakage
RoHS:	Yes
Termination:	Tin

Dimensions	
Footprint	7343
L	7.3mm +/-0.3mm
W	4.3mm +/-0.3mm
H	1.9mm +/-0.1mm
T	0.13mm REF
S	1.3mm +/-0.3mm
F	2.4mm +/-0.1mm
A	3.8mm MIN
X	0.05mm REF

Specifications	
Capacitance:	330 uF
Capacitance Tolerance:	20%
Voltage DC:	6.3 VDC (105C)
Temperature Range:	-55/+105C
Dissipation Factor:	10% 120Hz 25C
Failure Rate:	N/A
Resistance:	40 mOhms (100kHz 25C)
Current:	2200 mAmps (100kHz 45C), 1540 mAmps (85C), 1045 mAmps (105C)
Leakage:	62.4 uAmps (10min 5C)

Packaging Specifications	
Weight:	274.3 mg
Packaging:	T&R, 178mm
Packaging Quantity:	1000