

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0757300210](#)
Status: **Active**
Overview: EXTreme MicroPower™ Connectors
Description: 4.00mm EXTreme MicroPower™ Header, 10 Circuits, 3.81mm Tail Length

Documents:

[3D Model](#) [Packaging Specification PK-75730-118 \(PDF\)](#)
[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification


CSA LR19980
 UL E29179

General

Product Family PCB Headers
 Series [75730](#)
 Application Board-to-Board, Power
 Overview [EXTreme MicroPower™ Connectors](#)
 Product Name EXTreme MicroPower™
 UPC 822350843782

Physical

(p)ower-(s)ignal Configuration 10p - 0s
 Breakaway No
 Circuits (Loaded) 10
 Circuits (maximum) 10
 Color - Resin Black
 First Mate / Last Break No
 Flammability 94V-0
 Glow-Wire Compliant No
 Guide to Mating Part No
 Keying to Mating Part None
 Lock to Mating Part No
 Material - Metal Copper
 Material - Plating Mating Tin
 Material - Plating Termination Tin
 Material - Resin High Temperature Thermoplastic
 Net Weight 2.111/g
 Number of Rows 1
 Orientation Right Angle
 PC Tail Length 3.81mm
 PCB Locator No
 PCB Retention Yes
 PCB Thickness - Recommended 1.70mm, 3.18mm
 Packaging Type Tray
 Pitch - Mating Interface 4.00mm
 Pitch - Termination Interface 4.00mm
 Plating min - Mating 2.540µm
 Plating min - Termination 2.540µm
 Polarized to Mating Part No
 Polarized to PCB No
 Shrouded No
 Stackable No
 Surface Mount Compatible (SMC) Yes
 Temperature Range - Operating -40°C to +105°C
 Termination Interface: Style Through Hole



EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
 ED/21/2016 (20 June
 2016)

Halogen-Free

Status

Low-Halogen

**Need more information on product
 environmental compliance?**

Email productcompliance@molex.com
 Please visit the [Contact Us](#) section for any
 non-product compliance questions.

China ROHS

Not Relevant

ELV

Not Relevant

Search Parts in this Series

[75730 Series](#)

Electrical

Current - Maximum per Contact

16.0A

Voltage - Maximum

250V

Material Info**Reference - Drawing Numbers**

Packaging Specification

PK-75730-118

Sales Drawing

SD-75730-118

This document was generated on 07/15/2016

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION