

Tantalum, Polymer Tantalum, COTS, T543_COTS, 470 uF, 10%, 4 V, 7343, SMD, Polymer, Molded, COTS, Up Screening, A (Non-ER), 5 mOhms, 4mm



Dimensions	
Footprint	7343
L	7.3mm +/-0.3mm
W	4.3mm +/-0.3mm
H	3.8mm +/-0.2mm
T	0.13mm REF
S	1.3mm +/-0.3mm
F	2.4mm +/-0.1mm
A	3.8mm MIN
B	0.5mm +/-0.15mm
E	3.5mm REF
G	3.5mm REF
P	1.7mm REF
R	1mm REF
X	0.1mm +/-0.1mm

Packaging Specifications	
Weight:	481.55 mg
Packaging:	T&R, 178mm
Packaging Quantity:	500

General Information	
Dielectric:	Polymer Tantalum
Style:	SMD Chip
Series:	T543_COTS
Description:	SMD, Polymer, Molded, COTS, Up Screening
Features:	Non-Combustible, Up Screening, Low ESR, COTS
RoHS:	No
Termination:	Solder Coated
Notes:	In Polarity Stripe, At KEMET's Option, Type May Be Indicated: No Symbol = Standard MnO2 Tantalum Chip, O = Low ESR T494, R = Low ESR T495, F = Fused T496, HT = 150C Rated T498 (or B45196P, B45198P), H = 175C Rated T499, M = Multiple Anode Construction T51

Specifications	
Capacitance:	470 uF
Capacitance Tolerance:	10%
Voltage DC:	4 VDC (105C)
Temperature Range:	-55/+105C
Dissipation Factor:	10% 120Hz 25C
Failure Rate:	A (Non-ER)
Resistance:	5 mOhms (100kHz)
Current:	6943 mAmps (100kHz 45C)
Leakage:	188 uAmps
Testing and Reliability:	Standard Testing Only

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.