

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0956232881

Status:

Active

Overview:

Modular Jacks and Plugs

Description:

Modular Jack, Top Entry, Through Hole, 8/8, Shielded, Tray

- Documents:
- 3D Model

Test Summary STR-1508 (PDF)
- Drawing (PDF)

RoHS Certificate of Compliance (PDF)
- Product Specification PS-95623-001 (PDF)

Product Literature (PDF)
- Application Specification AS-85513-001 (PDF)

Agency Certification

UL

E107635

General

Product Family

Modular Jacks/Plugs

Series

95623

Comments

Reflow Capable, External Shield

Component Type

PCB Jack

Magnetic

No

Overview

Modular Jacks and Plugs

Performance Category

3

Power over Ethernet (PoE)

N/A

Product Literature Order No

987650-8441

Product Name

RJ45

UPC

800756696676

Physical

Boot Color

N/A

Color - Resin

Black

Durability (mating cycles max)

2500

Flammability

94V-0

Inverted / Top Latch

No

Jack Height

16.50mm

Lightpipes/LEDs

None

Material - Metal

Copper Alloy

Material - Plating Mating

Gold over Palladium Nickel

Material - Plating Termination

Tin

Material - Resin

High Temperature Thermoplastic

Net Weight

6.720/g

Orientation

Vertical (Top Entry)

PCB Locator

Yes

PCB Retention

Yes

PCB Thickness - Recommended

1.57mm

Packaging Type

Tray

Pitch - Mating Interface

1.02mm

Pitch - Termination Interface

1.27mm

Plating min - Mating

0.051µm, 1.016µm

Plating min - Termination

1.905µm

Ports

1

Positions / Loaded Contacts

8/8

Surface Mount Compatible (SMC)

No

Temperature Range - Operating

-40°C to +85°C

Termination Interface: Style


Through Hole

Waterproof / Dustproof

No

Wire/Cable Type

N/A



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

China RoHS

REACH SVHC

Not Contained Per
-ED/79/2015 (17
December 2015)

Halogen-Free

Status

Low-Halogen

Need more information on product
environmental compliance?

Email productcompliance@molex.com
Please visit the [Contact Us](#) section for any
non-product compliance questions.

China ROHS

Green Image

ELV

Not Relevant

Search Parts in this Series

95623 Series

Mates With

95043 Modular Plug, Short Body

Electrical

Current - Maximum per Contact	1.5A
Grounding to PCB	Yes
Shielded	Yes
Voltage - Maximum	125V DC

Solder Process Data

Duration at Max. Process Temperature (seconds)	045
Lead-freeProcess Capability	WAVE
Max. Cycles at Max. Process Temperature	003
Process Temperature max. C	260

Material Info

Reference - Drawing Numbers

Application Specification	AS-85513-001
Product Specification	PS-95623-001
Sales Drawing	SD-95623-001
Test Summary	STR-1508

This document was generated on 08/17/2016

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION