

Bat Handle Toggle, Single Pole




Features

- Slow-Make/Slow-Break Butt Contact
- 1 HP, 125-250VAC



S97



Specifications

Current Rating: 20A 125VAC, 10A 250VAC, 1 HP 125-250VAC
Insulation Resistance: 10^9 ohms (min.)
Dielectric Strength: 1500V RMS (min.)
Temperature Rating: +14°F to +149°F (-10°C to +65°C)
Electrical Life: 10,000 cycles (min.) at full load
Mechanical Life: 30,000 cycles (min.)
Terminal Type: Refer to Diag. No. in Table
Mounting Hole: .500 (12.7)

NTE Type No.	Circuitry	Action			Actuator	Diag No.
NEW 54-579	SPST	ON	NONE	OFF	Nickel Plated Brass	S97b
NEW 54-580	SPST	(ON)	NONE	OFF	Nickel Plated Brass	S97b
NEW 54-581	SPST	ON	NONE	(OFF)	Nickel Plated Brass	S97b
NEW 54-582	SPDT	ON	NONE	ON	Nickel Plated Brass	S97b
NEW 54-583	SPDT	ON	OFF	ON	Nickel Plated Brass	S97b
NEW 54-584	SPDT	(ON)	NONE	ON	Nickel Plated Brass	S97b
NEW 54-585	SPDT	(ON)	OFF	ON	Nickel Plated Brass	S97b
NEW 54-586	SPDT	(ON)	OFF	(ON)	Nickel Plated Brass	S97b
NEW 54-593	SPST	ON	NONE	OFF	Nickel Plated Brass	S97c
NEW 54-594	SPST	(ON)	NONE	OFF	Nickel Plated Brass	S97c
NEW 54-595	SPST	ON	NONE	(OFF)	Nickel Plated Brass	S97c
NEW 54-596	SPDT	ON	NONE	ON	Nickel Plated Brass	S97c
NEW 54-597	SPDT	ON	OFF	ON	Nickel Plated Brass	S97c
NEW 54-598	SPDT	(ON)	NONE	ON	Nickel Plated Brass	S97c
NEW 54-599	SPDT	(ON)	OFF	ON	Nickel Plated Brass	S97c
NEW 54-600	SPDT	(ON)	OFF	ON	Nickel Plated Brass	S97c

SPECIAL NOTE: () = Momentary Function

Bat Handle Toggle, Double Pole




Features

- Slow-Make/Slow-Break Butt Contact
- 1 HP, 125-250VAC



S98



Specifications

Current Rating: 20A 125VAC, 10A 250VAC, 1 HP 125-250VAC
Insulation Resistance: 10^9 ohms (min.)
Dielectric Strength: 1500V RMS (min.)
Temperature Rating: +14°F to +149°F (-10°C to +65°C)
Electrical Life: 10,000 cycles (min.) at full load
Mechanical Life: 30,000 cycles (min.)
Terminal Type: .250" Tab Q.C.
Mounting Hole: .500 (12.7)

NTE Type No.	Circuitry	Action			Actuator	Diag No.
NEW 54-590	DPST	ON	NONE	OFF	Nickel Plated Brass	S98b
NEW 54-591	DPDT	ON	NONE	ON	Nickel Plated Brass	S98b
NEW 54-592	DPDT	ON	OFF	ON	Nickel Plated Brass	S98b