

General Information

Extended Product Type:	OT63F4N2
Product ID:	1SCA105365R1001
EAN:	6417019393094
Catalog Description:	OT63F4N2 switch-disconnector
Long Description:	4-pole, front operated, base mounted, DIN-rail mountable switch-disconnector / non-fusible disconnect switch with protected clamp terminals, handle and shaft are not included

Categories

Products » Low Voltage Products and Systems » Switches » Switch Disconnectors

Ordering

EAN:	6417019393094
Minimum Order Quantity:	10 piece
Customs Tariff Number:	85365080

Dimensions

Product Net Width:	64 mm
Product Net Height:	92 mm
Product Net Depth:	73 mm
Product Net Weight:	0.3 kg

Container Information

Package Level 1 Units:	1 piece
Package Level 1 Width:	84 mm
Package Level 1 Height:	82 mm
Package Level 1 Length:	103 mm
Package Level 1 Gross Weight:	0.3 kg
Package Level 1 EAN:	6417019393094

Environmental

RoHS Status:	Planned to follow EU Directive 2002/95/EC August 18, 2005 and amendment after 2009 Q3
--------------	---

Technical UL/CSA

Maximum Operating Voltage UL/CSA:	600 V
Ampere Rating UL/CSA:	60 A
Horsepower Rating UL/CSA:	(acc. to UL 200 V) 15 Hp (acc. to UL 480 V) 30 Hp (acc. to UL 208 V) 15 Hp (acc. to UL 240 V) 15 Hp (acc. to UL 600 V) 30 Hp
Tightening Torque UL/CSA:	18 in-lb

Additional Information

Cable Cross-Section:	1.5...35 mm ² 1.5 ϕ 35 mm ²
Conventional Free-air Thermal Current (I _{th}):	q = 40 °C 63 A
Conventional Thermal Current (I _{the}):	Fully Enclosed 63 A
Dielectric Test Voltage:	6000 V
Earthing Switch Type:	No Additional Type
Handle Type:	Handle and shaft not included
IIT Publishing Status:	Level 0 - Information enabled
Includes:	None
Mounting Type:	Base mounting
Number of Poles:	4
Operating Mode:	Front Operated
Order Multiple:	10 piece
Pollution Degree:	3
Position of Line Terminals:	Top In - Bottom Out
Power Loss:	at Rated Operating Conditions per Pole 2.8 W
Product Main Type:	OT63

Product Name:	Switch-disconnector
Rated Impulse Withstand Voltage (U_{imp}):	8 kV
Rated Insulation Voltage (U_i):	750 V
Rated Operational Current AC-21A (I_e):	(500 V) 63 A (380 ... 415 V) 63 A (690 V) 63 A
Rated Operational Current AC-22A (I_e):	(500 V) 63 A (380 ... 415 V) 63 A (690 V) 63 A
Rated Operational Current AC-23A (I_e):	(380 ... 415 V) 45 A (500 V) 45 A (690 V) 20 A
Rated Operational Power AC-23A (P_e):	(500 V) 22 kW (690 V) 15 kW (690 V) 11 kW (400 V) 22 kW (415 V) 22 kW (220 ... 240 V) 11 kW
Rated Operational Voltage:	750 V
Rated Short-time Withstand Current (I_{cw}):	for 1 s 1 kiloampere rms
Special Functions:	No
Standards:	IEC 60947-3, UL 508 / CSA C22.2 NO.14
Switches Operating Mechanism:	Mechanism on Top of the Switch
Terminal Type:	Screw Terminals
Tightening Torque:	2 N·m

Certificates and Declarations (Document Number)

Data Sheet, Technical Information:	1SCC301020C0201
Declaration of Conformity - CE:	1SCC301167D2704
RoHS Information:	1SCC301183D0201

Classifications

ETIM 5:	EC000216 - Switch disconnector
Object Classification Code:	Q

