


Varistors, VC, Low Voltage, 8 V, 6 VAC, 11 V, 21 V, 1 Amps, 150 Amps, 500 mJ, 8000 uW



Dimensions	
Chip Size	1206
L	3.2mm +/-0.3mm
W	1.6mm +/-0.2mm
T	0.85mm MAX
B	0.5mm +/-0.25mm

Packaging Specifications	
Packaging:	T&R
Packaging Quantity:	4000

General Information	
Type:	Varistors
Style:	SMD Chip
Series:	VC
Description:	Surface Mount Varistors
Features:	Low Voltage
Approvals:	CECC, IEC, AEC-Q200
Termination:	Nickel Tin
RoHS:	Yes

Specifications	
Voltage DC:	8 VDC (25C)
Voltage AC:	6 VAC
Temperature Range:	-55/+125C
Storage Temperature Range:	-55/+150C
Varistor Voltage:	11 VDC at 1 mAmps
Clamping Voltage:	21 V
Clamping Current:	1 Amps (8/20 us MAX)
Surge Current:	150 Amps (8/20 us MAX)
Energy:	0.5 J (10/1000 us MAX)
Capacitance:	2600 pF (1kHz)