

TECHNICAL DATA SHEET



Alarm Cable Model: CB19511

RoHS
Compliant

Design of cable:	
Inner conductor	Stranded TCCA 7/0.20 ± 0.004mm
Insulation	PVC
Size of insulation	Ø1.1 ± 0.1mm
Core colour	Black/yellow/red/blue/white/green
Six wires twisted to a qual	
Rip wire	
Jacket	PE
Colour	Black
Size	Ø4.1 ± 0.2mm
Wall thickness	≈0.5mm
Printing	No marking
Electric data at 20°C:	
Conductor resistance	≤145Ω/km
Insulation resistance	≥200MΩ*km
Testing voltage	wire/wire 50Hz 1 min = 800V
Other requirements:	
Permissible temperature	-10°C - +60°C
Packing	100m on non-returnable reel

Important Notice : This data sheet and its contents (the "Information") belong to pro-POWER. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but pro-POWER assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where pro-POWER was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict pro-POWER's liability for death or personal injury resulting from its negligence.

