



### Model Number

**NBB2-V3-US**

### Features

- Sensing range 2 mm
- 2-wire AC/DC

## Technical Data

### General specifications

Switching element function	NO contact
Rated operating distance	$s_n$ 2 mm
Installation	flush mountable
Output polarity	AC/DC

### Nominal ratings

Operating voltage DC	10 ... 140 V
Operating voltage AC	20 ... 140 V
Switching frequency	$f$ 25 Hz
Reverse polarity protection	no
Short-circuit protection	no
Voltage drop	$U_d$ $\leq 7$ V
Operating current	$I_L$ 5 ... 200 mA max
Off-state current	$I_r$ $\leq 0.8$ mA
Switching state indication	LED, red

### Ambient conditions

Ambient temperature	-25 ... 70 °C (-13 ... 158 °F)
---------------------	--------------------------------

### Mechanical specifications

Connection type	cable PUR
Core cross-section	0.25 mm <sup>2</sup>
Housing material	PBT
Sensing face	PBT
Protection degree	IP67


### Compliance with standards and directives

Standard conformity	
Standards	EN 60947-5-2:2007 IEC 60947-5-2:2007

### Approvals and certificates

UL approval	cULus Listed, General Purpose
CSA approval	cCSAus Listed, General Purpose

## Dimensions



## Electrical Connection

