

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

1728790208

Status:

Active

Overview:

EdgeMate™ Wire-to-Edge-Card Power Connector

Description:

3.96mm Pitch EdgeMate™ Wire-to-Board Edge Card Connector, Female, Nylon 6, Black, UL94-V2, without Lock, Glow Wire Capable, 8 Circuits



Series image - Reference only

Documents:	
Drawing (PDF)	RoHS Certificate of Compliance (PDF)
Agency Certification	
UL	E29179
General	
Product Family	Edge Card Connectors
Series	172879
Application Tooling Part Link	11-03-0016
Circuit Size Range	1-64 Circuits
Comments	See Product Specification for maximum current rating by wire AWG and terminal material.
Component Type	Edgecard to Wire
Data Rate	Unrated
Edge Card Thickness	N/A
High Power Bay (30.0A or more)	No
Orientation	Right Angle
Overview	EdgeMate™ Wire-to-Edge-Card Power Connector
Product Name	EdgeMate™
Standard Based	General
UPC	889056377102
Physical	
(p)ower-(s)ignal Configuration	8p - 0s
Circuits (Loaded)	8
Circuits (maximum)	8
Color - Resin	Black
Durability (mating cycles max)	25
Entry Angle	90° Angle
Flammability	94V-2
Keying to Mating Part	Yes
Material - Plating Mating	N/A
Material - Resin	Nylon
Net Weight	3.139/g
PCB Locator	No
PCB Retention	None
PCB Thickness - Recommended	1.57mm
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	3.96mm
Polarized to Mating Part	Polarizing Ribs
Temperature Range - Operating	-40°C to +105°C, -40°C to +80°C
Termination Interface: Style	Straddle Mount-Edge Card
Electrical	
Current - Maximum per Contact	7.0A
Voltage - Maximum	250V
Solder Process Data	
Lead-freeProcess Capability	N/A

EU ELV

Not Relevant

EU RoHS

China RoHS

Compliant

REACH SVHC

Not Contained Per -

ED/21/2016 (20 June

2016)

Halogen-Free

Status

Not Low-Halogen

Need more information on product

environmental compliance?

Email productcompliance@molex.com

Please visit the [Contact Us](#) section for any

non-product compliance questions.

China ROHS

Green Image

ELV

Not Relevant

Search Parts in this Series

172879 Series

Mates With

Edge Card PCB

Use With

172160

Application Tooling | [FAQ](#)

Tooling specifications and manuals are

found by selecting the products below.

Crimp Height Specifications are then

contained in the Application Tooling

Specification document.

Global

Description

Product #

Extraction Tool

0011030016

Material Info

Reference - Drawing Numbers
Sales Drawing

SD-172879-0000

This document was generated on 07/18/2016

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION