

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [5013310207](#)
Status: **Active**
Overview: [Pico-Clasp™ Wire-to-Board Connectors](#)
Description: 1.00mm Pitch Pico-Clasp™ Wire-to-Board Header, Surface Mount, Single Row, Vertical, with Friction Lock, 2 Circuits, with Cover Tape

Documents:

[3D Model](#) [RoHS Certificate of Compliance \(PDF\)](#)
[Drawing \(PDF\)](#)

Agency Certification

UL E29179

General

Product Family PCB Headers
Series [501331](#)
Application Signal, Wire-to-Board
Overview [Pico-Clasp™ Wire-to-Board Connectors](#)
Product Name Pico-Clasp™
UPC 822348542772

Physical

Breakaway No
Circuits (Loaded) 2
Circuits (maximum) 2
Color - Resin Natural
Durability (mating cycles max) 30
Glow-Wire Compliant No
Lock to Mating Part Yes
Material - Metal Phosphor Bronze
Material - Plating Mating Tin
Material - Plating Termination Tin
Material - Resin Nylon
Net Weight 74.700/mg
Number of Rows 1
Orientation Vertical
PCB Locator No
PCB Retention Yes
Packaging Type Embossed Tape on Reel
Pitch - Mating Interface 1.00mm
Polarized to Mating Part Yes
Polarized to PCB No
Robotic Placement Vacuum Pick-Up Tape
Stackable No
Temperature Range - Operating -40°C to +105°C
Termination Interface: Style Surface Mount


Electrical

Current - Maximum per Contact 1.0A
Voltage - Maximum 50V AC (RMS)/DC

Material Info

Reference - Drawing Numbers

Sales Drawing SD-501331-001, SD-501331-003



EU ELV

Not Relevant

EU RoHS

Compliant

China RoHS

REACH SVHC

Not Contained Per -
ED/21/2016 (20 June
2016)

Halogen-Free

Status

Not Low-Halogen

**Need more information on product
environmental compliance?**

Email productcompliance@molex.com
Please visit the [Contact Us](#) section for any
non-product compliance questions.

China ROHS Green Image
ELV Not Relevant

Search Parts in this Series

[501331](#) Series

Mates With

[501330](#) Pico-Clasp™ Wire-to-Board Female
Housing

This document was generated on 07/11/2016

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION