

General Information

Extended Product Type:	332RS9
Product ID:	2CMA193132R1000
EAN:	7392696931328
Catalog Description:	Surface socket-outlet, 9h, 32A, IP44, 3P+E
Long Description:	Surface socket-outlet, earthing sleeve position 9h, rated current 32A, IP44 splashproof, 3-poles+earth, frequency 50-60 Hz, color code Blue

Categories

Products » Low Voltage Products and Systems » Industrial Plugs and Sockets » Plugs & Sockets » Surface Socket Outlets

Ordering

EAN:	7392696931328
Minimum Order Quantity:	10 piece
Country of Origin:	Czech Republic (CZ)

Dimensions

Product Net Width:	85 mm
Product Net Height:	163 mm
Product Net Length:	116 mm
Product Net Depth:	163 mm
Product Net Weight:	0.32 kg

Container Information

Package Level 1 Width:	173 mm
Package Level 1 Length:	430 mm
Package Level 1 Height:	199 mm
Package Level 1 Gross Weight:	0.35 kg
Package Level 1 EAN:	7392696931328
Package Level 1 Units:	10 piece

Environmental

RoHS Status:	Planned to follow EU Directive 2002/95/EC August 18, 2005 and amendment after 2006-03-01
--------------	--

Certificates and Declarations (Document Number)

Declaration of Conformity - CE:	2CMC700005D0001
Environmental Information:	2CMC700001D0002
RoHS Information:	2CMC700057D0001

Additional Information

Additional Information:	Cable entry, flexible membrane and metric threaded M25 insert for top cable entry.Rear knock-out cable entry.
Cable Cross-Section:	2.5 ... 10 mm ²
Color:	Blue
Degree of Protection:	acc. to IEC 60529 IP44
Enclosure Material:	Thermoplastic
Frequency (f):	60 Hz
Function:	Surface socket outlet
IIT Publishing Status:	Level 0 - Information enabled
Invoice Description:	Ind. P&S#332RS9
Number of Poles:	3
Object Classification Code:	2CMT005069
Product Main Type:	ERS
Product Name:	Industrial Socket Outlet
Protection Type:	Splashproof
Rated Current (I _n):	32 A
Rated Voltage (U _r):	200 ... 250 V 200 ⚡ 250 V
RoHS Date:	L23
Standards:	IEC 60309-1,-2

Suitable For: Surface Socket Outlets
Suitable for Product Class: Industrial Plugs and Sockets

Classifications

E-nummer: 2416499
UNSPSC: 39120000

