

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:	0192030084
Status:	Active
Overview:	High-Temperature Temp Terms Terminals and Splices
Description:	Krimptite™ Temp-Term Ring Tongue Terminal for 14 to 16 AWG Wire, Stud Size 8 (M4), Mylar Tape Carrier
Documents:	
Drawing (PDF)	RoHS Certificate of Compliance (PDF)
Agency Certification	
UL	E32244
General	
Product Family	Ring and Spade Terminals
Series	19203
Comments	1200° F (649° C)
Crimp Quality Equipment	Yes
Mil-Spec	N/A
Overview	High-Temperature Temp Terms Terminals and Splices
Product Name	Krimptite™, Temp-Terms
Type	Ring
UPC	800753049949
Physical	
Barrel Type	Closed
Insulation	None
Material - Plating Mating	Tin
Net Weight	0.628/g
Packaging Type	Adhesive Tape on Reel
Stud Size	8 (M4)
Wire Size AWG	14, 16
Wire Size mm²	1.00-2.50
Material Info	
Old Part Number	BB-U-137-08T
Reference - Drawing Numbers	
Sales Drawing	BBCD10104



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

China RoHS

Compliant

REACH SVHC

Not Contained Per -

ED/21/2016 (20 June

2016)

Halogen-Free

Status

Low-Halogen

Need more information on product

environmental compliance?

Email productcompliance@molex.com

Please visit the Contact Us section for any

non-product compliance questions.

China ROHS

Green Image

ELV

Not Relevant

Search Parts in this Series

19203 Series

Application Tooling | FAQ

Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global

Description

Product #

ATP Crimp Dies for the Tape Crimp Module and ATP-101 & 301 Press

0190270068

Mini-Mac™ Applicator, Air Feed Mylar Tape

0638853900

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION