

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0936011761](#)
Status: **Active**
Overview: [GWconnect® Heavy Duty Connectors \(HDC\)](#)
Description: [GWconnect® STD - Standard, Single Lever Hood, Die-cast Aluminum, with 2 Pegs, Side Entry, Size 10B «57x27», Extended M25 Thread, Grey](#)

Documents:

[RoHS Certificate of Compliance \(PDF\)](#)

General

| | |
|------------------|---|
| Product Family | Industrial Connectors / Enclosures |
| Series | 93601 |
| Component Size | 10B «57X27» |
| Component Type | Single Lever Hood |
| IP Rating | IP66, IP69 |
| Overview | GWconnect® Heavy Duty Connectors (HDC) |
| Product Category | Heavy Duty Connectors |
| Product Name | GWconnect® |
| Standard | ANSI/UL 50, ANSI/UL 50 E, CSA C22.2 No.94-1-2, EN 61984 |
| Type | STD |
| UPC | 887191847061 |
| Use With | Size 10B «57x27» S-D, S-DD, S-E, S-EE, S-EP, S-ES, S-HSB, S-ESHV, S-K, S-M, and S-EHV Inserts |

Physical

| | |
|---------------------|-------------------|
| Entry Location | Side |
| Hood Coating | Polyester Powder |
| Hood Color | GREY RAL 7037 |
| Lock to Mating Part | Yes |
| Material - Hood | Die-cast Aluminum |
| Material - Peg | Stainless Steel |
| Number of Pegs | 2 |
| Packaging Type | Bag |
| Thread Size | M25 |
| Thread Type | (M) Metric |

Electrical

| | |
|-------------------|------|
| Voltage - Maximum | 500V |
|-------------------|------|

Material Info

| | |
|-----------------|-------------|
| Old Part Number | 7810.6594.0 |
|-----------------|-------------|

GWconnect® is a registered trademark of Molex Incorporated in Italy and may be registered in other jurisdictions.



Series image - Reference only

EU ELV

Not Reviewed

EU RoHS

Not Reviewed

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

Need more information on product environmental compliance?

Email productcompliance@molex.com
Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS

Not Reviewed

ELV

Not Reviewed

Search Parts in this Series

[93601](#) Series