

Passive Voltage Probes

P3010 P6101B Datasheet



The P3010 and P6101B probes are designed to complement the Tektronix family of portable DSO and ART instruments.

Key features

- 1 M Ω inputs
- P6101B
 - 1X, 15 MHz, 300 V CAT II
 - Readout
- P3010
 - 10X, 100 MHz
- Molded passive voltage probes
- Single-piece, molded rubber body
- Lightweight ergonomic design
- 10-times improvement in durability

- HYBRID/SMT circuitry on multi-layer circuit board for improved performance and reliability
- New stronger, replaceable probe tip
- Safety certification
 - UL3111-2-031, CSA1010.2.031, EN61010-2-031, IEC61010-2-031
- 1-year unconditional guarantee
- Miniature probe tip compatible with a wide range of Tektronix accessories and adapters
- Mixture of high, medium, and low-frequency general-purpose relative measurements
 - Engineering and Design
 - Service
 - Manufacturing

P3010 P6101B passive voltage probes

Passive voltage probes are the most commonly used oscilloscope probe. Other specialty probes expand the range and functionality of an oscilloscope as a measurement system; but a general-purpose, passive voltage probe, is the working end of the oscilloscope, a tool used every day by engineers and technicians.



Two years of customer research, design innovation, and an exhaustive test program resulted in a most remarkable family of oscilloscope probes. This family of passive voltage probes is specifically designed for Tektronix analog and digital portable oscilloscopes. The 1X and 10X switchable probes combine the same high-quality electrical performance that customers expect from Tektronix with a new rugged mechanical design.

These probes are encased in a resilient, molded rubber body that is virtually indestructible. They are lighter in weight, more comfortable to hold, and more reliable than modular probe styles. The probes' replaceable tips are designed to withstand up to 20 pounds of force. Patented integral strain relief allows complete freedom of movement while providing superior cable flex. Each probe has received UL safety certification and meets MIL-T-28800, Class 3, environment specifications - something portable oscilloscope users will appreciate.

The P3010, and P6101B probes are designed to complement the Tektronix family of portable DSO and ART instruments. The core of each probe's performance is supplied by a Tektronix HYBRID/SMT device.

The instrumentation experience possessed by Tektronix provides an extra margin of quality and reliability to the molded probes that is not commonly available to probe manufacturers. These molded probes have been designed and tested to support the overall system performance and measurement quality that Tektronix oscilloscopes guarantee.

Through the introduction of the molded probes, Tektronix has set a new standard for passive voltage probe styling, performance, and durability.



Specifications

All specifications apply to all models unless noted otherwise.

Model overview

	P6101B	P3010
Attenuation	1X	10X
Bandwidth	15 MHz	100 MHz
Comp. range (Typical)	N.A.	10 pF to 15 pF
System input resistance	1 MΩ	10 MΩ
Input capacitance (Typical)	100 pF	13 pF
Input RMS	300 V _{RMS} CAT II	300 V _{RMS} CAT I & II ¹ 150 V _{RMS} CAT III ²
Readout		X

¹ 500 V peak, duty factor < 35%, pulse width < 100 ms

² 250 V peak, duty factor < 35%, pulse width < 100 ms

Physical characteristics

Cable length	2 m (6.56 ft)
Net weight (including accessories)	< 320 g (0.7 lb)

EMC, environment, and safety**Temperature range³**

P6101B	-15 °C to +65 °C (5 °F to 149 °F) Operating -62 °C to +85 °C (-80 °F to 185 °F) Nonoperating
P3010	-15 °C to +55 °C (5 °F to 131 °F) Operating -62 °C to +85 °C (-80 °F to 185 °F) Nonoperating

Humidity⁴

P6101B	95% to 97% Relative Humidity, 30 °C to 60 °C (86 °F to 140 °F)
P3010	95% to 97% Relative Humidity, 30 °C to 55 °C (86 °F to 131 °F)

Altitude	<3000 m (9842 ft), Operating <15, 240 m (50, 000 ft), Nonoperating
-----------------	---

Ordering information**Models**

P6101B	1X, 15 MHz Passive Voltage Probe.
P3010	10X, 100 MHz Passive Voltage Probe.

Standard accessories**Accessories**

016-0633-xx	Marker band set, 2 each of 5 colors
013-0107-xx	Retractable hook tip
196-3120-xx	6 in. ground lead
013-0277-xx	BNC-to-probe tip adapter
003-1433-xx	Adjustment tool
070-7819-xx	Manual (P6101B)
071-0466-xx	Manual (P3010)
-	Storage pouch

³ Tektronix Standard 062-2847-00, class 3. Refer to MIL-E-16400F, paragraphs 4.5.9 through 4.5.9.5.1, class 4.

⁴ Tektronix Standard 062-2847-00, class 3. Refer to MIL-E-16400F, paragraphs 4.5.9 through 4.5.9.5.1, class 4.

Recommended oscilloscopes

P6101B	All oscilloscopes
P3010	TDS3000

Warranty

One-year warranty covering all parts and labor.

Recommended accessories

Please see 5 mm Probe Accessories (miniature) probe system at <http://www.tek.com/datasheet/probe-accessories-2>



Tektronix is registered to ISO 9001 and ISO 14001 by SRI Quality System Registrar.

ASEAN / Australasia (65) 6356 3900
Belgium 00800 2255 4835*
Central East Europe and the Baltics +41 52 675 3777
Finland +41 52 675 3777
Hong Kong 400 820 5835
Japan 81 (3) 6714 3086
Middle East, Asia, and North Africa +41 52 675 3777
People's Republic of China 400 820 5835
Republic of Korea +822 6917 5084, 822 6917 5080
Spain 00800 2255 4835*
Taiwan 886 (2) 2656 6688

Austria 00800 2255 4835*
Brazil +55 (11) 3759 7627
Central Europe & Greece +41 52 675 3777
France 00800 2255 4835*
India 000 800 650 1835
Luxembourg +41 52 675 3777
The Netherlands 00800 2255 4835*
Poland +41 52 675 3777
Russia & CIS +7 (495) 6647564
Sweden 00800 2255 4835*
United Kingdom & Ireland 00800 2255 4835*

Balkans, Israel, South Africa and other ISE Countries +41 52 675 3777
Canada 1 800 833 9200
Denmark +45 80 88 1401
Germany 00800 2255 4835*
Italy 00800 2255 4835*
Mexico, Central/South America & Caribbean 52 (55) 56 04 50 90
Norway 800 16098
Portugal 80 08 12370
South Africa +41 52 675 3777
Switzerland 00800 2255 4835*
USA 1 800 833 9200

* European toll-free number. If not accessible, call: +41 52 675 3777

For Further Information. Tektronix maintains a comprehensive, constantly expanding collection of application notes, technical briefs and other resources to help engineers working on the cutting edge of technology. Please visit www.tek.com.

Copyright © Tektronix, Inc. All rights reserved. Tektronix products are covered by U.S. and foreign patents, issued and pending. Information in this publication supersedes that in all previously published material. Specification and price change privileges reserved. TEKTRONIX and TEK are registered trademarks of Tektronix, Inc. All other trade names referenced are the service marks, trademarks, or registered trademarks of their respective companies.



12 Apr 2016 51W-26153-4

