Sensitive Gate Silicon Controlled Rectifiers

Reverse Blocking Thyristors

Glassivated PNPN devices designed for high volume consumer applications such as temperature, light, and speed control; process and remote control, and warning systems where reliability of operation is important.

Features

- Glassivated Surface for Reliability and Uniformity
- Power Rated at Economical Prices
- Practical Level Triggering and Holding Characteristics
- Flat, Rugged, Thermopad Construction for Low Thermal Resistance, High Heat Dissipation and Durability
- Sensitive Gate Triggering
- These are Pb-Free Devices

MAXIMUM RATINGS (T_J = 25°C unless otherwise noted)

Characteristic	Symbol	Max	Unit
Peak Repetitive Off–State Voltage (Note 1) (Sine Wave, 50–60 Hz, R_{GK} = 1 kΩ, T_{C} = -40° to 110°C)	V _{DRM,} V _{RRM}		V
C106B C106D, C106D1* C106M, C106M1*		200 400 600	
On-State RMS Current (180° Conduction Angles, T _C = 80°C)	I _{T(RMS)}	4.0	Α
Average On-State Current (180° Conduction Angles, T _C = 80°C)	I _{T(AV)}	2.55	Α
Peak Non-Repetitive Surge Current (1/2 Cycle, Sine Wave, 60 Hz, T _J = +25°C)	I _{TSM}	20	Α
Circuit Fusing Considerations (t = 8.3 ms)	I ² t	1.65	A ² s
Forward Peak Gate Power (Pulse Width \leq 1.0 μ sec, T _C = 80°C)	P _{GM}	0.5	W
Forward Average Gate Power (Pulse Width \leq 1.0 μ sec, T _C = 80°C)	P _{G(AV)}	0.1	W
Forward Peak Gate Current (Pulse Width \leq 1.0 μ sec, T_C = 80°C)	I _{GM}	0.2	Α
Operating Junction Temperature Range	TJ	-40 to +110	°C
Storage Temperature Range	T _{stg}	-40 to +150	°C
Mounting Torque (Note 2)	_	6.0	in. lb.

Stresses exceeding Maximum Ratings may damage the device. Maximum Ratings are stress ratings only. Functional operation above the Recommended Operating Conditions is not implied. Extended exposure to stresses above the Recommended Operating Conditions may affect device reliability.

- 1. V_{DRM} and V_{RRM} for all types can be applied on a continuous basis. Ratings apply for zero or negative gate voltage; however, positive gate voltage shall not be applied concurrent with negative potential on the anode. Blocking voltages shall not be tested with a constant current source such that the voltage ratings of the devices are exceeded.
- Torque rating applies with use of compression washer (B52200F006).
 Mounting torque in excess of 6 in. lb. does not appreciably lower case-to-sink thermal resistance. Anode lead and heatsink contact pad are common.

1




Littelfuse.com

SCRs 4 A RMS, 200 – 600 Volts





MARKING DIAGRAM & PIN ASSIGNMENT



Y = Year

WW = Work Week

C106xx = Device Code

xx = B, D, D1, M, M1

G = Pb-Free Package

ORDERING INFORMATION

See detailed ordering and shipping information in the package dimensions section on page 5 of this data sheet.

THERMAL CHARACTERISTICS (T_C = 25°C unless otherwise noted.)

Characteristic	Symbol	Max	Unit
Thermal Resistance, Junction-to-Case	$R_{\theta JC}$	3.0	°C/W
Thermal Resistance, Junction-to-Ambient	$R_{ heta JA}$	75	°C/W
Maximum Lead Temperature for Soldering Purposes 1/8 in. from Case for 10 Seconds	TL	260	°C


ELECTRICAL CHARACTERISTICS ($T_C = 25^{\circ}C$ unless otherwise noted.)

Characteristic		Symbol	Min	Тур	Max	Unit
OFF CHARACTERISTICS		•	•	•	•	•
Peak Repetitive Forward or Reverse Blocking Current (V_{AK} = Rated V_{DRM} or V_{RRM} , R_{GK} = 1 k Ω)	T _J = 25°C T _J = 110°C	I _{DRM} , I _{RRM}	_ _	_ _	10 100	μ Α μ Α
ON CHARACTERISTICS						
Peak Forward On-State Voltage (Note 3) (I _{TM} = 4 A)		V _{TM}	_	-	2.2	V
Gate Trigger Current (Continuous dc) (Note 4) $(V_{AK}=6\ Vdc,\ R_L=100\ \Omega)$	$T_J = 25^{\circ}C$ $T_J = -40^{\circ}C$	l _{GT}	_ _	15 35	200 500	μΑ
Peak Reverse Gate Voltage (I _{GR} = 10 μA)		V_{GRM}	-	_	6.0	V
Gate Trigger Voltage (Continuous dc) (Note 4) $(V_{AK}=6~Vdc,~R_L=100~\Omega)$	$T_J = 25^{\circ}C$ $T_J = -40^{\circ}C$	V _{GT}	0.4 0.5	0.60 0.75	0.8 1.0	V
Gate Non-Trigger Voltage (Continuous dc) (Note 4) $(V_{AK} = 12 \text{ V}, R_L = 100 \Omega, T_J = 110^{\circ}\text{C})$		V _{GD}	0.2	-	_	V
Latching Current (V _{AK} = 12 V, I _G = 20 mA, R _{GK} = 1 k Ω)	$T_J = 25^{\circ}C$ $T_J = -40^{\circ}C$	ΙL	_ _	0.20 0.35	5.0 7.0	mA
Holding Current (V_D = 12 Vdc) (Initiating Current = 20 mA, R_{GK} = 1 k Ω)	$T_J = 25^{\circ}C$ $T_J = -40^{\circ}C$ $T_J = +110^{\circ}C$	I _H	- - -	0.19 0.33 0.07	3.0 6.0 2.0	mA
DYNAMIC CHARACTERISTICS					•	•
Critical Rate-of-Rise of Off-State Voltage (V _{AK} = Rated V _{DRM} , Exponential Waveform, R _{GK} = 1 k T _J = 110°C)	:Ω,	dv/dt	_	8.0	_	V/μs

^{3.} Pulse Test: Pulse Width \leq 2.0 ms, Duty Cycle \leq 2%. 4. R_{GK} is not included in measurement.

Voltage Current Characteristic of SCR

Symbol	Parameter
V_{DRM}	Peak Repetitive Off State Forward Voltage
I _{DRM}	Peak Forward Blocking Current
V_{RRM}	Peak Repetitive Off State Reverse Voltage
I _{RRM}	Peak Reverse Blocking Current
V_{TM}	Peak On State Voltage
I _H	Holding Current






Figure 1. Average Current Derating




Figure 2. Maximum On-State Power Dissipation




Figure 3. Typical Gate Trigger Current versus Junction Temperature

Figure 4. Typical Holding Current versus Junction Temperature






Figure 5. Typical Gate Trigger Voltage versus Junction Temperature

Figure 6. Typical Latching Current versus Junction Temperature

PACKAGE INTERCHANGEABILITY

The dimensional diagrams below compare the critical dimensions of the Littelfuse C-106 package with competitive devices. It has been demonstrated that the smaller dimensions of the Littelfuse package make it compatible in most lead-mount and chassis-mount applications. The user is advised to compare all critical dimensions for mounting compatibility.





Littelfuse C-106 Package

Competitive C-106 Package


ORDERING INFORMATION

Device	Package	Shipping [†]
C106BG	TO-225AA (Pb-Free)	500 Units / Box
C106DG	TO-225AA (Pb-Free)	500 Units / Box
C106D1G*	TO-225AA (Pb-Free)	500 Units / Box
C106MG	TO-225AA (Pb-Free)	500 Units / Box
C106M1G*	TO-225AA (Pb-Free)	500 Units / Box

^{*}D1 signifies European equivalent for D suffix and M1 signifies European equivalent for M suffix.

PACKAGE DIMENSIONS

TO-225 CASE 77-09 ISSUE Z



NOTES:

- DIMENSIONING AND TOLERANCING PER ANSI Y14 5M 1982
- 2. CONTROLLING DIMENSION: INCH.
 3. 077-01 THRU -08 OBSOLETE, NEW STANDARD 077-09.

	INCHES		MILLIN	IETERS	
DIM	MIN	MAX	MIN	MAX	
Α	0.425	0.435	10.80	11.04	
В	0.295	0.305	7.50	7.74	
С	0.095	0.105	2.42	2.66	
D	0.020	0.026	0.51	0.66	
F	0.115	0.130	2.93	3.30	
G	0.094 BSC		2.39 BSC		
Н	0.050	0.095	1.27	2.41	
J	0.015	0.025	0.39	0.63	
K	0.575	0.655	14.61	16.63	
M	5° TYP		5° TYP		
Q	0.148	0.158	3.76	4.01	
R	0.045	0.065	1.15	1.65	
S	0.025	0.035	0.64	0.88	
U	0.145	0.155	3.69	3.93	
٧	0.040		1.02		

STYLE 2:

PIN 1. CATHODE 2. ANODE 3. GATE

Littelfuse products are not designed for, and shall not be used for, any purpose (including, without limitation, automotive, military, aerospace, medical, life-saving, life-sustaining or nuclear facility applications, devices intended for surgical implant into the body, or any other application in which the failure or lack of desired operation of the product may result in personal injury, death, or property damage) other than those expressly set forth in applicable Littelfuse product documentation. Warranties granted by Littelfuse shall be deemed void for products used for any purpose not expressly set forth in applicable Littelfuse documentation. Littelfuse shall not be liable for any claims or damages arising out of products used in applications not expressly intended by Littelfuse as set forth in applicable Littelfuse documentation. The sale and use of Littelfuse products is subject to Littelfuse Terms and Conditions of Sale, unless otherwise agreed by Littelfuse.

Littelfuse.com

C106/D