



Drawings not to scale
All dimensions in mm

UL approved

SPECIFICATION

CONTACT FORM		B/CLOSED
SWITCHING VOLTAGE	Max. V	240 Vac/200 Vdc
SWITCHING CURRENT	Max. A	0.5
CARRY CURRENT	Max. A	1.0
SWITCHING CAPACITY	Max. VA	50
CONTACT RESISTANCE	Max. mΩ	200
LEAD WIRE		XLPE AWG22
REVERSIBLE SWITCH ACTION		YES
OPERATING PRESSURE	Max. Kg/cm ²	10
OPERATING TEMPERATURE	Deg. °C	-10° +120°
MATERIAL		Stainless Steel 304
SUITABLE SPECIFIC GRAVITY		0.75
WEIGHT	gm.	35
CLEARANCE HOLE DIA.	mm.	10

FLOAT SWITCHES

PART NUMBER
RF - 3001A

Rev. No.	Revision Note	Date	Signature
B	1998 Catalogue Page 52	1-1-98	RG



As part of the company policy of continued product improvement, specifications may change without notice. Our sales office will be pleased to help you with the latest information on this product range and details of our full design and manufacturing service. All products are supplied to our standard conditions of sale otherwise agreed in writing.

BS5750/ISO 9000
Reg. No. FM 21080