

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0010081051](#)
Status: **Active**
Overview: [KK® 508 Connector System](#)
Description: [KK® Header, Vertical, Round Pin, 5 Circuits, Tin \(Sn\) Plating, Pin Length 19.05mm](#)

Documents:

[3D Model](#) [Product Specification PS-99020-0087 \(PDF\)](#)
[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification


CSA LR19980
 UL E29179

General

Product Family PCB Headers
 Series 3003
 Application Board-to-Board, Power, Wire-to-Board
 Overview [KK® 508 Connector System](#)
 Product Name KK® 508
 UPC 800753745025

Physical

Breakaway No
 Circuits (Loaded) 5
 Circuits (maximum) 5
 Color - Resin Natural
 Durability (mating cycles max) 25
 First Mate / Last Break No
 Flammability 94V-2
 Glow-Wire Compliant No
 Guide to Mating Part No
 Keying to Mating Part None
 Lock to Mating Part None
 Material - Metal Brass
 Material - Plating Mating Tin
 Material - Plating Termination Tin
 Material - Resin Nylon
 Net Weight 1.258/g
 Number of Rows 1
 Orientation Vertical
 PC Tail Length 3.94mm
 PCB Locator No
 PCB Retention None
 PCB Thickness - Recommended 1.60mm
 Packaging Type Bag
 Pitch - Mating Interface 5.08mm
 Pitch - Termination Interface 5.08mm
 Plating min - Mating 5.080µm
 Plating min - Termination 5.080µm
 Polarized to Mating Part No
 Polarized to PCB No
 Shrouded No
 Stackable No
 Surface Mount Compatible (SMC) No
 Temperature Range - Operating See Product Specification
 Termination Interface: Style Through Hole



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per
 -ED/79/2015 (17
 December 2015)

Halogen-Free

Status

Low-Halogen

**Need more information on product
 environmental compliance?**

Email productcompliance@molex.com
 Please visit the [Contact Us](#) section for any
 non-product compliance questions.

China ROHS

ELV

Green Image

Not Relevant

Search Parts in this Series

[3003 Series](#)

Mates With

KK® Crimp Housing [3001](#) , [3002](#) KK® PC
 Board Connector

Electrical

Current - Maximum per Contact 7.0A
Voltage - Maximum 250V

Solder Process Data

Lead-freeProcess Capability N/A

Material Info

Engineering Number 3003-05A

Reference - Drawing Numbers

Product Specification PS-99020-0087
Sales Drawing SDAE-3003-N*

This document was generated on 08/26/2016

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION