

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0192210235](#)
Status: **Active**
Overview: Battery Cable Lugs
Description: Compression Style Ring Tongue Terminal for 2 AWG Wire, Stud Size 3/8" (M9), Plated

Documents:

[3D Model](#) [RoHS Certificate of Compliance \(PDF\)](#)
[Drawing \(PDF\)](#)

Agency Certification

CSA LR18689
 UL E32244

General

Product Family Ring and Spade Terminals
 Series [19221](#)
 Comments Heavy Duty
 Crimp Quality Equipment Yes
 Mil-Spec N/A
 Overview [Battery Cable Lugs](#)
 Product Name Battery Cable Lug
 Type Ring
 UPC 800753062344

Physical

Barrel Type Closed
 Insulation None
 Material - Plating Mating Tin
 Net Weight 10.540/g
 Packaging Type Bag
 Plating min - Mating 4.064µm
 Plating min - Termination 4.064µm
 Stud Size 3/8" (M9)
 Wire Insulation Diameter N/A
 Wire Size AWG 2

Solder Process Data


Lead-freeProcess Capability N/A

Material Info

Old Part Number BCL-238-PL

Reference - Drawing Numbers

Sales Drawing SD-19221-010



EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
 ED/21/2016 (20 June
 2016)

Halogen-Free

Status

Low-Halogen

**Need more information on product
 environmental compliance?**

Email productcompliance@molex.com
 Please visit the [Contact Us](#) section for any
 non-product compliance questions.

China ROHS

ELV

Green Image

Not Relevant

Search Parts in this Series

[19221](#) Series

Application Tooling | [FAQ](#)

*Tooling specifications and manuals are
 found by selecting the products below.
 Crimp Height Specifications are then
 contained in the Application Tooling
 Specification document.*

Global

Description	Product #
Hydraulic Dieless Crimping Tool	0638161700
Hand Crimp Tool	0192840034
Die Set (large) for the HHLS Hydraulic Crimper	0192900010
Manual tool for Crimping non-insulated 8AWG thru 4/0 Terminals	0192940008

Manual Putt Pump 0192860117
Hydraulic System,
Die set required
Square "DIN" style 0640037970
dies for 2 AWG

This document was generated on 07/12/2016

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION