

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [0459714185](#)  
**Status:** **Active**  
**Overview:** SEARAY\* Plugs, Receptacles and Copper Flex Assemblies  
**Description:** SEARAY\* Receptacle, 320 Circuits, 5.00mm Unmated Height, 8 Rows, with Pegs, Solder Charge™

**Documents:**

<a href="#">3D Model</a>	<a href="#">Packaging Specification PK-45971-002 (PDF)</a>
<a href="#">Drawing (PDF)</a>	<a href="#">Packaging Specification RPK-45971-009 (PDF)</a>
<a href="#">Packaging Specification PK-45971-001 (PDF)</a>	<a href="#">RoHS Certificate of Compliance (PDF)</a>

**Agency Certification**


CSA	LR19980
UL	E29179

**General**

Product Family	PCB Receptacles
Series	<a href="#">45971</a>
Application	Board-to-Board, Signal
Electrical Model	Yes
Overview	<a href="#">SEARAY* Plugs, Receptacles and Copper Flex Assemblies</a>
Product Name	SEARAY*
UPC	883906236403

**Physical**

Circuits (Loaded)	320
Circuits (maximum)	320
Color - Resin	Black
Durability (mating cycles max)	100
Flammability	94V-0
Glow-Wire Compliant	No
Guide to Mating Part	No
Keying to Mating Part	Yes
Lock to Mating Part	No
Material - Metal	Copper Alloy
Material - Plating Mating	Gold
Material - Plating Termination	Tin
Material - Resin	High Temperature Thermoplastic
Net Weight	3.597/g
Number of Rows	8
Orientation	Vertical
PCB Locator	Yes
PCB Retention	Yes
PCB Thickness - Recommended	1.60mm
Packaging Type	Embossed Tape on Reel
Pitch - Mating Interface	1.27mm
Pitch - Termination Interface	1.27mm
Plating min - Mating	0.762µm
Plating min - Termination	2.540µm
Polarized to Mating Part	Yes
Polarized to PCB	Yes
Robotic Placement	Pick and Place Cap
Stackable	No
Surface Mount Compatible (SMC)	Yes
Temperature Range - Operating	-55°C to +125°C
Termination Interface: Style	Surface Mount



*Series image - Reference only*

**EU ELV**

**Not Relevant**

**EU RoHS**

**Compliant**

**REACH SVHC**

Not Contained Per - ED/21/2016 (20 June 2016)

**Halogen-Free**

**Status**

**Low-Halogen**

**Need more information on product environmental compliance?**

Email [productcompliance@molex.com](mailto:productcompliance@molex.com)  
Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS

ELV

Green Image

Not Relevant

**Search Parts in this Series**

[45971](#) Series

**Mates With**

[45970](#) SEARAY\* Plug

Unmated Height 5.00mm

**Electrical**

Current - Maximum per Contact 2.7A  
Grounding to PCB No  
Voltage - Maximum 240V AC

**Solder Process Data**

Duration at Max. Process Temperature (seconds) 003  
Lead-freeProcess Capability REFLOW  
Max. Cycles at Max. Process Temperature 001  
Process Temperature max. C 260

**Material Info**

**Reference - Drawing Numbers**

Electrical Model Document EE-45970-010, EE-46556-0085  
Packaging Specification PK-45971-001, PK-45971-002, RPK-45971-009  
S-Parameter Model SP-45970-010, SP-46556-0085  
Sales Drawing SD-45971-001  
Symbol/Footprint Data SYM-45971-4185

\*SEARAY is a trademark of Samtec, Inc.

This document was generated on 07/13/2016

**PLEASE CHECK [WWW.MOLEX.COM](http://WWW.MOLEX.COM) FOR LATEST PART INFORMATION**