

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0460181541

Status:


Active

Overview:

Mini-Fit® Plus Connector System

Description:

Mini-Fit® Plus High Mating Cycle Female Crimp Terminal, 18-20 AWG, Reel, Select Gold (Au) Plating with Proprietary Molex Advanced Contact Surface Finish (CSF) in Contact Area



Documents:

Drawing (PDF)

RoHS Certificate of Compliance (PDF)

Packaging Specification PK-46018-001 (PDF)

General	
Product Family	Crimp Terminals
Series	46018
Application	Power
Comments	Current Rating = 9A Max. Using 18 AWG Wire and 7A Max. Using 20 AWG Wire
Crimp Quality Equipment	Yes
Overview	Mini-Fit® Plus Connector System
Packaging Alternative	46018-1542 (Loose)
Product Name	Mini-Fit® Plus
UPC	822350560474
Physical	
Gender	Female
Material - Metal	Copper Alloy
Material - Plating Mating	Gold
Material - Plating Termination	Tin
Net Weight	0.150/g
Packaging Type	Reel
Plating min - Mating	0.051µm
Plating min - Termination	2.540µm
Termination Interface: Style	Crimp or Compression
Wire Insulation Diameter	1.65-2.95mm
Wire Size AWG	18, 20
Wire Size mm²	N/A
Electrical	
Current - Maximum per Contact	13.0A
Voltage - Maximum	600V
Solder Process Data	
Lead-freeProcess Capability	N/A
Material Info	
Reference - Drawing Numbers	
Packaging Specification	PK-46018-001
Sales Drawing	SD-46018-001

EU ELV

Not Relevant

EU RoHS

Compliant

China RoHS

REACH SVHC

Not Contained Per -

ED/21/2016 (20 June

2016)

Halogen-Free

Status

Low-Halogen

Need more information on product

environmental compliance?

Email productcompliance@molex.com

Please visit the [Contact Us](#) section for any

non-product compliance questions.

China ROHS

Green Image

ELV

Not Relevant

Search Parts in this Series

46018 Series

Use With

5557 Mini-Fit Jr.™ Receptacles, 30067 Mini-Fit® TPA Receptacles, 42474 Mini-Fit® BMI Panel Mount Receptacles, 44516 Mini-Fit® BMI Panel Mount Slide-N-Lock Receptacles

Application Tooling | FAQ

Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global

Description

Product #

FineAdjust™

Applicator for

Insulation OD

0639002900

1.65-2.05mm, 18-24 AWG Wire Hand Crimp Tool for Male and Female Crimp Terminals, 16-24 AWG Wire Extraction Tool	<u>0638190900</u> <u>0011030044</u>
FineAdjust™ Applicator for Insulation OD 2.50-2.95mm, 18-24 AWG Wire FineAdjust™ Applicator for Insulation OD 1.90-2.30mm - 18-24 AWG FineAdjust™ Applicator for Insulation OD 1.40-1.70mm - 18-24 AWG FineAdjust™ Applicator for Insulation OD 2.30-2.60mm - 18-24 AWG T2 Terminator™ for insulation OD 2.50-2.95mm - 18-24 AWG T2 Terminator™ insulation OD 1.65 – 2.05mm – 18 – 24 AWG T2 Terminator™ for insulation OD 2.50-2.95mm optimized for 18 AWG only T2 Terminator™ for insulation OD 2.30-2.60mm - 18-24 AWG FineAdjust™ Applicator for Insulation OD 2.50-2.95mm Optimized for 18 AWG Only T2 Terminator™ for insulation OD 1.90-2.30mm - 18-24 AWG T2 Terminator™ for insulation OD 1.40-1.70mm - 18-24 AWG	 <u>0639002600</u> <u>0639015600</u> <u>0639023900</u> <u>0639024900</u> <u>0639102600</u> <u>0639102900</u> <u>0639124800</u> <u>0639124900</u> <u>0639024800</u> <u>0639115600</u> <u>0639123900</u>