

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0349690140

Status:

Active

Overview:

Stac64™ Single, Multi-Pocket and Hybrid Header System

Description:

Stac64™ Hybrid Receptacle Assembly, 14 Circuit, Black, Polarization A

Documents:

3D Model

Drawing (PDF)

Packaging Specification PK-31301-201 (PDF)

RoHS Certificate of Compliance (PDF)

General	
Product Family	Crimp Housings
Series	34969
Application	Power, Signal, Wire-to-Board
Comments	Current is dependent on connector size, ambient temperature, blade size and related factors. 2.80mm – 30.0A; 0.64mm - 6.0A. . Polarization A, 10 x 0.64 and 4 x 2.8
Overview	Stac64™ Single, Multi-Pocket and Hybrid Header System
Product Name	Stac64™
UPC	887191311913
Physical	
Circuits (maximum)	14
Circuits Detail	21 x 0.64 and 4 x 2.8
Color - Resin	Black
Gender	Female
Glow-Wire Compliant	No
Keying to Mating Part	Yes
Lock to Mating Part	No
Material - Resin	Modified Polystyrene
Net Weight	7.690/g
Number of Rows	2
Packaging Type	Carton
Panel Mount	No
Pitch - Mating Interface	2.54mm, 5.25mm
Polarized to Mating Part	Yes
Ports	1
Stackable	No
Temperature Range - Operating	-40°C to +105°C
Electrical	
Current - Maximum per Contact	30.0A, 6.0A
Solder Process Data	
Lead-freeProcess Capability	N/A
Material Info	
Reference - Drawing Numbers	
Packaging Specification	PK-31301-201
Sales Drawing	SD-34969-010



Series image - Reference only

EU ELV

Compliant

EU RoHS

Compliant

China RoHS

REACH SVHC

Not Contained Per -

ED/21/2016 (20 June

2016)

Halogen-Free

Status

Not Relevant

Need more information on product

environmental compliance?

Email productcompliance@molex.com

Please visit the [Contact Us](#) section for any

non-product compliance questions.

China ROHS

Not Relevant

ELV

Compliant

Search Parts in this Series

34969 Series

Mates With

34773 , 34772 Stac64™ Hybrid Receptacle

Connector

Use With

CTX64 Terminal 34803

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION