



NC10FRX-14-B

Easy to assemble 8 + 2 pole right-angle female XLR connector, black chrome metal housing, secure locking and proven Neutrik chuck type strain relief

Features & Benefits

- Suitable for data offering CAT 5e performance and power up to 16 A and 50 V - exceeds PoE+ capabilities
- Superior ruggedness compared to RJ45 type connectors
- All metal housing offers best overall RF protection and electromagnetic shielding



Technical Information

Product

Title	NC10FRX-14-B
Connection Type	XLR
Gender	female

Electrical

Contact resistance	$\leq 3 \text{ m}\Omega$
Dielectric strength	1 kVdc
Insulation resistance	$> 10 \text{ G}\Omega$ (initial), 0.1 (after damp heat test)

Number of electrical contacts	8 + 2
Rated current per contact	16 A (power pins), 3 A (data pins)
Cable shield - shell connection	choosable
Transmission performance	CAT 5e

Mechanical

Cable O.D.	8.0 - 10.0 mm
Insertion force	≤ 20 N
Withdrawal force	≤ 20 N
Lifetime	> 1000 mating cycles
Wiresize	2.5 mm ² / AWG 14 (power pins), 1 mm ² / AWG 18 (data pins)

Material

Bushing	PA / PU
Contact plating	0.2 μm Au hard alloy over 2 μm Ni
Contacts	Brass (CuZn39Pb3)
Insert	Polyamide (PA 6.6 30 % GR)
Locking element	Zinc diecast (ZnAl4Cu1)
Shell	Zinc diecast (ZnAl4Cu1)
Shell plating	Black chromium
Split sleeve	POM

Environmental

Flammability	UL 94 HB
Protection class	IP 40
Solderability	Complies with IEC 68-2-20
Temperature range	-30 °C to +80 °C
Manufacturing Standard	IEC 61076-2-103

Accessories

HTXX-14



XXR-*



XXCR



