

## General Information

Extended Product Type:	ZS6-WH
Product ID:	1SNK506065R0000
EAN:	3472595060658
Catalog Description:	ZS6-WH Screw Clamp Terminal Block - Feed-through - White
Long Description:	Save space by connecting conductors up to 6 mm <sup>2</sup> (without insulated ferrule, CB certified) 10 AWG in just 6 mm 0.236 in spacing, - Perfectly adapted to solar applications: voltage is rated 1000 V AC / DC IEC.

## Categories

Products » Low Voltage Products and Systems » Connection Devices » Terminal Blocks » SNK Series

## Ordering

Minimum Order Quantity:	50 piece
Customs Tariff Number:	85369010
Color:	White

## Dimensions

Product Net Height:	53 mm
Product Net Length:	47.3 mm
Product Net Depth:	47.3 mm
Product Net Weight:	10.6 g
Product Net Width:	6 mm

## Technical

Spacing:	6 mm
Connection Type:	Screw clamp
Function:	Feed-through
Number of Levels:	1
Connecting Capacity Main Circuit:	Screw Clamp / Flexible 1x 0.2 ... 6 mm <sup>2</sup> Screw Clamp / Flexible 2x 0.2 ... 2.5 mm <sup>2</sup> Screw Clamp / Rigid 1x 0.2 ... 6 mm <sup>2</sup> Screw Clamp / Rigid 2x 0.2 ... 2.5 mm <sup>2</sup> Screw Clamp / With Insulated Ferrule 1x 0.22 ... 4 mm <sup>2</sup> Screw Clamp / Without Insulated Ferrule 1x 0.22 ... 4 mm <sup>2</sup> Screw Clamp / With Twin Ferrule 2x 0.22 ... 2.5 mm <sup>2</sup>
Gauge Type:	A4-B3
Rated Current (I <sub>N</sub> ):	Main Circuit 41 A
Rated Short-time Withstand Current (I <sub>cw</sub> ):	for 1 s 720 A
Rated Voltage (U <sub>r</sub> ):	1000 V
Rated Impulse Withstand Voltage (U <sub>imp</sub> ):	8000 V
Dielectric Test Voltage:	2200 V
Pollution Degree:	3
Power Loss:	1.3 W
Degree of Protection:	acc. to IEC 60529, IEC 60947-1, EN 60529 Main Terminals IP20
Insulation Material:	Polyamide
Mounting on DIN Rail:	TH35-7.5 (35 x 7.5 mm Mounting Rail) acc. to IEC 60715 TH35-15 (35 x 15 mm Mounting Rail) acc. to IEC 60715
Wire Stripping Length:	10.5 mm
Recommended Screw Driver:	4 mm
Rated Cross-Section:	6 mm <sup>2</sup>

## Technical UL/CSA

Connecting Capacity Main Circuit UL/CSA:	Screw Clamp / Flexible 1x 24 ... 10 AWG Screw Clamp / Flexible 2x 24 ... 14 AWG Screw Clamp / Rigid 1x 24 ... 10 AWG Screw Clamp / Rigid 2x 24 ... 14 AWG Screw Clamp / With Insulated Ferrule 1x 24 ... 12 AWG Screw Clamp / Without Insulated Ferrule 1x 24 ... 12 AWG Screw Clamp / With Twin Ferrule 2x 24 ... 14 AWG
Connecting Capacity UL/CSA:	Stranded 10 AWG
Flammability According to UL94:	V0

Short-Circuit Current Rating (SCCR):	100 kA
Maximum Operating Voltage	Main Circuit 600 V
UL/CSA:	

## Environmental

Resistance to Vibrations acc. to IEC 60068-2-6:	Compliant
---	-----------

RoHS Status:	Following EU Directive 2002/95/EC August 18, 2005 and amendment
--------------	---

Ambient Air Temperature:	Operation -55 ... +110 °C
	Storage -55 ... +110 °C

## Certificates and Declarations (Document Number)

Instructions and Manuals:	1SNK160027C0201
ATEX Certificate:	1SND162004A1706
BV Certificate:	1SND161073A0203
CB Certificate:	1SND161025A0203
CSA Certificate:	1SND161070A0208
cUL Certificate:	1SND161040A0206
Data Sheet, Technical Information:	1SNK161008D0201
Declaration of Conformity - CE:	1SND225112U1000
DNV Certificate:	1SND161087A0202
EAC Certificate:	1SND161010A1100
RINA Certificate:	1SND161088A0200
RoHS Information:	1SND230491F0206

## Classifications

E-nummer:	2925932
ETIM 4:	EC000897 - Feed-through terminal block
ETIM 5:	EC000897 - Feed-through terminal block
ETIM 6:	EC000897 - Feed-through terminal block
Object Classification Code:	X

## Container Information

Package Level 1 Width:	62 mm
Package Level 1 Length:	252 mm
Package Level 1 Height:	52 mm
Package Level 1 Gross Weight:	0.53 kg
Package Level 1 EAN:	3472595060658
Package Level 2 Units:	750 piece
Package Level 2 Width:	300 mm
Package Level 2 Length:	400 mm
Package Level 2 Height:	200 mm
Package Level 2 Gross Weight:	8.450 kg
Package Level 3 Units:	36000 piece
Product Packing Type:	Box
Package Level 1 Units:	50 piece

