

General Information

Extended Product Type:	ZS6-D2
Product ID:	1SNK506210R0000
EAN:	3472595062102
Catalog Description:	ZS6-D2 Screw Clamp Terminal Block - Double Deck - Grey
Long Description:	- Save space with double deck terminal blocks: 2 independent circuits connected in just 6 mm 0.236 in spacing, - Customize yourself the ZS6-D2 by soldering electronic components (up to 8.8 mm x 3.2 mm 0.346 x 0.125 in) in the existing linking bars punching, - Boost the performances: ZS6-D... with ES4-D2 end section is rated 1000 V DC IEC, perfectly adapted to solar applications.

Categories

Products » Low Voltage Products and Systems » Connection Devices » Terminal Blocks » SNK Series

Ordering

Minimum Order Quantity:	50 piece
Customs Tariff Number:	85369010
Color:	Grey

Dimensions

Product Net Height:	70.4 mm
Product Net Length:	65.5 mm
Product Net Depth:	65.5 mm
Product Net Weight:	18.4 g
Product Net Width:	6 mm

Technical

Spacing:	6 mm
Connection Type:	Screw clamp
Function:	Feed-through
Number of Levels:	2
Connecting Capacity Main Circuit:	Screw Clamp / Flexible 1x 0.2 ... 6 mm ² Screw Clamp / Flexible 2x 0.2 ... 2.5 mm ² Screw Clamp / Rigid 1x 0.2 ... 6 mm ² Screw Clamp / Rigid 2x 0.2 ... 2.5 mm ² Screw Clamp / With Insulated Ferrule 1x 0.22 ... 4 mm ² Screw Clamp / Without Insulated Ferrule 1x 0.22 ... 4 mm ² Screw Clamp / With Twin Ferrule 2x 0.22 ... 2.5 mm ²
Gauge Type:	A4-B3
Rated Current (I_n):	Main Circuit 40 A
Rated Short-time Withstand Current (I_{cw}):	for 1 s 720 A
Rated Voltage (U_r):	800 V
Rated Impulse Withstand Voltage (U_{imp}):	8000 V
Dielectric Test Voltage:	2000 V
Pollution Degree:	3
Power Loss:	2.6 W
Degree of Protection:	acc. to IEC 60529, IEC 60947-1, EN 60529 Main Terminals IP20
Insulation Material:	Polyamide
Mounting on DIN Rail:	TH35-7.5 (35 x 7.5 mm Mounting Rail) acc. to IEC 60715 TH35-15 (35 x 15 mm Mounting Rail) acc. to IEC 60715
Wire Stripping Length:	10.0 mm
Recommended Screw Driver:	4 mm
Rated Cross-Section:	6 mm ²

Technical UL/CSA

Connecting Capacity Main Circuit UL/CSA:	Screw Clamp / Flexible 1x 24 ... 10 AWG Screw Clamp / Flexible 2x 24 ... 14 AWG Screw Clamp / Rigid 1x 24 ... 10 AWG Screw Clamp / Rigid 2x 24 ... 14 AWG Screw Clamp / With Insulated Ferrule 1x 24 ... 12 AWG Screw Clamp / Without Insulated Ferrule 1x 24 ... 12 AWG Screw Clamp / With Twin Ferrule 2x 24 ... 14 AWG
Connecting Capacity UL/CSA:	Stranded 10 AWG

Flammability According to UL94:	V0
Short-Circuit Current Rating (SCCR):	100 kA
Maximum Operating Voltage	Main Circuit 300 V
UL/CSA:	

Environmental

Resistance to Vibrations acc. to IEC 60068-2-6:	Compliant
RoHS Status:	Following EU Directive 2002/95/EC August 18, 2005 and amendment
Ambient Air Temperature:	Operation -55 ... +110 °C Storage -55 ... +110 °C

Certificates and Declarations (Document Number)

Instructions and Manuals:	1SNK160027C0201
ATEX Certificate:	1SND162004A1706
BV Certificate:	1SND161073A0203
CB Certificate:	1SND161026A0204
CSA Certificate:	1SND161070A0208
cUL Certificate:	1SND161040A0206
Data Sheet, Technical Information:	1SNK161014D0201
Declaration of Conformity - CE:	1SND225112U1000
DNV Certificate:	1SND161087A0202
EAC Certificate:	1SND161010A1100
RINA Certificate:	1SND161088A0200
RoHS Information:	1SND230491F0206

Classifications

E-number:	2925935
ETIM 4:	EC000897 - Feed-through terminal block
ETIM 5:	EC000897 - Feed-through terminal block
ETIM 6:	EC000897 - Feed-through terminal block
Object Classification Code:	X

Container Information

Package Level 1 Width:	61 mm
Package Level 1 Length:	353 mm
Package Level 1 Height:	67 mm
Package Level 1 Gross Weight:	0.92 kg
Package Level 1 EAN:	3472595062102
Package Level 2 Units:	400 piece
Package Level 2 Width:	300 mm
Package Level 2 Length:	400 mm
Package Level 2 Height:	200 mm
Package Level 2 Gross Weight:	7.860 kg
Package Level 3 Units:	19200 piece
Product Packing Type:	Box
Package Level 1 Units:	50 piece

