

## General Information

<b>Extended Product Type:</b>	AF12-30-01-12
<b>Product ID:</b>	1SBL157001R1201
<b>EAN:</b>	3471523110427
<b>Catalog Description:</b>	AF12-30-01-12 48-130V50/60HZ-DC Contactor
<b>Long Description:</b>	AF12 contactors are used for controlling power circuits up to 690 V AC and 220 V DC. They are mainly used for controlling 3-phase motors, non-inductive or slightly inductive loads. AF... contactors include an electronic coil interface accepting a wide control voltage $U_c$ min. ... $U_c$ max. Only four coils cover control voltages between 24...500 V 50/60 Hz or 20...500 V DC. AF contactors can manage large control voltage variations. One coil can be used for different control voltages used worldwide without any coil change. AF contactors have built-in surge protection and do not require additional surge suppressors. The AF... series 1-stack 3-pole contactors are of the block type design. - Main poles and auxiliary contact blocks: 3 main poles, 1 built-in auxiliary contact, front and side-mounted add-on auxiliary contact blocks (mechanically-linked auxiliary contacts compliant with Annex L of IEC 60947-5-1. N.C. mirror contacts compliant with Annex F of IEC 60947-4-1) - Control circuit: AC or DC operated - Accessories: a wide range of accessories is available.

## Categories

Products » Low Voltage Products and Systems » Control Products » Contactors » Block Contactors

## Ordering

<b>Minimum Order Quantity:</b>	1 piece
<b>Customs Tariff Number:</b>	85369085
<b>EAN:</b>	3471523110427

## Dimensions

<b>Product Net Depth:</b>	77 mm
<b>Product Net Height:</b>	86 mm
<b>Product Net Weight:</b>	0.270 kg
<b>Product Net Width:</b>	45 mm

## Container Information

<b>Package Level 1 Width:</b>	87 mm
<b>Package Level 1 Length:</b>	79 mm
<b>Package Level 1 Height:</b>	47 mm
<b>Package Level 1 Gross Weight:</b>	0.27 kg
<b>Package Level 1 EAN:</b>	3471523110427
<b>Package Level 2 Units:</b>	54 piece
<b>Package Level 2 Width:</b>	250 mm
<b>Package Level 2 Length:</b>	300 mm
<b>Package Level 2 Height:</b>	315 mm
<b>Package Level 3 Units:</b>	1296 piece
<b>Package Level 1 Units:</b>	1 piece

## Technical

<b>Number of Main Contacts NC:</b>	0
<b>Number of Auxiliary Contacts NO:</b>	0
<b>Number of Auxiliary Contacts NC:</b>	1
<b>Standards:</b>	IEC 60947-1 / 60947-4-1 and EN 60947-1 / 60947-4-1, UL 508, CSA C22.2 N°14
<b>Rated Operational Voltage:</b>	Auxiliary Circuit 690 V Main Circuit 690 V
<b>Rated Frequency (f):</b>	Auxiliary Circuit 50 / 60 Hz Main Circuit 50 / 60 Hz
<b>Conventional Free-air Thermal Current (<math>I_{th}</math>):</b>	acc. to IEC 60947-4-1, Open Contactors $q = 40$ °C 35 A acc. to IEC 60947-5-1, $q = 40$ °C 16 A
<b>Rated Operational Current AC-1 (<math>I_e</math>):</b>	(690 V) 40 °C 28 A (690 V) 60 °C 28 A (690 V) 70 °C 24 A
<b>Rated Operational Current AC-3 (<math>I_e</math>):</b>	(220 / 230 / 240 V) 60 °C 12 A (380 / 400 V) 60 °C 12 A (415 V) 60 °C 12 A (440 V) 60 °C 12 A (500 V) 60 °C 12.5 A (690 V) 60 °C 9 A

<b>Rated Operational Power AC-3 (P<sub>e</sub>):</b>	(220 / 230 / 240 V) 3 kW (380 / 400 V) 5.5 kW (400 V) 5.5 kW (415 V) 5.5 kW (440 V) 5.5 kW (500 V) 7.5 kW (690 V) 7.5 kW
<b>Rated Operational Current AC-15 (I<sub>e</sub>):</b>	(220 / 240 V) 4 A (24 / 127 V) 6 A (400 / 440 V) 3 A (500 V) 2 A (690 V) 2 A
<b>Rated Short-time Withstand Current (I<sub>cw</sub>):</b>	at 40 °C Ambient Temp, in Free Air, from a Cold State 10 s 150 A at 40 °C Ambient Temp, in Free Air, from a Cold State 15 min 35 A at 40 °C Ambient Temp, in Free Air, from a Cold State 1 min 60 A at 40 °C Ambient Temp, in Free Air, from a Cold State 1 s 300 A at 40 °C Ambient Temp, in Free Air, from a Cold State 30 s 80 A for 0.1 s 140 A for 1 s 100 A
<b>Maximum Breaking Capacity:</b>	cos phi=0.45 (cos phi=0.35 for I <sub>e</sub> > 100 A) at 440 V 250 A cos phi=0.45 (cos phi=0.35 for I <sub>e</sub> > 100 A) at 690 V 106 A
<b>Maximum Electrical Switching Frequency:</b>	AC-1 600 cycles per hour AC-15 1200 cycles per hour AC-2 / AC-4 300 cycles per hour AC-3 1200 cycles per hour DC-13 900 cycles per hour
<b>Rated Operational Current DC-13 (I<sub>e</sub>):</b>	(110 V) 0.55 A / 60 W (125 V) 0.55 A / 69 W (220 V) 0.27 A / 60 W (24 V) 6 A / 144 W (250 V) 0.27 A / 68 W (400 V) 0.15 A / 60 W (48 V) 2.8 A / 134 W (500 V) 0.13 A / 65 W (600 V) 0.1 A / 60 W (72 V) 1 A / 72 W
<b>Rated Insulation Voltage (U<sub>i</sub>):</b>	acc. to UL/CSA 600 V acc. to IEC 60947-4-1 and VDE 0110 (Gr. C) 690 V
<b>Rated Impulse Withstand Voltage (U<sub>imp</sub>):</b>	6 kV
<b>Maximum Mechanical Switching Frequency:</b>	3600 cycles per hour
<b>Rated Control Circuit Voltage (U<sub>c</sub>):</b>	50 Hz 48 ... 130 V 60 Hz 48 ... 130 V DC Operation 48 ... 130 V
<b>Operate Time:</b>	Between Coil De-energization and NC Contact Closing 13...98 ms Between Coil De-energization and NO Contact Opening 11...95 ms Between Coil Energization and NC Contact Opening 38...90 ms Between Coil Energization and NO Contact Closing 40...95 ms
<b>Connecting Capacity Main Circuit:</b>	Flexible with Insulated Ferrule 1x 0.75...4 mm <sup>2</sup> Flexible with Insulated Ferrule 2x 0.75...2.5 mm <sup>2</sup> Flexible with Ferrule 1/2x 0.75...6 mm <sup>2</sup> Rigid 1/2x 1...6 mm <sup>2</sup>
<b>Connecting Capacity Auxiliary Circuit:</b>	Flexible with Ferrule 1/2x 0.75 ... 2.5 mm <sup>2</sup> Flexible with Insulated Ferrule 1x 0.75 ... 2.5 mm <sup>2</sup> Flexible with Insulated Ferrule 2x 0.75 ... 1.5 mm <sup>2</sup> Rigid 1/2x 1...2.5 mm <sup>2</sup>
<b>Connecting Capacity Control Circuit:</b>	Flexible with Ferrule 1/2x 0.75 ... 2.5 mm <sup>2</sup> Flexible with Insulated Ferrule 1x 0.75 ... 2.5 mm <sup>2</sup> Flexible with Insulated Ferrule 2x 0.75 ... 1.5 mm <sup>2</sup> Rigid 1/2x 1 ... 2.5 mm <sup>2</sup>
<b>Wire Stripping Length:</b>	Auxiliary Circuit 10 mm Control Circuit 10 mm Main Circuit 10 mm
<b>Degree of Protection:</b>	acc. to IEC 60529, IEC 60947-1, EN 60529 Auxiliary Terminals IP20 acc. to IEC 60529, IEC 60947-1, EN 60529 Coil Terminals IP20 acc. to IEC 60529, IEC 60947-1, EN 60529 Main Terminals IP20
<b>Terminal Type:</b>	Screw Terminals
<b>Number of Main Contacts NO:</b>	3

## Environmental

<b>Climatic Withstand:</b>	Category B according to IEC 60947-1 Annex Q
<b>Maximum Operating Altitude Permissible:</b>	3000 m
<b>Resistance to Vibrations acc. to IEC</b>	5 ... 300 Hz 4 g closed position / 2 g open position

**60068-2-6:****Resistance to Shock acc. to IEC 60068-2-27:**

Closed, Shock Direction: B1 25 g  
 Open, Shock Direction: B1 5 g  
 Shock Direction: A 30 g  
 Shock Direction: B2 15 g  
 Shock Direction: C1 25 g  
 Shock Direction: C2 25 g

**RoHS Status:**

Planned to follow EU Directive 2002/95/EC August 18, 2005 and amendment after 2008 Q1

**Ambient Air Temperature:**

Close to Contactor for Storage -60...+80 °C  
 Close to Contactor Fitted with Thermal O/L Relay -25 ... +60 °C  
 Close to Contactor without Thermal O/L Relay -40 ... +70 °C

**Technical UL/CSA****General Use Rating UL/CSA:**

(600 V AC) 28 A

**Horsepower Rating UL/CSA:**

(120 V AC) Single Phase 1 Hp  
 (240 V AC) Single Phase 2 Hp  
 (200 ... 208 V AC) Three Phase 3 Hp  
 (220 ... 240 V AC) Three Phase 3 Hp  
 (440 ... 480 V AC) Three Phase 7-1/2 Hp  
 (550 ... 600 V AC) Three Phase 10 Hp

**Tightening Torque UL/CSA:**

Auxiliary Circuit 11 in-lb  
 Control Circuit 11 in-lb  
 Main Circuit 13 in-lb

**Certificates and Declarations (Document Number)****Instructions and Manuals:**

1SBC101027M6801

**ABS Certificate:**

ABS\_15-GE1349500-PDA\_90682247

**CB Certificate:**

CB\_SE\_70855M1

**CCC Certificate:**

CCC\_2010010304445624

**Data Sheet, Technical Information:**

1SBC101405D0201

**Declaration of Conformity - CE:**

1SBD250000U1000

**DNV Certificate:**

DNV-GL\_E13871

**EAC Certificate:**

EAC\_RU C-FR ME77 B01010

**GL Certificate:**

DNV-GL\_E13871

**GOST Certificate:**

GOST\_POCCFR.ME77.B07175.pdf

**LR Certificate:**

LRS\_1300087E1

**RINA Certificate:**

RINA\_ELE084013XG

**RMRS Certificate:**

RMRS\_1400682124

**RoHS Information:**

1SBD251013E1000

**UL Certificate:**

UL\_20140305-E312527\_7\_1

**UL Listing Card:**

UL\_E312527

**Classifications****E-number:**

3211363

**ETIM 4:**

EC000066 - Magnet contactor, AC-switching

**ETIM 5:**

EC000066 - Magnet contactor, AC-switching

**ETIM 6:**

EC000066 - Power contactor, AC switching

**UNSPSC:**

39121529

**Object Classification Code:**

Q

