

General Information

Extended Product Type:	CT MAX 300
Product ID:	2CSG225945R1101
EAN:	8012542259459
Catalog Description:	CT MAX 300 Current transformer
Long Description:	CT MAX 300 is used to transform primary currents to $\approx 1/5$ A secondary currents for c.a. measurement instruments

Categories

Products » Low Voltage Products and Systems » Modular DIN Rail Products » Modular DIN Rail Components MDRCs » Modular Measuring Instruments

Ordering

Minimum Order Quantity:	1 piece
Customs Tariff Number:	90303100
EAN:	8012542259459

Dimensions

Product Net Height:	0.110 m
Product Net Depth:	0.045 m
Product Net Weight:	0.32 kg
Product Net Width:	0.070 m

Container Information

Package Level 1 Width:	0.093 m
Package Level 1 Height:	0.08 m
Package Level 1 Length:	0.143 m
Package Level 1 Gross Weight:	0.5 kg
Package Level 1 EAN:	8012542259459
Package Level 1 Units:	1 piece

Technical

Mounting Type:	Through primary
Cable Use:	Cable, Horizontal and Vertical bars
Cable Cross-Section:	30 mm
Rated Cross-Section:	40 x 10 mm
Rated Primary Current (I_{pn}):	300 A

Environmental

RoHS Status:	Following EU Directive 2002/95/EC August 18, 2005 and amendment
--------------	-----------------------------------------------------------------

Certificates and Declarations (Document Number)

Instructions and Manuals:	On the product's package
Data Sheet, Technical Information:	2CSC400002D0211
Declaration of Conformity - CE:	2CSC445003D2701
RoHS Information:	2CSC445004K2701

Classifications

ETIM 4:	EC002048 - Current transformer
ETIM 5:	EC002048 - Current transformer
Object Classification Code:	P

