


Surface Mount TRANSZORB® Transient Voltage Suppressors



FEATURES

- Very low profile - typical height of 0.95 mm
- Ideal for automated placement
- Uni-directional only
- Excellent clamping capability
- Peak pulse power:
 - 600 W (10/1000 μ s)
 - 4 kW (8/20 μ s)
- ESD capability: IEC 61000-4-2 level 4
 - 15 kV (air)
 - 8 kV (contact)
- Meets MSL level 1, per J-STD-020, LF maximum peak of 260 °C
- Material categorization: For definitions of compliance please see www.vishay.com/doc?99912



RoHS
COMPLIANT
HALOGEN
FREE

PRIMARY CHARACTERISTICS	
V_{BR}	6.4 V to 24.5 V
V_{WM}	5.0 V to 20 V
P_{PPM} (10 x 1000 μ s)	600 W
P_{PPM} (8 x 20 μ s)	4000 W
P_D at $T_M = 55$ °C	6 W
T_J max.	175 °C
Polarity	Uni-directional
Package	DO-221AC (SlimSMA)

MECHANICAL DATA

Case: DO-221AC (SlimSMA)

Molding compound meets UL 94 V-0 flammability rating
Base P/N-M3 - halogen-free, RoHS-compliant, and commercial grade

Terminals: Matte tin plated leads, solderable per J-STD-002 and JESD22-B102

M3 suffix meets JESD 201 class 2 whisker test

Polarity: Color band denotes cathode end

TYPICAL APPLICATIONS


Use in sensitive electronics protection against voltage transients induced by inductive load switching and lighting on ICs, MOSFET, signal lines of sensor units for consumer, computer, industrial, and telecommunication.

MAXIMUM RATINGS ($T_A = 25$ °C, unless otherwise noted)				
PARAMETER		SYMBOL	VALUE	UNIT
Peak pulse power dissipation	with a 10/1000 μ s waveform	P_{PPM} ⁽¹⁾	600	W
	with a 8/20 μ s waveform		4000	
Peak pulse current	with a 10/1000 μ s waveform	I_{PPM} ⁽¹⁾	See next table	A
	with a 8/20 μ s waveform			
Power dissipation	$T_M = 55$ °C	P_D ⁽²⁾	6	W
	$T_A = 25$ °C	P_D ⁽³⁾	1.0	
Storage temperature range		T_{STG}	-65 to +175	°C
Operating junction temperature range		T_J	-55 to +175	

Notes

- (1) Non-repetitive current pulse, per fig. 3 and derated above $T_A = 25$ °C per fig. 2.
- (2) Power dissipation mounted on infinite heatsink
- (3) Power dissipation mounted on minimum recommended pad layout

INDEX OF SYMBOLS	
SYMBOL	PARAMETER
V_{WM}	Stand-off voltage
V_{BR}	Breakdown voltage
V_C	Clamping voltage
I_D	Leakage current at V_{WM}
I_{PP}	Peak pulse current
αT	Voltage temperature coefficient
V_F	Forward voltage drop
R_D	Dynamic resistance



Zener Voltage Regulator

ELECTRICAL CHARACTERISTICS ($T_A = 25\text{ }^\circ\text{C}$ unless otherwise noted)															
DEVICE TYPE	DEVICE MARKING CODE	BREAKDOWN VOLTAGE V_{BR} AT I_T (1)			STAND-OFF VOLTAGE V_{WM}	MAXIMUM REVERSE LEAKAGE I_D AT V_{WM} (3)			V_C AT I_{PP}		R_D (2)	V_C AT I_{PP}		R_D (2)	αT (3)
		MIN.	MAX.			25 °C	85 °C		10/1000 μs			8/20 μs			
		V	mA	V	μA	V	V	A	Ω	V	A	Ω	MAX.		MAX.
SMA6F5.0A	6AE	6.40	7.07	10	5	150	375	5.0	9.2	68.0	0.031	13.4	298	0.021	5.7
SMA6F6.0A	6AG	6.70	7.41	10	6	600	1500	6.0	9.5	63.2	0.033	13.7	290	0.022	5.9
SMA6F6.5A	6AK	7.20	7.96	10	6.5	100	250	6.5	10.2	58.8	0.038	14.5	276	0.024	6.1
SMA6F7.5A	6AP	8.33	9.21	1	7.5	50	125	7.5	11.8	50.8	0.051	17.0	235	0.033	6.5
SMA6F8.0A	6AR	8.89	9.83	1	8.0	20	50	8.0	12.8	46.9	0.063	18.2	220	0.038	7.0
SMA6F8.5A	6AT	9.4	10.4	1	8.5	20	50	8.5	13.3	45.1	0.064	18.7	205	0.040	7.3
SMA6F10A	6AX	11.1	12.3	1	10	1.0	5.0	10	15.7	38.2	0.089	19.6	184	0.040	7.8
SMA6F11A	6AZ	12.2	13.5	1	11	1.0	5.0	11	17.2	34.8	0.107	21.5	172	0.047	8.1
SMA6F12A	6BE	13.3	14.7	1	12	0.2	1.0	12	18.8	31.9	0.128	23.5	157	0.056	8.3
SMA6F12AHD	6BF	13.2	14.3	1	12	0.2	1.0	12	18.5	32.4	0.130	22.9	157	0.055	8.4
SMA6F13A	6BG	14.4	15.9	1	13	0.2	1.0	13	20.4	29.4	0.153	23.9	147	0.064	8.4
SMA6F15A	6BM	16.7	18.5	1	15	0.2	1.0	15	23.6	25.4	0.201	27.7	123	0.075	8.8
SMA6F16A	6BP	17.8	19.7	1	16	0.2	1.0	16	25.2	23.8	0.229	29.5	119	0.082	8.8
SMA6F17A	6BR	18.9	20.9	1	17	0.2	1.0	17	26.7	22.5	0.259	31.4	111	0.095	9.0
SMA6F18A	6BT	20.0	22.1	1	18	0.2	1.0	18	28.3	21.2	0.292	33.2	102	0.109	9.2
SMA6F20A	6BV	22.2	24.5	1	20	0.2	1.0	20	31.4	19.1	0.361	36.8	93	0.132	9.4

Notes

- (1) Pulse test: $t_p \leq 50\text{ ms}$
- (2) To calculate maximum clamping voltage at other surge currents, use following formula: $V_{CL\text{ max.}} = R_D \times I_{PP} + V_{BR\text{ max.}}$
- (3) To calculate V_{BR} vs. junction temperature, use following formula: V_{BR} at $T_J = V_{BR}$ at $25\text{ }^\circ\text{C} \times (1 + \alpha T \times (T_J - 25))$

THERMAL CHARACTERISTICS ($T_A = 25\text{ }^\circ\text{C}$ unless otherwise noted)			
PARAMETER	SYMBOL	VALUE	UNIT
Typical thermal resistance, junction to ambient	$R_{\theta JA}$ (1)	150	$^\circ\text{C/W}$
Typical thermal resistance, junction to mount	$R_{\theta JM}$ (2)	20	$^\circ\text{C/W}$

Notes

- (1) Mounted on minimum recommended pad layout
- (2) Mounted on infinite heatsink



IMMUNITY TO STATIC ELECTRICAL DISCHARGE TO THE FOLLOWING STANDARDS					
(T _A = 25 °C unless otherwise noted)					
STANDARD	TEST TYPE	TEST CONDITIONS	SYMBOL	CLASS	VALUE
IEC 61000-4-2	Human body model (contact mode)	C = 150 pF, R = 330 Ω	V _C	4	> 8 kV
	Human body model (air discharge mode)				> 15 kV

ORDERING INFORMATION (Example)				
PREFERRED P/N	UNIT WEIGHT (g)	PREFERRED PACKAGE CODE	BASE QUANTITY	DELIVERY MODE
SMA6F5.0A-M3/6A	0.032	6A	3500	7" diameter plastic tape and reel
SMA6F5.0A-M3/6B	0.032	6B	14 000	13" diameter plastic tape and reel

RATINGS AND CHARACTERISTICS CURVES

(T_A = 25 °C unless otherwise noted)




Fig. 1 - Peak Pulse Power Rating Curve




Fig. 3 - Pulse Waveform




Fig. 2 - Pulse Power or Current vs. Initial Junction Temperature




Fig. 4 - Typical Junction Capacitance




Fig. 5 - Power Dissipation Derating Curve





Fig. 6 - Typical Transient Thermal Impedance

PACKAGE OUTLINE DIMENSIONS in inches (millimeters)

DO-221AC (SlimSMA)





Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and / or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Except as expressly indicated in writing, Vishay products are not designed for use in medical, life-saving, or life-sustaining applications or for any other application in which the failure of the Vishay product could result in personal injury or death. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.