

### General Information

Extended Product Type:	OS200J03
Product ID:	1SCA022733R6130
EAN:	6417019237435
Catalog Description:	OS200J03 Fusible disconnect switch
Long Description:	Including terminal bolt kit as standard. The handle and shaft have to be ordered separately.

### Categories

Products » Low Voltage Products and Systems » Switches » Switch Fuses

### Ordering

EAN:	6417019237435
Minimum Order Quantity:	1 piece
Customs Tariff Number:	85365080

### Dimensions

Product Net Width:	182 mm
Product Net Height:	218 mm
Product Net Depth:	132 mm
Product Net Weight:	3 kg

### Container Information

Package Level 1 Units:	1 piece
Package Level 1 Width:	210 mm
Package Level 1 Height:	163 mm
Package Level 1 Length:	236 mm
Package Level 1 Gross Weight:	3.08 kg
Package Level 1 EAN:	6417019237435

### Environmental

RoHS Status:	Planned to follow EU Directive 2002/95/EC August 18, 2005 and amendment after 2009 Q4
--------------	---

### Technical UL/CSA

Ampere Rating UL/CSA:	200 A
Horsepower Rating UL/CSA:	(acc. to UL 480 V) 125 Hp (acc. to UL 240 V) 60 Hp (acc. to UL 600 V) 150 Hp

### Additional Information

Conventional Free-air Thermal Current ( $I_{th}$ ):	$q = 40\text{ °C } 200\text{ A}$
Conventional Thermal Current ( $I_{the}$ ):	Fully Enclosed 200 A
Fuse Size:	200 A
Fuse System:	Class J
Fuse Type:	J
Handle Type:	Handle and shaft not included
IIT Publishing Status:	Level 0 - Information enabled
Includes:	None
Mounting Type:	Base Mounting
Number of Poles:	3
Operating Mode:	Front Operated
Pollution Degree:	3
Position of Line Terminals:	Top In - Bottom Out
Power Loss:	8 W
Product Main Type:	OS200
Product Name:	Fusible disconnect switch
Rated Impulse Withstand Voltage ( $U_{imp}$ ):	12 kV
Rated Insulation Voltage ( $U_i$ ):	1000 V
Rated Operational Current AC-23A ( $I_e$ ):	(500 V) 200 A (690 V) 200 A

<b>Rated Operational Power AC-23A (P<sub>e</sub>):</b>	(500 V) 132 kW (690 V) 200 kW (400 V) 110 kW (415 V) 110 kW (220 ... 240 V) 60 kW
<b>Rated Operational Voltage:</b>	690 V AC
<b>Rated Short-time Withstand Current (I<sub>cw</sub>):</b>	for 1 s 8 kiloampere rms
<b>Standards:</b>	UL
<b>Switches Operating Mechanism:</b>	Mechanism at the End of the Switch
<b>Terminal Type:</b>	Lug terminals

**Certificates and Declarations (Document Number)**

<b>Data Sheet, Technical Information:</b>	1SCC311013C0201
<b>Declaration of Conformity - CE:</b>	1SCC311096D0201

**Classifications**

<b>ETIM 5:</b>	EC001040 - Fuse switch disconnecter
<b>Object Classification Code:</b>	Q

