

General Information

Extended Product Type:	PSR12-600-11
Product ID:	1SFA896106R1100
EAN:	7320500477175
Catalog Description:	PSR12-600-11 SOFTSTARTER
Long Description:	Softstarter PSR12-600-11 for max 600V main voltage and 24V AC/DC control supply voltage

Categories

Products » Low Voltage Products and Systems » Control Products » Softstarters » Softstarters

Interactive Guides

Category Related Guides: [ABB improves mining industry efficiency - Softstarter PSTX](#)

Ordering

Minimum Order Quantity:	1 piece
Customs Tariff Number:	85371099
EAN:	7320500477175

Dimensions

Product Net Height:	140.000 mm
Product Net Depth:	114.000 mm
Product Net Weight:	0.4 kg
Product Net Width:	45.000 mm

Container Information

Package Level 1 Length:	156 mm
Package Level 1 Height:	124 mm
Package Level 1 Gross Weight:	0.55 kg
Package Level 1 EAN:	7320500477175
Package Level 1 Units:	1 piece
Package Level 2 Units:	1 piece
Package Level 1 Width:	51 mm

Technical

Rated Control Supply Voltage (U_s):	24 V AC/DC
Rated Control Circuit Voltage (U_c):	DC Operation 24 V
Rated Operational Power - In-Line Connection (P_e):	at 230 V 3 kW at 400 V 5.5 kW at 500 V 5.5 kW
Rated Operational Current - In-Line Connection (I_e):	12 A
Service Factor Percentage:	100 %
Overload Protection:	Recommended MS132 10.00 ... 16.00
Integrated Electronic Overload:	No
Starting Capacity at Maximum Rated Current I_e :	4x I_e for 6s
Ramp Time:	During Start 1 ... 10 second [unit of time] During Stop 0 ... 20 second [unit of time]
Initial Voltage During Start:	40 ... 70 %
Step Down Voltage Special Ramp:	100...60 %
Current Limit Function:	No
Switch for Inside Delta Connection:	No
Run Signal Relay:	Yes
By-pass Signal Relay:	No
Fault Signal Relay:	No
Overload Signal Relay:	No
Signal indication completed start ramp (LED):	Green
Signal indication ready to start/standby ON (LED):	Green
Signal indication running R (LED):	Green
Signal indication ramping up/down (LED):	Green

Number of Starts Per Hour at 3.5^{le} for 7 sec. 50% ON Time 50% OFF Time:	10
Communication:	FiledBusPlug(Optional)
Degree of Protection:	acc. to IEC 60529, IEC 60947-1, EN 60529 Main Terminals IP20
Terminal Type:	Screw Terminals
Connecting Capacity Main Circuit:	Rigid 1/2x0.75 ... 2.5 mm ²
Connecting Capacity Control Circuit:	Rigid 1/2x0.75 ... 2.5 mm ²
Connecting Capacity Supply Circuit:	Rigid 1/2x0.75 ... 2.5 mm ²
Tightening Torque:	Main Circuit 1 N·m Supply Circuit 1 N·m Control Circuit 1 N·m
Product Main Type:	PSR12
Rated Operational Voltage:	Main Circuit 208 ... 600 V AC

Environmental

Ambient Air Temperature:	Operation -25 ... +60 °C Storage -40 ... +70 °C
RoHS Status:	Following EU Directive 2002/95/EC August 18, 2005 and amendment

Certificates and Declarations (Document Number)

Instructions and Manuals:	1SFC132076M9901
Data Sheet, Technical Information:	1SFC132005C0201
Declaration of Conformity - CE:	2CMT004861
RoHS Information:	1SFC132031D0202

Classifications

ETIM 4:	EC002572 - Electronic motor control and protection device
ETIM 5:	EC002572 - Electronic motor control and protection device
UNSPSC:	39121521
Object Classification Code:	Q

