

### **General Information**

 Extended Product Type:
 AF26-40-00-12

 Product ID:
 1SBL237201R1200

 EAN:
 3471523115224

Catalog Description: AF26-40-00-12 48-130V50/60HZ-DC Contactor

**Long Description:** AF26 4-pole contactors are used for controlling power circuits up to 690 V AC and 440 V

DC. They are mainly used for controlling non-inductive or slightly inductive loads (i.e. resistance furnaces...). AF... contactors include an electronic coil interface accepting a wide control voltage Uc min. ... Uc max. Only four coils cover control voltages between 24...500 V 50/60 Hz or 20...500 V DC. AF contactors can manage large control voltage variations. One coil can be used for different control voltages used worldwide without any coil change. AF contactors have built-in surge protection and do not require additional surge suppressors. The AF... series 4-pole contactors are of the block type design. - Main poles and auxiliary contact blocks: 4 N.O. main poles, front and side-mounted add-on auxiliary contact blocks (mechanically-linked auxiliary contacts compliant with Annex L of IEC 60947-5-1. N.C. mirror contacts compliant with Annex F of IEC 60947-4-1) - Control circuit: AC or DC

operated - Accessories: a wide range of accessories is available.

# Categories

Products » Low Voltage Products and Systems » Control Products » Contactors » Block Contactors

#### Ordering

 Minimum Order Quantity:
 1 piece

 Customs Tariff Number:
 85369085

 EAN:
 3471523115224

#### **Dimensions**

Product Net Depth: 101 mm
Product Net Height: 86 mm
Product Net Weight: 0.360 kg
Product Net Width: 45 mm

#### **Container Information**

Package Level 1 Width: 87 mm Package Level 1 Length: 103 mm Package Level 1 Height: 47 mm Package Level 1 Gross Weight: 0.36 kg Package Level 1 EAN: 3471523115224 Package Level 2 Units: 36 piece 250 mm Package Level 2 Width: Package Level 2 Length: 300 mm Package Level 2 Height: 315 mm Package Level 3 Units: 864 piece Package Level 1 Units: 1 piece

### Technical

Number of Main Contacts NC: 0
Number of Auxiliary Contacts NO: 0
Number of Auxiliary Contacts NC: 0

Standards: IEC 60947-1 / 60947-4-1 and EN 60947-1 / 60947-4-1, UL 508, CSA C22.2 N°14

Rated Operational Voltage: Main Circuit 690 V
Rated Frequency (f): Main Circuit 50 / 60 Hz

**Conventional Free-air Thermal** acc. to IEC 60947-4-1, Open Contactors  $q = 40 \,^{\circ}\text{C}$  55 A

Current (I<sub>th</sub>):

Rated Operational Current AC-1 (Ie): (690 V) 40  $^{\circ}$ C 45 A

(690 V) 60 °C 40 A (690 V) 70 °C 32 A

Rated Operational Current AC-3 (Ie): (220 / 230 / 240 V) 60 °C 23.2 A

(380 / 400 V) 60 °C 22 A (415 V) 60 °C 21.2 A (440 V) 60 °C 20 A (500 V) 60 °C 17.6 A (690 V) 60 °C 10.5 A

Rated Operational Power AC-3 (Pe): (220 / 230 / 240 V) 5.5 kW

(400 V) 11 kW

(415 V) 11 kW (440 V) 11 kW (500 V) 11 kW (690 V) 9 kW

Rated Short-time Withstand Current at 40 °C Ambient Temp, in Free Air, from a Cold State 10 s 300 A

 $(I_{cw})$ :

at 40 °C Ambient Temp, in Free Air, from a Cold State 15 min 55 A at 40 °C Ambient Temp, in Free Air, from a Cold State 1 min 150 A at 40 °C Ambient Temp, in Free Air, from a Cold State 1 s 450 A at 40 °C Ambient Temp, in Free Air, from a Cold State 30 s 225 A

**Maximum Electrical Switching** 

Frequency:

AC-1 600 cycles per hour

Rated Insulation Voltage (Ui): acc. to UL/CSA 600 V

acc. to IEC 60947-4-1 and VDE 0110 (Gr. C) 690 V

Rated Impulse Withstand Voltage

(U<sub>imp</sub>):

**Maximum Mechanical Switching** 

Frequency:

3600 cycles per hour

Rated Control Circuit Voltage (U<sub>c</sub>):

50 Hz 48 ... 130 V 60 Hz 48 ... 130 V DC Operation 48 ... 130 V

**Operate Time:** Between Coil De-energization and NC Contact Closing 13...98 ms

Between Coil De-energization and NO Contact Opening 11...95 ms Between Coil Energization and NC Contact Opening 38...90 ms Between Coil Energization and NO Contact Closing 40...95 ms

Flexible with Insulated Ferrule 1x 1.5...16 mm<sup>2</sup> **Connecting Capacity Main Circuit:** 

Flexible with Insulated Ferrule 2x 1.5...16 mm<sup>2</sup>

Flexible with Ferrule 1/2x 1.5...16 mm<sup>2</sup>

Rigid 1/2x 1.5...16 mm<sup>2</sup>

Connecting Capacity Control Circuit: Flexible with Ferrule 1/2x 0.75 ... 2.5 mm<sup>2</sup>

Flexible with Insulated Ferrule 1x 0.75 ... 2.5 mm<sup>2</sup> Flexible with Insulated Ferrule 2x 0.75 ... 1.5 mm<sup>2</sup>

Rigid 1/2x 1 ... 2.5 mm<sup>2</sup>

Wire Stripping Length: Control Circuit 10 mm

Main Circuit 12 mm

Degree of Protection: acc. to IEC 60529, IEC 60947-1, EN 60529 Coil Terminals IP20

acc. to IEC 60529, IEC 60947-1, EN 60529 Main Terminals IP20

**Terminal Type:** Screw Terminals

**Number of Main Contacts NO:** 

**Environmental** 

Climatic Withstand: Category B according to IEC 60947-1 Annex Q

**Maximum Operating Altitude** 

Permissible:

3000 m

Resistance to Vibrations acc. to IEC 5 ... 300 Hz 4 g closed position / 2 g open position

60068-2-6:

Resistance to Shock acc. to IEC

60068-2-27:

Closed, Shock Direction: B1 25 g Open, Shock Direction: B1 5 g Shock Direction: A 30 g Shock Direction: B2 15 g Shock Direction: C1 25 g Shock Direction: C2 25 g

**RoHS Status:** Following EU Directive 2011/65/EC

Close to Contactor for Storage -60...+80 °C **Ambient Air Temperature:** 

Near Contactor for Operation in Free Air -40 ... +70 °C

**Technical UL/CSA** 

General Use Rating UL/CSA: (600 V AC) 45 A Tightening Torque UL/CSA: Control Circuit 11 in·lb

Main Circuit 22 in·lb

Certificates and Declarations (Document Number)

Instructions and Manuals: 1SBC101027M6801

**ABS Certificate:** ABS 15-GE1349500-PDA 90682247

**CB Certificate:** CB\_SE\_70858M1 **CCC Certificate:** CCC\_2010010304445623 Data Sheet, Technical Information: 1SBC101423D0201 **Declaration of Conformity - CE:** 1SBD250001U1000 **DNV Certificate:** DNV-GL\_E13871

**EAC Certificate:** EAC RU C-FR ME77 B01010

**GL Certificate:** DNV-GL E13871

**GOST Certificate:** GOST POCCFR.ME77.B07175.pdf 

 LR Certificate:
 LRS\_1300087E1

 RINA Certificate:
 RINA\_ELE084013XG

 RMRS Certificate:
 RMRS\_1400682124

 RoHS Information:
 1SBD251015E1001

 UL Certificate:
 UL\_20120918-E319322-3-1

 UL Listing Card:
 UL\_E319322

# Classifications

E-nummer:	3211510
ETIM 4:	EC000066 - Magnet contactor, AC-switching
ETIM 5:	EC000066 - Magnet contactor, AC-switching
ETIM 6:	EC000066 - Power contactor, AC switching
UNSPSC:	39121529
Object Classification Code:	Q

