

General Information

Extended Product Type:	M2M LV MODBUS
Product ID:	2CSG296992R4052
EAN:	8012542969921
Catalog Description:	M2M LV MODBUS Network analyser
Long Description:	M2M is a network analyser with 2 digital outputs, aux supply 24- 230 V a.c./d.c., embedded RS485

Categories

Products » Low Voltage Products and Systems » Modular DIN Rail Products » Modular DIN Rail Components MDRCs » Modular Measuring Instruments

Ordering

Minimum Order Quantity:	1 piece
Customs Tariff Number:	90303100
EAN:	8012542969921

Dimensions

Product Net Height:	0.096 m
Product Net Depth:	0.060 m
Product Net Weight:	0.350 kg
Product Net Width:	0.096 m

Container Information

Package Level 1 Width:	0.11 m
Package Level 1 Height:	0.23 m
Package Level 1 Length:	0.155 m
Package Level 1 Gross Weight:	0.5 kg
Package Level 1 EAN:	8012542969921
Package Level 1 Units:	1 piece

Technical

Meter Type:	Digital
Mounting Type:	Front-panel
Dimensions:	96 mm x 96 mm
Rated Operational Voltage:	10 ... 500 V AC
Options Provided:	Total harmonic distortion (THD)
I/O Option:	2 digital output
Power Loss:	at Rated Operating Conditions per Pole 7 W

Environmental

Ambient Air Temperature:	Operation -5 ... +5 °C
RoHS Status:	Following EU Directive 2002/95/EC August 18, 2005 and amendment

Certificates and Declarations (Document Number)

Instructions and Manuals:	2CSG445010D1001
Data Sheet, Technical Information:	2CSC400002D0209
Declaration of Conformity - CE:	ITSCE188M2M
RoHS Information:	2CSC445023K2703

Classifications

ETIM 4:	EC001194 - Power quality analyzer
ETIM 5:	EC001194 - Power quality analyzer
Object Classification Code:	P

