

General Information

| | |
|------------------------|--|
| Extended Product Type: | S201M-D50 |
| Product ID: | 2CDS271001R0501 |
| EAN: | 4016779599702 |
| Catalog Description: | Miniature Circuit Breaker - S200M - 1P - D - 50 A |
| Long Description: | System pro M compact S200M miniature circuit breakers are current limiting. They have two different tripping mechanisms, the delayed thermal tripping mechanism for overload protection and the electromechanic tripping mechanism for short circuit protection. They are available in different characteristics (B, C, D, K, Z), configurations (1P, 1P+N, 2P, 3P, 3P+N, 4P), breaking capacities (up to 10 kA at 230/400 V AC) and rated currents (up to 63A). All MCBs of the product range S200M comply with IEC/EN 60898-1 and IEC/EN 609 47-2, allowing the use for residential, commercial and industrial applications. Bottom-fitting auxiliary contact can be mounted on S200M to save 50% space. |

Categories

Products » Low Voltage Products and Systems » Modular DIN Rail Products » Miniature Circuit Breakers MCBs

Ordering

| | |
|-------------------------|---------------|
| Minimum Order Quantity: | 1 piece |
| Customs Tariff Number: | 85362010 |
| EAN: | 4016779599702 |

Dimensions

| | |
|---------------------|----------|
| Product Net Depth: | 69 mm |
| Product Net Height: | 88 mm |
| Product Net Weight: | 0.125 kg |
| Product Net Width: | 17.5 mm |

Container Information

| | |
|-------------------------------|---------------|
| Package Level 1 Width: | 92 mm |
| Package Level 1 Length: | 183 mm |
| Package Level 1 Height: | 80 mm |
| Package Level 1 Gross Weight: | 1.295 kg |
| Package Level 1 EAN: | 4016779602563 |
| Package Level 2 Units: | 120 piece |
| Package Level 2 Width: | 275 mm |
| Package Level 2 Length: | 395 mm |
| Package Level 2 Height: | 210 mm |
| Package Level 2 Gross Weight: | 11.92 kg |
| Package Level 2 EAN: | 4016779975988 |
| Package Level 1 Units: | 10 piece |

Environmental

| | |
|---|---|
| Ambient Air Temperature: | Operation -25 ... +55 °C Storage -40 ... +70 °C |
| Resistance to Shock acc. to IEC 60068-2-27: | 25g / 2 shocks / 13 ms |
| Resistance to Vibrations acc. to IEC 60068-2-6: | 5g, 20 cycles at 5 ... 150 ... 5 Hz with load 0.8 In |
| Environmental Conditions: | 28 cycles with 55 °C / 90-96 % and 25 °C / 95-100 % |
| RoHS Status: | Following EU Directive 2002/95/EC August 18, 2005 and amendment |

Technical

| | |
|---|--|
| Number of Poles: | 1 |
| Tripping Characteristic: | D |
| Rated Current (I _n): | 50 A |
| Rated Operational Voltage: | acc. to IEC 60898-1 230 / 400 V AC acc. to IEC 60947-2 230 V AC |
| Power Loss: | 2.9 W at Rated Operating Conditions per Pole 2.9 W |
| Rated Insulation Voltage (U _i): | acc. to IEC/EN 60664-1 440 V |
| Operational Voltage: | Maximum (Incl. Tolerance) 253 V AC |

Maximum (Incl. Tolerance) 72 V DC
Minimum 12 V AC / 12 V DC

| | |
|---|--|
| Rated Frequency (f): | 50 Hz 60 Hz |
| Rated Short-Circuit Capacity (I_{cn}): | (230 / 400 V AC) 10 kA |
| Rated Ultimate Short-Circuit Breaking Capacity (I_{cu}): | (133 V AC) 25 kA |
| Rated Service Short-Circuit Breaking Capacity (I_{cs}): | (133 V AC) 18.8 kA |
| Energy Limiting Class: | 3 |
| Overvoltage Category: | III |
| Pollution Degree: | 3 |
| Rated Impulse Withstand Voltage (U_{imp}): | 4 kV (6.2 kV @ sea level) (5.0 kV @ 2000 m) |
| Dielectric Test Voltage: | 50 / 60 Hz, 1 min: 2 kV |
| Housing Material: | Insulation Group II, RAL 7035 |
| Actuator Type: | Insulation group II, black, sealable |
| Contact Position Indication: | Red ON / Green OFF |
| Degree of Protection: | IP20 |
| Remarks: | IP40 in enclosure with cover |
| Electrical Endurance: | 10000 AC cycle |
| Mechanical Endurance: | 20000 cycle |
| Terminal Type: | Screw Terminals |
| Screw Terminal Type: | Failsafe Bi-directional Cylinder-lift Terminal |
| Connecting Capacity: | Busbar 10 / 10 mm ² Flexible with Ferrule 0.75 ... 25 mm ² Flexible 0.75 ... 25 mm ² Rigid 0.75 ... 35 mm ² Stranded 0.75 ... 35 mm ² |
| Tightening Torque: | 2 N·m |
| Recommended Screw Driver: | Pozidriv 2 |
| Mounting on DIN Rail: | TH35-7.5 (35 x 7.5 mm Mounting Rail) acc. to IEC 60715 TH35-15 (35 x 15 mm Mounting Rail) acc. to IEC 60715 |
| Mounting Position: | Any |
| Standards: | IEC/EN 60898-1 IEC/EN 60947-2 |

Technical UL/CSA

| | |
|--|---------------------------------------|
| Connecting Capacity UL/CSA: | Busbar 14-8 AWG Conductor 14-4 AWG |
| Tightening Torque UL/CSA: | 18 in·lb |
| Interrupting Rating acc. to UL1077: | 6 kA (DC) 10 kA |
| Maximum Operating Voltage UL/CSA: | 480Y / 277 V AC |

Certificates and Declarations (Document Number)

| | |
|---|-----------------|
| Instructions and Manuals: | 2CSC400002D0208 |
| Data Sheet, Technical Information: | 2CSC400002D0208 |
| Declaration of Conformity - CE: | 2CDK403001D0604 |
| RoHS Information: | 2CDK400003K0201 |

Classifications

| | |
|------------------------------------|--|
| ETIM 4: | EC000042 - Miniature circuit breaker (MCB) |
| ETIM 5: | EC000042 - Miniature circuit breaker (MCB) |
| ETIM 6: | EC000042 - Miniature circuit breaker (MCB) |
| eClass: | 7.0 27141901 |
| UNSPSC: | 39121614 |
| Object Classification Code: | F |

Accessories [Show accessory images](#)

| 32 Products | | Filter | <input type="text"/> |
|-----------------|---|-----------|----------------------|
| Identifier | Description | Type | Qty Unit Of Measure |
| 2CCA880100R0001 | Strom-Messsystem Sensor CMS-100PS 80A, 18mm für pro M compact u. SMISLINE | CMS-100PS | 1 piece |
| | Strom-Messsystem Sensor CMS-101PS 40A, 18mm für pro M compact u. | | |

| Identifier | Description | Type | Qty | Measure |
|-----------------|--|---------------|-----|---------|
| 2CCA880101R0001 | SMISLINE | CMS-101PS | 1 | piece |
| 2CCA880102R0001 | Strom-Messsystem Sensor CMS-102PS 20A, 18mm für pro M compact u. | CMS-102PS | 1 | piece |
| 2CDS200909R0001 | S2C-A1 - Arbeitsstromauslöser | S2C-A1 | 1 | piece |
| 2CDS200909R0002 | S2C-A2 - Arbeitsstromauslöser | S2C-A2 | 1 | piece |
| 2CDS200912R0001 | S2C-H6R - Hilfskontakt | S2C-H6R | 1 | piece |
| 2CDS200918R0001 | S2C-NT - Manueller Neutralleiter | S2C-NT | 1 | piece |
| 2CDS200922R0001 | S2C-S/H6R - Signal- / Hilfskontakt | S2C-S/H6R | 1 | piece |
| 2CDS200936R0001 | S2C-H11L - Hilfskontakt | S2C-H11L | 1 | piece |
| 2CDS200936R0002 | S2C-H20L - Hilfskontakt | S2C-H20L | 1 | piece |
| 2CDS200936R0003 | S2C-H02L - Hilfskontakt | S2C-H02L | 1 | piece |
| 2CDS200946R0001 | S2C-H6-11R - Hilfskontakt | S2C-H6-11R | 1 | piece |
| 2CDS200946R0002 | S2C-H6-20R - Hilfskontakt | S2C-H6-20R | 1 | piece |
| 2CDS200946R0003 | S2C-H6-02R - Hilfskontakt | S2C-H6-02R | 1 | piece |
| 2CDS200970R0001 | S2C-H01 - Hilfskontakt | S2C-H01 | 1 | piece |
| 2CDS200970R0002 | S2C-H10 - Hilfskontakt | S2C-H10 | 1 | piece |
| 2CSS200911R0001 | S2C-UA 12 DC - Unterspannungsauslöser | S2C-UA 12 DC | 1 | piece |
| 2CSS200911R0002 | S2C-UA 24 AC - Unterspannungsauslöser | S2C-UA 24 AC | 1 | piece |
| 2CSS200911R0003 | S2C-UA 48 AC - Unterspannungsauslöser | S2C-UA 48 AC | 1 | piece |
| 2CSS200911R0004 | S2C-UA 110 AC - Unterspannungsauslöser | S2C-UA 110 AC | 1 | piece |
| 2CSS200911R0005 | S2C-UA 230 AC - Unterspannungsauslöser | S2C-UA 230 AC | 1 | piece |
| 2CSS200911R0006 | S2C-UA 400 AC - Unterspannungsauslöser | S2C-UA 400 AC | 1 | piece |
| 2CSS200911R0007 | S2C-UA 24 DC - Unterspannungsauslöser | S2C-UA 24 DC | 1 | piece |
| 2CSS200911R0008 | S2C-UA 48 DC - Unterspannungsauslöser | S2C-UA 48 DC | 1 | piece |
| 2CSS200911R0009 | S2C-UA 110 DC - Unterspannungsauslöser | S2C-UA 110 DC | 1 | piece |
| 2CSS200911R0010 | S2C-UA 230 DC - Unterspannungsauslöser | S2C-UA 230 DC | 1 | piece |
| 2CSS200998R0001 | S2C-BP - Mechanical tripping device | S2C-BP | 1 | piece |
| 2CSS200999R0001 | S2C-EST - Stecksocket | S2C-EST | 1 | piece |
| 2CSS201997R0013 | S2C-CM1 - Motorantrieb | S2C-CM1 | 1 | piece |
| 2CSS203997R0013 | S2C-CM2/3 - Motorantrieb | S2C-CM2/3 | 1 | piece |
| 2CSS204997R0013 | S2C-CM4 - Motorantrieb | S2C-CM4 | 1 | piece |
| GHS2001901R0003 | S2C-DH - Mechanical Accessories | S2C-DH | 1 | piece |

