


HALOGEN

FREE

GREEN

High Intensity LED in Ø 3 mm Tinted Diffused Package



DESCRIPTION

This series has been designed to meet the increasing demand for AllnGaP technology.

wide viewing angle of these devices provides a high brightness across a large field of view.

All packing units are categorized in luminous intensity and color groups. That allows users to assemble LEDs with uniform appearance.

PRODUCT GROUP AND PACKAGE DATA

• Product group: LED · Package: 3 mm

· Product series: standard • Angle of half intensity: ± 30°

FEATURES

- AllnGaP technology
- Standard Ø 3 mm (T-1) package
- · Small mechanical tolerances
- · Suitable for DC and high peak current
- · Wide viewing angle
- · Very high intensity
- · Luminous intensity and color categorized
- ESD-withstand voltage: up to 2 kV HBM according to JESD22-A114-B
- · Material categorization: for definitions of compliance please see www.vishav.com/doc?99912

APPLICATIONS

- Status lights
- · Off / on indicator
- · Background illumination
- · Readout lights
- Maintenance lights
- · Legend light

It is housed in a 3 mm tinted, diffused plastic package. The

PARTS TABLE														
PART COLOR		LUMINOUS INTENSITY (mcd)		at I _F	WA	WAVELENGTH (nm)		at I _F	FORWARD VOLTAGE (V)		at I _F (mA)	TECHNOLOGY		
		MIN.	TYP.	MAX.	(mA)	MIN.	TYP.	MAX.	(mA)	MIN.	TYP.	MAX.	(IIIA)	
TLHF4400	Soft orange	40	-	-	10	598	-	611	10	-	1.9	2.6	20	AllnGaP on GaAs
TLHF4401	Soft orange	100	200	360	10	602	605	609	10	-	1.9	2.6	20	AllnGaP on GaAs

ABSOLUTE MAXIMUM RATINGS ($T_{amb} = 25$ °C, unless otherwise specified) TLHF440.						
PARAMETER	TEST CONDITION	SYMBOL	VALUE	UNIT		
Reverse voltage		V_{R}	5	V		
DC forward current	T _{amb} ≤ 60 °C	I _F	30	mA		
Surge forward current	t _p ≤ 10 μs	I _{FSM}	0.1	А		
Power dissipation	T _{amb} ≤ 60 °C	P _V	80	mW		
Junction temperature		Tj	100	°C		
Operating temperature range		T _{amb}	-40 to +100	°C		
Storage temperature range		T _{stg}	-55 to +100	°C		
Soldering temperature	t ≤ 5 s, 2 mm from body	T _{sd}	260	°C		
Thermal resistance junction/ambient		R _{thJA}	400	K/W		



OPTICAL AND ELECTRICAL CHARACTERISTICS ($T_{amb} = 25$ °C, unless otherwise specified) TLHF440., SOFT ORANGE							
PARAMETER	TEST CONDITION	PARTS	SYMBOL	MIN.	TYP.	MAX.	UNIT
Luminous intensity (1)	I _E = 10 mA	TLHF4400	I _V	40	-	-	mcd
Luminous intensity (*)	IF = 10 IIIA	TLHF4401	I _V	100	200	360	mcd
Dominant wavelength	I _F = 10 mA	TLHF4400	λ_{d}	598	-	611	nm
Dominant wavelength		TLHF4401	λ_{d}	602	605	609	nm
Peak wavelength	I _F = 10 mA		λ_{p}	-	610	-	nm
Angle of half intensity	I _F = 10 mA		φ	-	± 30	-	deg
Forward voltage	I _F = 20 mA		V _F	-	1.9	2.6	V
Reverse voltage	I _R = 10 μA		V_R	5	-	-	V
Junction capacitance	V _R = 0 V, f = 1 MHz		Cj	-	15	-	pF

Note

⁽¹⁾ In one packing unit $I_{Vmin.}/I_{Vmax.} \le 0.5$.

LUMINOUS INTENSITY CLASSIFICATION							
GROUP	GROUP LIGHT INTENSITY (mcd)						
STANDARD	MIN.	MAX.					
U	40	80					
V	63	125					
W	100	200					
Х	130	260					
Y	180	360					

Note

Luminous intensity is tested at a current pulse duration of 25 ms.
The above type numbers represent the order groups which
include only a few brightness groups. Only one group will be
shipped on each bag (there will be no mixing of two groups on
each bag).

In order to ensure availability, single brightness groups will not be orderable.

In a similar manner for colors where wavelength groups are measured and binned, single wavelength groups will be shipped on any one bag.

In order to ensure availability, single wavelength groups will not be orderable.

COLOR CLASSIFICATION						
	SOFT ORANGE DOM. WAVELENGTH (nm)					
GROUP						
	MIN.	MAX.				
1	598	601				
2	600	603				
3	602	605				
4	604	607				
5	606	609				
6	608	611				

Note

Wavelengths are tested at a current pulse duration of 25 ms.

TYPICAL CHARACTERISTICS (T_{amb} = 25 °C, unless otherwise specified)




Fig. 1 - Forward Current vs. Ambient Temperature




Fig. 2 - Relative Luminous Intensity vs. Angular Displacement






Fig. 3 - Forward Current vs. Forward Voltage




Fig. 4 - Relative Luminous Intensity vs. Ambient Temperature




Fig. 5 - Relative Luminous Intensity vs. Forward Current







Fig. 6 - Relative Intensity vs. Wavelength



PACKAGE DIMENSIONS in millimeters







technical drawings according to DIN specifications

Drawing-No.: 6.544-5255.01-4

Issue: 9; 28.07.14



Legal Disclaimer Notice

Vishay

Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and / or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Except as expressly indicated in writing, Vishay products are not designed for use in medical, life-saving, or life-sustaining applications or for any other application in which the failure of the Vishay product could result in personal injury or death. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.

Revision: 13-Jun-16 1 Document Number: 91000