

## General Information

Extended Product Type:	416T6
Product ID:	2CMA168124R1000
EAN:	7392696681247
Catalog Description:	Three way adaptor, 6h, 16A, IP44, 3P+N+E
Long Description:	Three way adaptor, earthing sleeve position 6h, rated current 16A, IP44 splashproof, 3-poles+neutral+earth, frequency 50-60 Hz, color code Red

## Categories

Products » Low Voltage Products and Systems » Industrial Plugs and Sockets » Adaptors

## Ordering

EAN:	7392696681247
Minimum Order Quantity:	1 piece
Country of Origin:	Czech Republic (CZ)

## Dimensions

Product Net Width:	205 mm
Product Net Height:	85 mm
Product Net Length:	192 mm
Product Net Depth:	85 mm
Product Net Weight:	0.89 kg

## Container Information

Package Level 1 Width:	205 mm
Package Level 1 Length:	192 mm
Package Level 1 Height:	85 mm
Package Level 1 Gross Weight:	0.89 kg
Package Level 1 EAN:	7392696681247
Package Level 1 Units:	1 piece

## Environmental

RoHS Status:	Planned to follow EU Directive 2002/95/EC August 18, 2005 and amendment after 2006-03-01
--------------	--

## Certificates and Declarations (Document Number)

Declaration of Conformity - CE:	2CMC700005D0001
Environmental Information:	2CMC700001D0002
RoHS Information:	2CMC700057D0001

## Additional Information

Additional Information:	The adaptor unit has one inlet and three socket-outlets
Color:	Red
Degree of Protection:	IP44
Enclosure Material:	Thermoplastic
Frequency (f):	50 Hz
Function:	Three way adaptor IEC to IEC
IIT Publishing Status:	Level 0 - Information enabled
Invoice Description:	Ind. P&S#416T6
Number of Poles:	4
Object Classification Code:	2CMT005069
Product Main Type:	Adaptor
Product Name:	Industrial Adaptor
Protection Type:	Splashproof
Rated Current (I <sub>n</sub> ):	16 A
Rated Voltage (U <sub>r</sub> ):	346 $\blacklozenge$ 415 V 346 ... 415 V
RoHS Date:	L23
Standards:	IEC 60309-1,-2
Suitable For:	416T6
Suitable for Product Class:	Industrial Plugs and Sockets

## Classifications

---

E-nummer: 2417444

UNSPSC: 39120000

---

