

## TCXO / VC-TCXO ULTRA HIGH STABILITY

### TG5032CAN TG5032SAN

•Frequency range : 10 MHz to 50 MHz •Supply voltage : 3.3 V Typ. / 5.0V Typ. •Frequency / temperature characteristics

: ±0.1× 10<sup>-6</sup> Max. \*1

Frequency aging : ±0.02× 10<sup>-6</sup> Max./24 hours <sup>-2</sup>
 External dimensions: 5.0 × 3.2 × 1.45 mm (10 pads)
 Applications : FemtoCell, Small Cells
 Features : Ultra high stability





Product Number (please contact us) TG5032CAN :X1G004431xxxx00 TG5032SAN :X1G004441xxxx00





Actual size

### Specifications (characteristics)

Item	Symbol	TG5032CAN (CMOS output) TG5032SAN(Clipped sine wave)				
		VC-TCXO	TCXO	VC-TCXO	TCXO	Conditions / Remarks
		10 MHz to 50 MHz				
Output frequency range	fo	19.2, 26, 30.72, 40 MHz			Standard frequency	
Supply voltage	V <sub>CC</sub>	C: 3.3 V ±5%, H: 5.0 V ±5% (Supply voltage range :2.7 V to 5.5 V)				
Storage temperature	T_stg	-40 °C to +90 °C				Storage as single product
Operating temperature	T use	A: 0 °C to +70 °C			Standard temp. range	
Frequency tolerance	f tol	±2.0 × 10 <sup>-6</sup> Max.			After reflow, +25 °C	
Frequency/temperature Characteristics *1	fo-Tc	A: ±0.1 ×10 <sup>-6</sup> Max. / A: 0 to +70 °C (standard spec.)			C: 0 to +85 °C or L: -10 to +70 °C : Option1 or 2 (Temperature range)	
		H: ±0.25 ×10 <sup>-6</sup> Max. / G: -40 to +85 °C				Option3
		±0.08 ×10 <sup>-6</sup> Max. / +50 to +70 °C, ±0.1 ×10 <sup>-6</sup> Max. / +15 to +85 °C				Option4
		and ±0.25 ×10 <sup>6</sup> Max. / -5 to +85 °C				(Please contact us about suffix)
		±0.08 ×10 <sup>-6</sup> Max. / +40 to +60 °C, ±0.1 ×10 <sup>-6</sup> Max. / 0 to +70 °C			Option5	
		and ±0.25 ×10 <sup>-6</sup> Max. / -20 to +70 °C				(Please contact us about suffix)
Frequency/load coefficient	fo-Load	±0.1 ×10 <sup>-6</sup> Max. (10 MHz≦fo≦40 MHz)				Load ±10 %
		±0.2 ×10 <sup>-6</sup> Max. (40 MHz <fo≦50 mhz)<="" td=""></fo≦50>				
Frequency/voltage coefficient	fo-Vcc	±0.1 ×10 <sup>-6</sup> Max. (10 MHz≦fo≦40 MHz)				Vcc ±5%
		±0.2 ×10 <sup>-6</sup> Max. (40 MHz <fo≦50 mhz)<="" td=""></fo≦50>				
Frequency aging *2	f_age	±0.02 ×10 <sup>-6</sup> Max.				+25 °C, 24h
requestoy aging 2					+25 °C, First year	
Current consumption	Icc	5.0 mA Max. / 6.0 mA Max.			10 MHz≦fo≦26 MHz (3.3V / 5.0V)	
		6.0 mA Max. / 8.0 mA Max.		5.0 mA Max.		26 MHz < fo ≤ 40 MHz (3.3V / 5.0V)
				40 MHz < f0 ≤ 50 MHz (3.3V / 5.0V)		
Input resistance	Rin	100 kΩ Min.		100 kΩ Min.		Vc- GND (DC)
Frequency control range	f_cont	±5 ×10 <sup>-6</sup> to	_	±5 ×10 <sup>-6</sup> to	_	J,D :Vc=1.5 V $\pm$ 1.0 V at V <sub>cc</sub> =3.3 V
		±10 ×10 <sup>-6</sup>		±10 ×10 <sup>-6</sup>		K,E: $Vc=1.65 V \pm 1.0 V \text{ at } V_{cc}=3.3 V$
For any or the same and a street						L,H: Vc=2.5 V ± 2.0 V at V <sub>cc</sub> =5.0 V
Frequency change polarity		Positive polarity		Positive polarity		01101 1 (00 1)
Symmetry	SYM	45 % to 55 %		<del>_</del>		GND level (DC cut)
Output voltage	Voн	90 % Vcc Min.		<del>_</del>		
-	Vol	10 % Vcc Max.		0.8 V Min.		De aluta De alu
Output level	VPP	- 2.0 and May (Filters Storedard) /				Peak to Peak
Start-up time	t_str	2.0 sec. Max.(Filter: Standard) /		5.0 ms Max.(Non-Filter: Option)		T=0 at 90% Vcc
Output load condition	Load	15 pF		10 K22//10 pF		

\* Note: Please contact us for requirements not listed in this specification. \*1 Based on frequency at (fmax+fmin)/2. \*2 After 48 hours operating

Product Name (Standard form)

TG5032 C AN 19.200000MHz C A A N D A ① ② ③ ④ ⑥ ⑥ ⑦ ⑧ ⑨ 

 ® Vc function (symbol table)

 Vc [V]
 Non
 1.5
 1.65
 2.5
 Any

 Filter ON
 G
 J
 K
 L
 F


 Non Filter
 N
 D
 E
 H
 A


①Model ②Output (C: CMOS, S: Clipped sine wave)

③Frequency ④Supply voltage (C: 3.3 V Typ.)

⑤Frequency / temperature characteristics (A: ±0.1 × 10<sup>-6</sup> Max.) ⑥Operating temperature (A: 0 °C to +70 °C) ⑦OE function (N: Non) ⑥Vc function(Refer to symbol table) ⑥Internal identification code ("A" is default)

# External dimensions





## PROMOTION OF ENVIRONMENTAL MANAGEMENT SYSTEM CONFORMING TO INTERNATIONAL STANDARDS

At Seiko Epson, all environmental initiatives operate under the Plan-Do-Check-Action (PDCA) cycle designed to achieve continuous improvements. The environmental management system (EMS) operates under the ISO 14001 environmental management standard.

All of our major manufacturing and non-manufacturing sites, in Japan and overseas, completed the acquisition of ISO 14001 certification.

ISO 14000 is an international standard for environmental management that was established by the International Standards Organization in 1996 against the background of growing concern regarding global warming, destruction of the ozone layer, and global deforestation.

#### **WORKING FOR HIGH QUALITY**

In order provide high quality and reliable products and services than meet customer needs.

Seiko Epson made early efforts towards obtaining ISO9000 series certification and has acquired ISO9001 for all business establishments in Japan and abroad. We have also acquired ISO/TS 16949 certification that is requested strongly by major automotive manufacturers as standard.

ISO/TS16949 is the international standard that added the sector-specific supplemental requirements for automotive industry based on ISO9001.

#### Explanation of the mark that are using it for the catalog



►Pb free.



- ► Complies with EU RoHS directive.
  - \*About the products without the Pb-free mark.

    Contains Pb in products exempted by EU RoHS directive.

    (Contains Pb in sealing glass, high melting temperature type solder or other.)



▶ Designed for automotive applications such as Car Multimedia, Body Electronics, Remote Keyless Entry etc.



lacktriangle Designed for automotive applications related to driving safety (Engine Control Unit, Air Bag, ESC etc ).

### **Notice**

- This material is subject to change without notice.
- Any part of this material may not be reproduced or duplicated in any form or any means without the written permission of Seiko Epson.
- The information about applied data, circuitry, software, usage, etc. written in this material is intended for reference only. Seiko Epson
  does not assume any liability for the occurrence of customer damage or infringing on any patent or copyright of a third party. This
  material does not authorize the licensing for any patent or intellectual copyrights.
- When exporting the products or technology described in this material, you should comply with the applicable export control laws and regulations and follow the procedures required by such laws and regulations.
- You are requested not to use the products (and any technical information furnished, if any) for the development and/or manufacture of weapon of mass destruction or for other military purposes. You are also requested that you would not make the products available to any third party who may use the products for such prohibited purposes.
- These products are intended for general use in electronic equipment. When using them in specific applications that require extremely high reliability, such as the applications stated below, you must obtain permission from Seiko Epson in advance.
  - / Space equipment (artificial satellites, rockets, etc.) / Transportation vehicles and related (automobiles, aircraft, trains, vessels, etc.) / Medical instruments to sustain life / Submarine transmitters / Power stations and related / Fire work equipment and security equipment / traffic control equipment / and others requiring equivalent reliability.
- All brands or product names mentioned herein are trademarks and/or registered trademarks of their respective.