

Product availability : Stock - Normally stocked in distribution facility



Price* : 669.00 USD



Main

Range of product	125 A Frame EDB-EGB-EJB
Product or component type	Miniature circuit-breaker
Device short name	EDB
Module type	E-Frame
Trip unit rating	1800 A

Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 1423 - Schneider Electric declaration of conformity Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold
Product environmental profile	Available
Product end of life instructions	Need no specific recycling operations

Ordering and shipping details

Category	00931 - EDB CIRCUIT BREAKERS
Discount Schedule	DE2
GTIN	00785901875345
Nbr. of units in pkg.	1
Package weight(Lbs)	3.6299999999999999
Returnability	Y
Country of origin	MX

Contractual warranty

Warranty period	18 months
-----------------	-----------

Complementary

Line Rated Current	60 A
System Voltage	480Y/277 V AC
AWG gauge	AWG 12...AWG 2/0 aluminium AWG 14...AWG 2/0 copper
Breaking capacity	18 kA at 480Y/277 V AC 25 kA at 240 V AC
Circuit breaker application	HACR rated
Depth	4.05 in
Electrical connection	Lugs
Height	5.66 in
Holding current	630 A
Local signalling	Trip indicator
Mounting mode	Bolt-on
Number of poles	3
Number of spaces	3
Number of spaces required	3
Product destination	NF panelboard
Protection type	Short-circuit Overload
Width	2.94 in

Environment

Product certifications	CSA UL listed
Ambient air temperature for operation	104 °F (40 °C)