

Productname : Amberclens fg
Ref.Nr.: BDS000316_3_20150123 (EN)

Creationdate : 23.01.15 Version : 1.0
Replaces: BDS000316_20110607

SECTION 1: Identification of the substance/mixture and of the company/undertaking

1.1. Product identifier

Amberclens fg
Aerosol

1.2. Relevant identified uses of the substance or mixture and uses advised against

Cleaners - Precision

1.3. Details of the supplier of the safety data sheet

CRC Industries UK Ltd.
Ambersil House - Wylds Road
Castlefield Industrial Estate
TA6 4DD Bridgwater Somerset
United Kingdom
Tel.: +44 1278 727200
Fax.: +44 1278 425644
E-mail : hse.uk@crcind.com

1.4. Emergency telephone number

(+44)(0)1278 72 7200

SECTION 2: Hazards identification

2.1. Classification of the substance or mixture

Classification according to Regulation (EC) No 1272/2008

Physical:	Aerosol, category 3 Pressurised container: May burst if heated. Not flammable under normal conditions of use but contains flammable components (Testing on flammability in closed space, FEA X610-E, are negative)
Health:	Not classified
Environment:	Not classified
Other hazards :	7 % by mass of the contents are flammable. Safety data sheet available on request.

Classification according to 67/548/EEC or 1999/45/EC:

None

Productname : Amberclens fg **Creationdate :** 23.01.15 Version : 1.0
Ref.Nr.: BDS000316_3_20150123 (EN) **Replaces:** BDS000316_20110607

Health: Not classified
Physical: Not classified
 Not flammable under normal conditions of use but contains flammable components
 (Testing on flammability in closed space, FEA X610-E, are negative)
Environment: Not classified

2.2. Label elements

Labelling according to Regulation (EC) No 1272/2008

Signal word: Warning
Hazard statement(s): H229 : Pressurised container: May burst if heated.
Precautionary statement(s): P102 : Keep out of reach of children.
 P210 : Keep away from heat, hot surfaces, sparks, open flames and other ignition sources. No smoking.
 P251 : Do not pierce or burn, even after use.
 P410/412 : Protect from sunlight. Do not expose to temperatures exceeding 50°C/122°F.
Supplemental Hazard information: 7 % by mass of the contents are flammable.
 Safety data sheet available on request.

Regulation (EC) No 648/2004 on detergents: aliphatic hydrocarbons < 5 %
 anionic surfactants < 5 %
 non-ionic surfactants < 5 %

2.3. Other hazards

None

SECTION 3: Composition/information on ingredients

3.1. Substances

Not applicable.

3.2. Mixtures

Hazardous ingredient	CAS-nr.	EC-nr	w/w %	symbol	R-phrases*	Notes
Alcohol C10, ethoxylated	26183-52-8	Polymer	1-5	Xn,Xi	R22,R36	
(2-methoxymethylethoxy)propanol	34590-94-8	252-104-2	1-5	-	-	A
Hydrocarbons,C3-4-rich, petroleum distillate Petroleumgas (1,3-butadiene < 0.1%)	68512-91-4	270-990-9	1-5	F+	12	K,G
Explanation notes						
A : substance with Community workplace exposure limit						

Productname : Amberclens fg **Creationdate :** 23.01.15 Version : 1.0
Ref.Nr.: BDS000316_3_20150123 (EN) **Replaces:** BDS000316_20110607

G : exempted from the obligation to register in accordance with art.2(7)(a)of REACH Regulation No 1907/2006

K : not classified as carcinogen, less than 0.1% w/w 1,3-butadiene (Einecs-nr. 203-450-8)

Hazardous ingredient	Registration number	CAS-nr.	EC-nr	w/w %	Hazard Class and Category	Hazard statement	Notes
Alcohol C10, ethoxylated	-	26183-52-8	Polymer	1-5	Acute Tox. 4, Eye Irrit. 2	H302,H319	
(2-methoxymethylethoxy)propanol	01-2119450011-60	34590-94-8	252-104-2	1-5	-	-	A
Hydrocarbons,C3-4-rich, petroleum distillate Petroleumgas (1,3-butadiene < 0.1%)	-	68512-91-4	270-990-9	1-5	Press. Gas, Flam. Gas 1	H280,H220	K,G

Explanation notes

A : substance with Community workplace exposure limit

G : exempted from the obligation to register in accordance with art.2(7)(a)of REACH Regulation No 1907/2006

K : not classified as carcinogen, less than 0.1% w/w 1,3-butadiene (Einecs-nr. 203-450-8)

(* Explanation phrases : see chapter 16)

SECTION 4: First aid measures

4.1. Description of first aid measures

Contact with eyes :	If substance has got into eyes, immediately wash out with plenty of water
Contact with skin :	Wash with plenty of soap and water.
Inhalation :	Remove victim to fresh air and keep at rest in a position comfortable for breathing.
Ingestion :	If swallowed accidentally, do not induce vomiting and seek medical advice.

4.2. Most important symptoms and effects, both acute and delayed

Inhalation :	No adverse health effects expected
Ingestion :	May cause gastrointestinal disturbances Symptoms : sore throat, abdominal pain, nausea, vomiting
Skin contact :	May cause irritation.
Eye contact :	May cause irritation.

4.3. Indication of any immediate medical attention and special treatment needed

General Advice :	In case of accident or if you feel unwell, seek medical advice (show the label where possible) If symptoms persist always call a doctor
-------------------------	--

SECTION 5: Firefighting measures

5.1. Extinguishing media

water, foam, carbon dioxide or dry agent

5.2. Special hazards arising from the substance or mixture

Productname : Amberclens fg
Ref.Nr.: BDS000316_3_20150123 (EN)

Creationdate : 23.01.15 Version : 1.0
Replaces: BDS000316_20110607

Aerosols may explode if heated above 50°C
Forms hazardous decomposition products
CO,CO2

5.3. Advice for firefighters

Keep container(s) exposed to fire cool, by spraying with water
In case of fire, do not breathe fumes

SECTION 6: Accidental release measures

6.1. Personal precautions, protective equipment and emergency procedures

Shut off all ignition sources
Ensure adequate ventilation
Wear suitable protective clothing and gloves.

6.2. Environmental precautions

Do not allow to enter public sewers and watercourses

6.3. Methods and material for containment and cleaning up

Absorb spillage in suitable inert material
Wash spill site with water and detergent

6.4. Reference to other sections

For further information see section 8

SECTION 7: Handling and storage

7.1. Precautions for safe handling

Keep away from heat and sources of ignition
Do not spray on a naked flame or incandescent material.
Do not pierce or burn aerosols, even after use.
Do not breathe aerosols or vapours.
Ensure adequate ventilation
Avoid contact with skin and eyes.

7.2. Conditions for safe storage, including any incompatibilities

Pressurised container: protect from sunlight and do not expose to temperatures exceeding 50°C. Do not pierce or burn, even after use.
Store in a well-ventilated place.
Store frost free
Keep out of reach of children.

Productname : Amberclens fg **Creationdate :** 23.01.15 Version : 1.0
Ref.Nr.: BDS000316_3_20150123 (EN) **Replaces:** BDS000316_20110607

7.3. Specific end use(s)

Cleaners - Precision

SECTION 8: Exposure controls/personal protection

8.1. Control parameters

Exposure limits :

Hazardous ingredient	CAS-nr.	method	
EU established exposure limits:			
(2-methoxymethylethoxy)propanol	34590-94-8	TWA	50 ppm
National established exposure limits, United Kingdom			
(2-methoxymethylethoxy)propanol	34590-94-8	TWA	50 ppm

8.2. Exposure controls

Control procedures :	Ensure adequate ventilation Keep away from heat and sources of ignition
Personal protection :	Take precautions to avoid contact with skin and eyes when handling the product. Ensure adequate ventilation
inhalation :	In case of insufficient ventilation, wear suitable respiratory equipment.
recommended respiratory protection:	Air purifying respirator equipped with ABEK type cartridge
hands and skin :	Wear suitable protective gloves against chemicals
Recommended gloves:	Nitrile
eyes :	Wear safety goggles.
Environmental protection:	Avoid release to the environment. Collect spillage.

SECTION 9: Physical and chemical properties

9.1. Information on basic physical and chemical properties

(for aerosols data for the product without propellant)

Apperance : physical state :	Propane/butane propelled liquid.
colour :	White.
odour :	Neutral.
pH :	11
Boiling point/range :	100 °C
Flash point :	None
Evaporation rate :	Not available.
Explosion limits : upper limit :	Not available.
lower limit :	Not available.
Vapour pressure :	Not available.
Relative density :	1.01 g/cm ³ (@ 20°C).

Productname : Amberclens fg
Ref.Nr.: BDS000316_3_20150123 (EN)

Creationdate : 23.01.15 Version : 1.0
Replaces: BDS000316_20110607

Solubility in water : Soluble in water
Auto-ignition : > 200 °C
Viscosity : Not applicable.

9.2. Other information

VOC: 69 g/l

SECTION 10: Stability and reactivity

10.1. Reactivity

No hazardous reactions known if used for its intended purpose

10.2. Chemical stability

Stable

10.3. Possibility of hazardous reactions

No hazardous reactions known if used for its intended purpose

10.4. Conditions to avoid

Pressurized container : protect from sunlight and do not expose to temperatures exceeding 50°C.
Avoid overheating
Store frost free

10.5. Incompatible materials

Strong oxidising agent

10.6. Hazardous decomposition products

CO,CO2

SECTION 11: Toxicological information

11.1. Information on toxicological effects

Information on likely routes of exposure:

Inhalation : No adverse health effects expected
Ingestion : Ingestion is unlikely to occur
Skin contact : May cause irritation.
Eye contact : May cause irritation.

Toxicological data :

Productname : Amberclens fg
Ref.Nr.: BDS000316_3_20150123 (EN)

Creationdate : 23.01.15 Version : 1.0
Replaces: BDS000316_20110607

Hazardous ingredient	CAS-nr.	method	
(2-methoxymethylethoxy)propanol	34590-94-8	LD50 oral rat	> 4000 mg/kg
		LD50 derm.rabit	9510 mg/kg

SECTION 12: Ecological information

12.1. Toxicity

Not classified

Ecotoxicological data:

Hazardous ingredient	CAS-nr.	method	
(2-methoxymethylethoxy)propanol	34590-94-8	EC50 daphnia	1919 mg/l

12.2. Persistence and degradability

Readily biodegradable - OECD 301B

12.3. Bioaccumulative potential

No experimental data available

12.4. Mobility in soil

Soluble in water

12.5. Results of PBT and vPvB assessment

No information available

12.6. Other adverse effects

No experimental data available

SECTION 13: Disposal considerations

13.1. Waste treatment methods

Product : This material and its container must be disposed of in a safe way. Do not discharge into drains or the environment, dispose to an authorised waste collection point.

National regulations : Disposal should be in accordance with local, state or national legislation

Productname : Amberclens fg
Ref.Nr.: BDS000316_3_20150123 (EN)

Creationdate : 23.01.15 Version : 1.0
Replaces: BDS000316_20110607

SECTION 14: Transport information

14.1. UN number

UN-number : 1950

14.2. UN proper shipping name

Proper shipping name: AEROSOLS

14.3. Transport hazard class(es)

Class: 2.2
ADR/RID - Classification code: 5A

14.4. Packing group

Packing group: Not applicable.

14.5. Environmental hazards

ADR/RID - Environmentally
hazardous: No
IMDG - Marine pollutant: No
IATA/ICAO - Environmentally
hazardous: No

14.6. Special precautions for user

ADR/RID - Tunnelcode: (E)
IMDG - Ems: F-D, S-U
IATA/ICAO - PAX: 203
IATA/ICAO - CAO: 203

14.7. Transport in bulk according to Annex II of MARPOL73/78 and the IBC Code

Not applicable.

SECTION 15: Regulatory information

15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture

The Safety Data Sheet is compiled according to the current European requirements.
Dir. 2013/10/EU, 2008/47/EC amendment of the aerosol dispenser directive 75/324/EEC.
Regulation (EC) No 1907/2006 (REACH)
EU-directive 99/45/EC
Regulation (EC) No 1272/2008 (CLP)

Productname : Amberclens fg **Creationdate :** 23.01.15 Version : 1.0
Ref.Nr.: BDS000316_3_20150123 (EN) **Replaces:** BDS000316_20110607

15.2. Chemical safety assessment

No information available

SECTION 16: Other information

*Explanation risk-phrases: R12: Extremely flammable.
RR22
R36: Irritating to eyes.

*Explanation hazard statements: - : -
H220 : Extremely flammable gas.
H280 : Contains gas under pressure; may explode if heated.
H302 : Harmful if swallowed.
H319 : Causes serious eye irritation.

This product should be stored, handled and used in accordance with good industrial hygiene practices and in conformity with any legal regulation.

The information contained herewith is based on the present state of our knowledge and is intended to describe our products from the point of view of safety requirements. It does not guarantee any specific properties. Apart from any fair dealing for purposes of study, research and review of health, safety and environmental risks, no part of these documents may be reproduced by any process without written permission from CRC.