


Desktop and Wall Mount 2-Post Rack *1459 Series*

800 lbs Weight Capacity



Features

- Constructed in 16-gauge steel.
- EIA-310-D compliant front 19" mounting rails with 10-32 tapped clip nuts.
- Suitable for desktop or wall mounting applications.
- Welded open frame includes:
 - Removable top & bottom panels.
 - Optional side panels sold separately.
- Rubber feet included for table mounting.
- Desktop tested to nearly double the suggested load rating of 800 lbs (363 kg).
- Finished in textured black powder paint.
- RoHS Compliant.
- Manufactured in North America.

Note: This product will soon include a hardware pack of fifty (50) 10-32 screws and clip nuts. As this is a rolling change the product you receive may include less.

Accessories

- Universal Rack Shelf
- Two Post Mounting Clamping Shelf
- Adjustable Depth DIN Rail Panel
- Outlet Strips
- Rack Panels
- Rack Unit Label
- Two Post Mounting Adjustable Shelf
- Two Post Mounting Keyboard & Equipment Shelf
- 10-32 Mounting Screw and Clip Nut Combo-Pack
- Hinged Acrylic Door Panel Cover
- Cable Management

Part No.	Overall Dimensions			Rack Units	Mounting Dimensions			Optional Side Panels (Sold in Pairs)
	Height	Width	Depth		Height	Width	Depth	
1459FBK1	24.70	21.12	16.14	13U	22.75	19.00	16.14	1459FQBK1
1459JBK1	35.20	21.12	16.14	19U	33.25	19.00	16.14	1459JQBK1
1459MBK1	49.20	21.12	16.14	27U	47.25	19.00	16.14	1459MQBK1

Part No.	Overall Dimensions			Rack	Mounting Dimensions			Optional Side Panels
	Height	Width	Depth	Units	Height	Width	Depth	(Sold in Pairs)
1459M24BK1	49.20	21.12	24.14	27U	47.25	19.00	24.14	1459M24QBK1

Tags: **Relay Rack, H-Frame, Server Rack, Equipment Rack, SmartRack, Network Rack**

Data subject to change without notice

© 2016. Hammond Manufacturing Ltd. All rights reserved.