

15 Amp Horizontal Rackmount Surge Strip *1582-S Series*

Front Mounted Receptacles

Features



- Designed for power distribution from the front of the unit.
- 1U horizontal 19" rackmount installation.
- Available with lighted on/off switch or red pilot light to indicate power on.
- Available in ASA 61 grey or black powder coat finish.
- **Click here for our non-surge protected version.**

Specification

- Heavy duty 14 gauge wire cord - 14/3 SJT type for extreme temperature ranges and integral molded plug.
- Plug types available are NEMA 5-15P straight blade or NEMA L5-15P locking type.
- Includes 15 Amp, 125 VAC circuit breaker to prevent accidental overload.
- Surge protected panels incorporate our surge module:
 - 18,000 Amp rated MOV's
 - Maximum 54,000 Amps transient current and 780 Joules.
 - 400V Clamp Rating.
 - Protection in all 3 AC modes (L-N, N-G, and L-G).
 - Green indicator light confirms surge module is active.
 - Internal protection will disconnect the surge module at the end of its useful life (and extinguish the green light) but will maintain power to the load, now unprotected.
- Voltage suppression at the outlet guards against transients from equipment on the outlet strip.
- CSA certified, Standards C22.2 (No. 21-95, No. 42-99 and No. 8-M1986).



Accessories

- Mounting Hardware
- Rail Depth Adapter Kit

Black Part No.	ANSI 61 Gray Part No.	Overall Dimensions			Number	Number	Outlet NEMA Type	Cord Length (ft)	Plug Blade Type	NEMA Plug Type	Rack Units
		Height	Width	Depth	of Outlets On Front	of Outlets On Rear					
1582H6A1SBK	1582H6A1S	1.72	19.00	2.66	6	0	5-15R	6	Straight	5-15P	1U
1582H6B1SBK	1582H6B1S	1.72	19.00	2.66	6	0	5-15R	15	Straight	5-15P	1U
1582H6C1SBK	1582H6C1S	1.72	19.00	2.66	6	0	5-15R	6	Locking	L5-15P	1U
1582H6D1SBK	1582H6D1S	1.72	19.00	2.66	6	0	5-15R	15	Locking	L5-15P	1U

Data subject to change without notice

