

## SECTION 1: Identification of the substance/mixture and of the company/undertaking

### 1.1. Product identifier

PROPOWER GLASS CLEANER  
Aerosol

### 1.2. Relevant identified uses of the substance or mixture and uses advised against

Cleaners - Heavy duty

### 1.3. Details of the supplier of the safety data sheet

Premier Farnell  
150 Armley Road  
Leeds LS12 2QQ  
Tel. : +44 (0) 870 129 8608

### 1.4. Emergency telephone number

+44 (0) 870 202530

## SECTION 2: Hazards identification

### 2.1. Classification of the substance or mixture

Classification according to Regulation (EC) No 1272/2008



Physical	: Aerosols, category 1 Extremely flammable aerosol. Pressurised container: May burst if heated.
Health	: Eye irritation, category 2 Causes serious eye irritation. Specific target organ toxicity - single exposure, category 3 May cause drowsiness or dizziness.
Environment	: Not classified.

Classification according to 67/548/EEC or 1999/45/EC:

Extremely Flammable	
Xi : Irritant	
Health	: R36: Irritating to eyes. R67: Vapours may cause drowsiness and dizziness.
Physical	: R12: Extremely flammable. Extremely Flammable
Environment	: Not classified

### 2.2. Label elements

Labelling according to Regulation (EC) No 1272/2008

Product identifier	: Contains: propan-2-ol; isopropyl alcohol ;isopropanol
Hazard pictogram(s)	:  
Signal word	: Danger
Hazard statement(s)	: H222 : Extremely flammable aerosol. H229 : Pressurised container: May burst if heated. H319 : Causes serious eye irritation. H336 : May cause drowsiness or dizziness.

# Safety Data Sheet

pro-POWER

Precautionary statement(s) : P102 : Keep out of reach of children.  
 P210 : Keep away from heat, hot surfaces, sparks, open flames and other ignition sources. No smoking.  
 P211 : Do not spray on an open flame or other ignition source.  
 P251 : Do not pierce or burn, even after use.  
 P261 : Avoid breathing dust/fume/gas/mist/vapours/spray.  
 P271 : Use only outdoors or in a well-ventilated area.  
 P410/412 : Protect from sunlight. Do not expose to temperatures exceeding 50°C/122°F.  
 P501-2 : Dispose of contents/container to an authorised waste collection point.

Regulation (EC) No 648/2004 on detergents : aliphatic hydrocarbons 5 - 15 %  
 perfumes hexyl cinnamal, hydroxycitronellal

## 2.3. Other hazards

None

## SECTION 3: Composition/information on ingredients

### 3.1. Substances

Not applicable.

### 3.2. Mixtures

Hazardous ingredient	CAS-nr.	EC-nr	w/w %	symbol	R-phrases*	Notes
propan-2-ol; isopropyl alcohol ;isopropanol	67-63-0	200-661-7	30-60	F,Xi	11-36-67	B
Hydrocarbons,C3-4-rich, petroleum distillate Petroleumgas (1,3-butadiene < 0.1%)	68512-91-4	270-990-9	10-30	F+	12	K,G
ammonia .... %	1336-21-6	215-647-6	0-1	C,N	34-50	

#### Explanation notes

**B** : substance with national established workplace exposure limit

**G** : exempted from the obligation to register in accordance with art.2(7)(a)of REACH Regulation No 1907/2006

**K** : not classified as carcinogen, less than 0.1% w/w 1,3-butadiene (Einecs-nr. 203-450-8)

Hazardous ingredient	Registration number	CAS-nr.	EC-nr	w/w %	Hazard Class and Category	Hazard Statement	Notes
propan-2-ol; isopropyl alcohol; isopropanol	01-2119457558-25	67-63-0	200-661-7	30-60	Flam. Liq. 2, Eye Irrit. 2, STOT SE 3	H225, H319, H336	B
Hydrocarbons,C3-4-rich, petroleum distillate Petroleumgas (1,3-butadiene < 0.1%)	-	68512-91-4	270-990-9	10-30	Press. Gas, Flam. Gas 1	H280, H220	K, G
ammonia .... %		1336-21-6	215-647-6	0-1	Skin Corr. 1B, Aquatic Acute 1	H314, H400	

#### Explanation notes

**B** : substance with national established workplace exposure limit

**G** : exempted from the obligation to register in accordance with art.2(7)(a)of REACH Regulation No 1907/2006

**K** : not classified as carcinogen, less than 0.1% w/w 1,3-butadiene (Einecs-nr. 203-450-8)

(\*Explanation phrases : see chapter 16)

www.element14.com  
 www.farnell.com  
 www.newark.com  
 www.cpc.co.uk

pro-POWER

## SECTION 4: First aid measures

### 4.1. Description of first aid measures

- Contact with eyes : IF IN EYES: Rinse cautiously with water for several minutes.  
Remove contact lenses, if present and easy to do. Continue rinsing.  
If eye irritation persists: Get medical advice/attention.
- Contact with skin : Take off contaminated clothing and wash before reuse.  
IF ON SKIN: Wash with plenty of soap and water.  
If skin irritation occurs: Get medical advice/attention.
- Inhalation : IF INHALED: Remove person to fresh air and keep comfortable for breathing.  
Call a POISON CENTER or doctor/physician if you feel unwell.
- Ingestion : If swallowed accidentally, do not induce vomiting and seek medical advice.

### 4.2. Most important symptoms and effects, both acute and delayed

- Inhalation : Excessive inhalation of solvent vapours may give rise to nausea,  
headaches and dizziness
- Ingestion : May cause gastrointestinal disturbances  
Symptoms : sore throat, abdominal pain, nausea, vomiting
- Skin contact : May cause irritation.  
Symptoms : redness and pain
- Eye contact : Irritating to eyes  
Symptoms : redness and pain

### 4.3. Indication of any immediate medical attention and special treatment needed

- General Advice : If you feel unwell, seek medical advice (show the label where possible)  
If symptoms persist always call a doctor

## SECTION 5: Firefighting measures

### 5.1. Extinguishing media

Foam, carbon dioxide or dry agent

### 5.2. Special hazards arising from the substance or mixture

Aerosols may explode if heated above 50°C  
Forms hazardous decomposition products  
CO,CO<sub>2</sub>

### 5.3. Advice for firefighters

Keep container(s) exposed to fire cool, by spraying with water  
In case of fire, do not breathe fumes

## SECTION 6: Accidental release measures

### 6.1. Personal precautions, protective equipment and emergency procedures

Shut off all ignition sources  
Ensure adequate ventilation  
Wear suitable protective clothing and gloves.

### 6.2. Environmental precautions

Do not allow to enter public sewers and watercourses  
If polluted water reaches drainage systems or water courses, immediately inform appropriate authorities

### 6.3. Methods and material for containment and cleaning up

Absorb spillage in suitable inert material  
Place in appropriate container

### 6.4. Reference to other sections

For further information see section 8

## SECTION 7: Handling and storage

### 7.1. Precautions for safe handling

Keep away from heat and sources of ignition  
Take precautionary measures against static discharges  
Equipment should be earthed  
Use explosion-proof electrical/ventilating/lighting/.../equipment.  
Use only non-sparking tools.  
Do not breathe aerosols or vapours.  
Ensure adequate ventilation  
Avoid contact with skin and eyes.  
Wash thoroughly after use  
Wear protective gloves/protective clothing/eye protection/face protection.  
Eyewash bottles should be available

### 7.2. Conditions for safe storage, including any incompatibilities

Pressurized container : protect from sunlight and do not expose to temperatures exceeding 50°C.  
Keep out of reach of children.

### 7.3. Specific end use(s)

Cleaners - Heavy duty

## SECTION 8: Exposure controls/personal protection

### 8.1. Control parameters

Exposure limits:

Hazardous ingredient	CAS-nr.	method	
<b>EU established exposure limits:</b>			
propan-2-ol; isopropyl alcohol;sopropanol	67-63-0	TWA	400 ppm
		STEL	500 ppm

### 8.2. Exposure controls

Control procedures : Ensure adequate ventilation  
Keep away from heat and sources of ignition  
Take precautionary measures against static discharges

Personal protection : Take precautions to avoid contact with skin and eyes when handling the product.  
Ensure adequate ventilation

Inhalation : In case of insufficient ventilation, wear suitable respiratory equipment.

Hands and Skin : Wear suitable protective gloves against chemicals

Recommended gloves : Nitrile

Eyes : Wear safety goggles.

Environmental protection : Avoid release to the environment.  
Collect spillage.

## SECTION 9: Physical and chemical properties

### 9.1. Information on basic physical and chemical properties

(for aerosols data for the product without propellant)

Appearance : physical state	: Liquid under pressure.
Colour	: Colourless.
Odour	: Characteristic odor.
pH	: Not applicable.
Boiling point/range	: 82°C
Flash point	: 12°C
Evaporation rate	: Not available.
Explosion limits : upper limit	: 12%
Lower limit	: 1.8%
Vapour pressure	: Not available.
Relative density	: 0.933 g/cm <sup>3</sup> (@ 20°C).
Solubility in water	: Miscible with water
Auto-ignition	: 460°C
Viscosity	: Not available.

### 9.2. Other information

VOC	: 669 g/l
-----	-----------

## SECTION 10: Stability and reactivity

### 10.1. Reactivity

No hazardous reactions known if used for its intended purpose

### 10.2. Chemical stability

Stable

### 10.3. Possibility of hazardous reactions

No hazardous reactions known if used for its intended purpose

### 10.4. Conditions to avoid

Avoid overheating

### 10.5. Incompatible materials

Strong oxidising agent

### 10.6. Hazardous decomposition products

CO,CO<sub>2</sub>

## SECTION 11: Toxicological information

### 11.1. Information on toxicological effects

Information on likely routes of exposure:

Inhalation	: Inhalation of solvent vapours may give rise to nausea, headaches and dizziness
Ingestion	: May cause gastrointestinal disturbances
Skin contact	: May cause irritation.
Eye contact	: Irritating to eyes

## Toxicological data:

Hazardous ingredient	CAS-nr.	method	
propan-2-ol; isopropyl alcohol ;isopropanol	67-63-0	LD50 oral rat	> 5000 mg/kg
		LC50 inhal.rat	> 20 mg/l
		LD50 derm.rabit	> 5000 mg/kg

## SECTION 12: Ecological information

### 12.1. Toxicity

Not classified

### Ecotoxicological data:

Hazardous ingredient	CAS-nr.	method	
propan-2-ol; isopropyl alcohol ;isopropanol	67-63-0	IC50 algae	> 1000 mg/l
		LC50 fish	> 1000 mg/l
		EC50 daphnia	> 1000 mg/l

### 12.2. Persistence and degradability

No information available

### 12.3. Bioaccumulative potential

No information available

### 12.4. Mobility in soil

Miscible with water

### 12.5. Results of PBT and vPvB assessment

No information available

### 12.6. Other adverse effects

No information available

## SECTION 13: Disposal considerations

### 13.1. Waste treatment methods

Product : This material and its container must be disposed of in a safe way.  
Do not discharge into drains or the environment, dispose to an authorised waste collection point.

National regulations : Disposal should be in accordance with local, state or national legislation

## SECTION 14: Transport information

### 14.1. UN number

UN-number : 1950

### 14.2. UN proper shipping name

Proper shipping name : AEROSOLS

### 14.3. Transport hazard class(es)

Class : 2.1

ADR/RID - Classification code : 5F

### 14.4. Packing group

Packing group : Not applicable.

## 14.5. Environmental hazards

ADR/RID - Environmentally hazardous : No  
IMDG - Marine pollutant : No  
IATA/ICAO - Environmentally hazardous : No

## 14.6. Special precautions for user

ADR/RID - Tunnelcode : (D)  
IMDG - Ems : F-D, S-U  
IATA/ICAO - PAX : 203  
IATA/ICAO - CAO : 203

## 14.7. Transport in bulk according to Annex II of MARPOL73/78 and the IBC Code

Not applicable.

## SECTION 15: Regulatory information

### 15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture

The Safety Data Sheet is compiled according to the current European requirements.  
Dir. 2013/10/EU, 2008/47/EC amendment of the aerosol dispenser directive 75/324/EEC.  
EU-directive 99/45/EC  
Regulation (EC) No 1272/2008 (CLP)  
Regulation (EC) No 1907/2006 (REACH)

### 15.2. Chemical safety assessment

No information available

## SECTION 16: Other information

\*Explanation risk-phrases : R11: Highly flammable.  
R12: Extremely flammable.  
R34: Causes burns.  
R36: Irritating to eyes.  
R50: Very toxic to aquatic organisms.  
R67: Vapours may cause drowsiness and dizziness.

\*Explanation hazard statements : H220 : Extremely flammable gas.  
H225 : Highly flammable liquid and vapour.  
H280 : Contains gas under pressure; may explode if heated.  
H314 : Causes severe skin burns and eye damage.  
H319 : Causes serious eye irritation.  
H336 : May cause drowsiness or dizziness.  
H400 : Very toxic to aquatic life.

This product should be stored, handled and used in accordance with good industrial hygiene practices and in conformity with any legal regulation.

The information contained herewith is based on the present state of our knowledge and is intended to describe our products from the point of view of safety requirements. It does not guarantee any specific properties.

<b>Part Number</b>
--------------------

PPC106
--------

**Important Notice** : This data sheet and its contents (the "Information") belong to the members of the Premier Farnell group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. pro-POWER is the registered trademark of the Group. © Premier Farnell Limited 2016.