

Product data sheet

Characteristics

QMB363T

SWITCH, FUSIBLE QMB 600V 100A 3P TWIN

Product availability : Stock - Normally stocked in distribution facility



Main

Product or component type	Fuse-switch
Range of product	QMB Square D

Complementary

Line Rated Current	100 A
Device composition	Without neutral
Device mounting	Surface
Height	7.5 in
Material	Steel
Number of poles	3
Permissible voltage	<= 600 V AC
Product destination	Meter board Distribution board
Protection type	Fuse protection
Short circuit protection	200000 A AIR
Switch function	TPST

Environment

Product certifications	UL listed
------------------------	-----------

Ordering and shipping details

Category	00037 - QMB BRANCH CB,SW,& MAIN SW
Discount Schedule	PE1A
GTIN	00785901186182
Nbr. of units in pkg.	1
Package weight(Lbs)	32.79999999999997

Returnability	Y
Country of origin	US

Offer Sustainability

Sustainable offer status	Not Green Premium product
RoHS (date code: YYWW)	Will be compliant on 3Q2014 Will be compliant on 3Q2014
REACH	Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold

Contractual warranty

Warranty period	18 months
-----------------	-----------
