

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0010112043

Status:

Active

Overview:

KK® Interconnect System - Molex

Description:

KK® 254 Crimp Housing, High Pressure, 4 Circuits

Documents:

3D Model

Packaging Specification PK-7880-001-001 (PDF)

Drawing (PDF)

RoHS Certificate of Compliance (PDF)

Product Specification PS-7879-001 (PDF)

Agency Certification	
CSA	LR19980
UL	E29179
General	
Product Family	Crimp Housings
Series	7880
Application	Signal, Wire-to-Board
Overview	KK® Interconnect System - Molex
Product Name	KK® 254
UPC	800753612297
Physical	
Circuits (maximum)	4
Color - Resin	Natural (White)
Flammability	94V-0
Gender	Female
Glow-Wire Compliant	No
Material - Resin	Nylon
Net Weight	0.392/g
Number of Rows	1
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	2.54mm
Pitch - Termination Interface	2.54mm
Stackable	No
Temperature Range - Operating	See Product Specification
Solder Process Data	
Lead-freeProcess Capability	N/A
Material Info	
Engineering Number	7880-4B
Reference - Drawing Numbers	
Packaging Specification	PK-7880-001-001
Product Specification	PS-7879-001
Sales Drawing	SD-7880



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

China RoHS

Compliant

REACH SVHC

Not Contained Per -ED/01/2017 (12 January 2017)

Halogen-Free

Status

Low-Halogen

Need more information on product environmental compliance?

Email productcompliance@molex.com

Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS

ELV

RoHS Phthalates

Green Image

Not Relevant

Not Contained

Search Parts in this Series

7880 Series

Mates With

KK®254 PCB Headers [42375](#) , [42377](#) , [42376](#) , [4030](#) , [6373](#) , [6410](#)

Use With

[7879](#) KK® High Pressure Crimp Terminal

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION