

Medium Power Phase Control Thyristors (Power Modules), 50 A, 70 A, 90 A



D-55

FEATURES

- Electrically isolated base plate
- Types up to 1200 V_{RRM}
- 3500 V_{RMS} isolating voltage
- Simplified mechanical designs, rapid assembly
- High surge capability
- Large creepage distances
- UL E78996 approved
- Designed and qualified for industrial level
- Material categorization: For definitions of compliance please see www.vishay.com/doc?99912


RoHS
COMPLIANT

PRODUCT SUMMARY

Package	D-55
Diode variation	Single SCR
$I_{T(AV)}$	50 A, 70 A, 90 A
V_{DRM}/V_{RRM}	100 V, 1200 V
V_{TM}	1.55 V
I_{GT}	120 mA
T_J	-40 °C to 125 °C

DESCRIPTION

These series of T-modules are intended for general purpose applications such as battery chargers, welders and plating equipment, regulated power supplies and temperature and speed control circuits. The semiconductors are electrically isolated from the metal base, allowing common heatsinks and compact assemblies to be built.

MAJOR RATINGS AND CHARACTERISTICS

SYMBOL	CHARACTERISTICS	T50RIA	T70RIA	T90RIA	UNITS
$I_{T(AV)}$	70 °C	50	70	90	A
$I_{T(RMS)}$		80	110	141	A
I_{TSM}	50 Hz	1310	1660	1780	A
	60 Hz	1370	1740	1870	
I^2t	50 Hz	8550	13 860	15 900	A ² s
	60 Hz	7800	12 650	14 500	
$I^2\sqrt{t}$		85 500	138 500	159 100	A ² \sqrt{s}
V_{RRM}	Range	100 to 1200			V
T_J		-40 to 125			°C

ELECTRICAL SPECIFICATIONS

VOLTAGE RATINGS

TYPE NUMBER	VOLTAGE CODE	V_{RRM}/V_{DRM} , MAXIMUM REPETITIVE PEAK REVERSE AND PEAK OFF-STATE VOLTAGE V	V_{RSM} , MAXIMUM NON-REPETITIVE PEAK REVERSE VOLTAGE V	I_{RRM}/I_{DRM} MAXIMUM AT $T_J = 25$ °C μA
VS-T50RIA VS-T70RIA VS-T90RIA	10	100	150	100
	20	200	300	
	40	400	500	
	60	600	700	
	80	800	900	
	100	1000	1100	
	120	1200	1300	



ON-STATE CONDUCTION								
PARAMETER	SYMBOL	TEST CONDITIONS		T50RIA	T70RIA	T90RIA	UNITS	
Maximum average on-state current at case temperature	$I_{T(AV)}$	180° conduction, half sine wave		50	70	90	A	
				70	70	70	°C	
Maximum RMS on-state current	$I_{T(RMS)}$			80	110	141	A	
Maximum peak, one-cycle on-state, non-repetitive surge current	I_{TSM}	t = 10 ms	No voltage reapplied	Sine half wave, initial $T_J = T_J$ maximum	1310	1660	1780	A
		t = 8.3 ms			1370	1740	1870	
		t = 10 ms	100 % V_{RRM} reapplied		1100	1400	1500	
		t = 8.3 ms			1150	1460	1570	
Maximum I^2t for fusing	I^2t	t = 10 ms	No voltage reapplied		8550	13 860	15 900	A ² s
		t = 8.3 ms			7800	12 650	14 500	
		t = 10 ms	100 % V_{RRM} reapplied		6050	9800	11 250	
		t = 8.3 ms			5520	8950	10 270	
Maximum $I^2\sqrt{t}$ for fusing	$I^2\sqrt{t}$	t = 0.1 to 10 ms, no voltage reapplied		85 500	138 500	159 100	A ² √s	
Low level value of threshold voltage	$V_{T(TO)1}$	$(16.7 \% \times \pi \times I_{T(AV)} < I < \pi \times I_{T(AV)})$, T_J maximum		0.97	0.77	0.78	V	
High level value of threshold voltage	$V_{T(TO)2}$	$(I > \pi \times I_{T(AV)})$, T_J maximum		1.13	0.88	0.88		
Low level value of on-state slope resistance	r_{t1}	$(16.7 \% \times \pi \times I_{T(AV)} < I < \pi \times I_{T(AV)})$, T_J maximum		4.1	3.6	2.9	mΩ	
High level value of on-state slope resistance	r_{t2}	$(I > \pi \times I_{T(AV)})$, T_J maximum		3.3	3.2	2.6		
Maximum on-state voltage drop	V_{TM}	$I_{TM} = \pi \times I_{T(AV)}$, $T_J = 25\text{ °C}$, $t_p = 400\ \mu\text{s}$ square Average power = $V_{T(TO)} \times I_{T(AV)} + r_f \times (I_{T(RMS)})^2$		1.60	1.55	1.55	V	
Maximum forward voltage drop	V_{FM}	$I_{TM} = \pi \times I_{T(AV)}$, $T_J = 25\text{ °C}$, $t_p = 400\ \mu\text{s}$ square Average power = $V_{T(TO)} \times I_{T(AV)} + r_f \times (I_{T(RMS)})^2$		1.60	1.55	1.55	V	
Maximum holding current	I_H	Anode supply = 6 V, initial $I_T = 30\text{ A}$, $T_J = 25\text{ °C}$		200	200	200	mA	
Maximum latching current	I_L	Anode supply = 6 V, resistive load = 10 Ω Gate pulse: 10 V, 100 μs, $T_J = 25\text{ °C}$		400	400	400		

SWITCHING				
PARAMETER	SYMBOL	TEST CONDITIONS	VALUES	UNITS
Typical turn-on time	t_{gd}	$T_J = 25\text{ °C}$, $V_d = 50\% V_{DRM}$, $I_{TM} = 50\text{ A}$ $I_g = 500\text{ mA}$, $t_r \leq 0.5$, $t_p \geq 6\ \mu\text{s}$	0.9	μs
Typical reverse recovery time	t_{rr}	$T_J = 125\text{ °C}$, $I_{TM} = 50\text{ A}$, $t_p = 300\ \mu\text{s}$, $di/dt = 10\text{ A}/\mu\text{s}$	3	
Typical turn-off time	t_q	$T_J = T_J$ maximum, $I_{TM} = 50\text{ A}$, $t_p = 300\ \mu\text{s}$, $di/dt = 15\text{ A}/\mu\text{s}$, $V_R = 100\text{ V}$, linear to 80 % V_{DRM}	110	

BLOCKING				
PARAMETER	SYMBOL	TEST CONDITIONS	VALUES	UNITS
Maximum peak reverse and off-state leakage current	I_{RRM} , I_{DRM}	$T_J = T_J$ maximum	15	mA
RMS isolation voltage	V_{ISOL}	50 Hz, circuit to base, all terminals shorted, $T_J = 25\text{ °C}$, $t = 1\text{ s}$	3500	V
Critical rate of rise of off-state voltage	dV/dt	$T_J = T_J$ maximum, linear to 80 % rated V_{DRM} ⁽¹⁾	500	V/μs

Note

⁽¹⁾ Available with $dV/dt = 1000\text{ V}/\mu\text{s}$, to complete code add S90 i.e. T90RIA80S90



TRIGGERING							
PARAMETER	SYMBOL	TEST CONDITIONS		T50RIA	T70RIA	T90RIA	UNITS
Maximum peak gate power	P_{GM}	$T_J = T_J$ maximum, $t_p \leq 5$ ms		10	12	12	W
Maximum average gate power	$P_{G(AV)}$	$T_J = T_J$ maximum, $f = 50$ Hz		2.5	3	3	
Maximum peak gate current	I_{GM}	$T_J = T_J$ maximum, $t_p \leq 5$ ms		2.5	3	3	A
Maximum peak negative gate voltage	$-V_{GT}$			10	10	10	V
Maximum required DC gate voltage to trigger	V_{GT}	$T_J = -40$ °C	Anode supply = 6 V, resistive load; $R_a = 1 \Omega$	4.0	4.0	4.0	V
		$T_J = 25$ °C		2.5	2.5	2.5	
		$T_J = T_J$ maximum		1.5	1.5	1.5	
Maximum required DC gate current to trigger	I_{GT}	$T_J = -40$ °C		250	270	270	mA
		$T_J = 25$ °C		100	120	120	
		$T_J = T_J$ maximum		50	60	60	
Maximum gate voltage that will not trigger	V_{GD}	$T_J = T_J$ maximum, rated V_{DRM} applied		0.2	0.2	0.2	V
Maximum gate current that will not trigger	I_{GD}			5.0	6.0	6.0	mA
Maximum rate of rise of turned-on current	di/dt	$V_D = 0.67$ rated V_{DRM} , $I_{TM} = 2 \times$ rated di/dt $I_G = 400$ mA for T50RIA and $I_G = 500$ mA for T70RIA/T90RIA; $t_r < 0.5 \mu s$, $t_p \geq 6 \mu s$ For repetitive value use 40 % non-repetitive Per JEDEC STD. RS397, 5.2.2.6		200	200	200	A/ μs
				180	180	180	
				160	160	160	
				150	150	150	

THERMAL AND MECHANICAL SPECIFICATIONS							
PARAMETER	SYMBOL	TEST CONDITIONS		T50RIA	T70RIA	T90RIA	UNITS
Maximum junction operating temperature range	T_J			- 40 to 125			°C
Maximum storage temperature range	T_{Stg}			- 40 to 150			
Maximum thermal resistance, junction to case per junction	R_{thJC}	DC operation		0.65	0.50	0.38	K/W
Maximum thermal resistance, case to heatsink	R_{thCS}	Mounting surface, smooth, flat and greased		0.2			
Mounting torque, ± 10 % <small>to heatsink terminals</small>		Non-lubricated threads	M3.5 mounting screws ⁽¹⁾	1.3 \pm 10 %			Nm
			M5 screw terminals	3 \pm 10 %			
Approximate weight				54			g
Case style				D-55 (T-module)			

Note

⁽¹⁾ A mounting compound is recommended and the torque should be rechecked after a period of 3 hours to allow for the spread of the compound

ΔR CONDUCTION PER JUNCTION											
DEVICES	SINUSOIDAL CONDUCTION AT T_J MAXIMUM					RECTANGULAR CONDUCTION AT T_J MAXIMUM					UNITS
	180°	120°	90°	60°	30°	180°	120°	90°	60°	30°	
T50RIA	0.08	0.10	0.13	0.19	0.31	0.06	0.10	0.14	0.20	0.32	K/W
T70RIA	0.07	0.08	0.10	0.14	0.24	0.05	0.08	0.11	0.15	0.24	
T90RIA	0.05	0.06	0.08	0.12	0.20	0.04	0.06	0.09	0.12	0.20	

Note

• Table shows the increment of thermal resistance R_{thJC} when devices operate at different conduction angles than DC




Fig. 1 - Current Ratings Characteristics




Fig. 2 - Current Ratings Characteristics




Fig. 3 - On-State Power Loss Characteristics




Fig. 4 - On-State Power Loss Characteristics




Fig. 5 - Maximum Non-Repetitive Surge Current




Fig. 6 - Maximum Non-Repetitive Surge Current




Fig. 7 - On-State Voltage Drop Characteristics




Fig. 8 - Gate Characteristics




Fig. 9 - Current Ratings Characteristics




Fig. 10 - Current Ratings Characteristics




Fig. 11 - On-State Power Loss Characteristics




Fig. 12 - On-State Power Loss Characteristics




Fig. 13 - Maximum Non-Repetitive Surge Current




Fig. 14 - Maximum Non-Repetitive Surge Current




Fig. 15 - On-State Voltage Drop Characteristics




Fig. 16 - Gate Characteristics




Fig. 17 - Current Ratings Characteristics




Fig. 18 - Current Ratings Characteristics




Fig. 19 - On-State Power Loss Characteristics




Fig. 20 - On-State Power Loss Characteristics




Fig. 21 - Maximum Non-Repetitive Surge Current




Fig. 22 - Maximum Non-Repetitive Surge Current




Fig. 23 - On-State Voltage Drop Characteristics





Fig. 24 - Thermal Impedance Z_{thJC} Characteristics




ORDERING INFORMATION TABLE



- 1** - Vishay Semiconductors product
- 2** - Module type
- 3** - Current rating
- 4** - Circuit configuration
- 5** - Voltage code x 10 = V_{RRM}

CIRCUIT CONFIGURATION



LINKS TO RELATED DOCUMENTS

Dimensions	www.vishay.com/doc?95336
------------	--



Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and / or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Except as expressly indicated in writing, Vishay products are not designed for use in medical, life-saving, or life-sustaining applications or for any other application in which the failure of the Vishay product could result in personal injury or death. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.