

# 2 mode Noise Filters

Type: EXC24CB/CP EXC24CN




#### **Features**


- Burst/radiation noise filtering for audio circuits
- The optimally magnetic-coupled ferrite beads allow for the filtering of both common and normal mode noises
- The strong multi-layer structure provides high resistance to reflow soldering heat and a high mounting reliability
- Magnetic shield type
- High Impedance : 220 to 1 k $\Omega$  (EXC24CB type)
- Low Resistance Value : 0.4  $\Omega$  max. (EXC24CP type)
- ullet High Impedance : 600  $\Omega$ , Low Resistance Value : 0.9  $\Omega$  max. (EXC24CN type)
- RoHS compliant

## **Recommended Applications**


- Smart phones, Tablet PCs, DSC and Portable Music Player
- Noise suppression of burst noise of Receiver/Microphone and D-class power amplifier



#### Construction




#### Dimensions in mm (not to scale)



Jul 2014



# **Circuit Configuration (No Polarity)**



 The pin numbers shown here are for reference purposes only. Confirm the actual pin number arrangement with the exchanged specification documents.


# **Ratings**

Part Number	Impedance (0	Open mode)	Rated Voltage	Rated Current	DC Resistance
Fait Number	(Ω) at 100 MHz	Tolerance(%)	(V DC)	(mA DC)	$(\Omega)$ max.
EXC24CP121U	120			500	0.3
EXC24CP221U	220	±25	5	350	0.4
EXC24CB221U	220	±25	5	100	0.7
EXC24CB102U	1000			50	1.5

Part Number	Impedance (Co	mmon mode)	Rated Voltage	Rated Current	DC Resistance
rait Nullibel	(Ω) at 100 MHz	Tolerance(%)	(V DC)	(mA DC)	$(\Omega)$ max.
EXC24CN601X	600	±25	5	200	0.9


• Category Temperature Range -40 °C to +85 °C

# **Impedance Characteristics (Typical)**




# **Panasonic**

# **Attenuation Characteristics (Typical)**



# Measurement Circuit (A) Open Mode (B) Common (C) Differential Mode




# **Packaging Methods (Taping)**


#### Standard Quantity

Part Number	Size (inch)	Kind of Taping	Pitch (P <sub>1</sub> )	Quantity
EXC14CP□□□U	0302	Embassad Carrior Taning	2 mm	10,000 pcs./reel
EXC24CP/CB□□□U	0504	Embossed Carrier Taping	4 mm	5,000 pcs./reel
EXC24CN□□□X	0504	Pressed Carrier Taping	2 mm	10,000 pcs./reel


#### Embossed Carrier Taping



#### Pressed Carrier Taping



# • Taping Reel



#### • Embossed Carrier Dimensions

(mm)

	Part Number	А	В	W	F	Е	P <sub>1</sub>	P <sub>2</sub>	P <sub>0</sub>	$\phi D_0$	t <sub>1</sub>	t <sub>2</sub>
	EXC14CP	0.75±0.10	0.95±0.10	8.0±0.2	3.50±0.05	1.75±0.10	2.0±0.1	2.0±0.1	4.0±0.1	1.5+0.1	0.25±0.05	0.85±0.15
_	FXC24CP/CB	1 20+0 15	1 45+0 15	8.0+0.2	35+01	1 75+0 10	4 0+0 1	2 0+0 1	4 0+0 1	1.5+0.1	0.25+0.05	0.90+0.15

# Pressed Carrier Dimensions

(mm)

The second carrier armendients										(11111)
Part Number	А	В	W	F	Е	P <sub>1</sub>	P <sub>2</sub>	P <sub>0</sub>	$\phi D_0$	t <sub>2</sub>
EXC24CN	1.14±0.10	1.38±0.15	8.0±0.2	3.5±0.1	1.75±0.10	2.0±0.1	2.0±0.1	4.0±0.1	1.5 <sup>+0.1</sup>	0.68±0.10


#### Standard Reel Dimensions

(mm)

Part Number	φΑ	φB	φC	φD	Е	W	Т
EXC14C/EXC24C	180.0±3.0	60.0±1.0	13.0±0.5	21.0±0.8	2.0±0.5	9.0±0.3	11.4±1.5



## **Recommended Land Pattern Design**




Part			Dimensi	on (mm	)	
Number	А	В	С	D	Е	F
EXC14CP	0.80 to 1.00	0.80	0.30	0.25 to 0.35	0.30	0.20
EXC24CP EXC24CB EXC24CN	1.50 to 1.90	1.10	0.50	0.50 to 0.70	0.40	0.30

#### **Recommended Soldering Conditions**

Recommendations and precautions are described below.

- Recommended soldering conditions for reflow
- Reflow soldering shall be performed a maximum of two times.
- · Please contact us for additional information when used in conditions other than those specified.
- Please measure the temperature of the terminals and study every kind of solder and printed circuit board for solderability before actual use.



For soldering (Example: Sn-37Pb)

	Temperature	Time		
Preheating	140 °C to 160 °C	60 s to 120 s		
Main heating	Above 200 °C	30 s to 40 s		
Peak	235 ± 10 °C	max. 10 s		

For lead-free soldering (Example : Sn/3Ag/0.5Cu)

	Temperature	Time
Preheating	150 °C to 170 °C	60 s to 120 s
Main heating	Above 230 °C	30 s to 40 s
Peak	max. 260 °C	max. 10 s

- Flow soldering
- · We do not recommend flow soldering, because flow soldering may cause bridges between the electrodes.

#### <Repair with hand soldering>

- Preheat with a blast of hot air or similar method. Use a soldering iron with a tip temperature of 350 °C or less.
   Solder each electrode for 3 seconds or less.
- Never touch this product with the tip of a soldering iron.

#### 

The following are precautions for individual products. Please also refer to the common precautions for EMC Components in this catalog.

- 1. Use rosin-based flux or halogen-free flux.
- 2. For cleaning, use an alcohol-based cleaning agent. Before using any other type, consult with our sales person in advance.
- 3. Do not apply shock to 2 mode Noise Filters (hereafter called the filters) or pinch them with a hard tool (e.g. pliers and tweezers). Otherwise, their bodies may be chipped, affecting their performance. Excessive mechanical stress may damage the filters. Handle with care.
- 4. Store the filters in a location with a temperature ranging from -5 °C to +40 °C and a relative humidity of 40 % to 60 %, where there are no rapid changes in temperature or humidity.
- 5. Use the filters within a year after the date of the outgoing inspection indicated on the packages.

# **Panasonic**

#### △ Safety Precautions (Common precautions for EMC Components and ESD Suppressor)

- When using our products, no matter what sort of equipment they might be used for, be sure to make a written agreement on the specifications with us in advance. The design and specifications in this catalog are subject to change without prior notice.
- Do not use the products beyond the specifications described in this catalog.
- This catalog explains the quality and performance of the products as individual components. Before use, check and evaluate their operations when installed in your products.
- Install the following systems for a failsafe design to ensure safety if these products are to be used in equipment where a defect in these products may cause the loss of human life or other significant damage, such as damage to vehicles (automobile, train, vessel), traffic lights, medical equipment, aerospace equipment, electric heating appliances, combustion/gas equipment, rotating equipment, and disaster/crime prevention equipment.
- \* Systems equipped with a protection circuit and a protection device
- \* Systems equipped with a redundant circuit or other system to prevent an unsafe status in the event of a single fault

#### (1) Precautions for use

- These products are designed and manufactured for general and standard use in general electronic equipment (e.g. AV equipment, home electric appliances, office equipment, information and communication equipment)
- These products are not intended for use in the following special conditions. Before using the products, carefully check the effects on their quality and performance, and determine whether or not they can be used.
  - 1. In liquid, such as water, oil, chemicals, or organic solvent
  - 2. In direct sunlight, outdoors, or in dust
  - 3. In salty air or air with a high concentration of corrosive gas, such as Cl2, H2S, NH3, SO2, or NO2
- 4. Electric Static Discharge (ESD) Environment (except ESD Suppressors)
  - These components are sensitive to static electricity and can be damaged under static shock (ESD).
  - Please take measures to avoid any of these environments.
  - Smaller components are more sensitive to ESD environment.
- 5. Electromagnetic Environment
  - Avoid any environment where strong electromagnetic waves exist.
- 6. In an environment where these products cause dew condensation
- 7. Sealing or coating of these products or a printed circuit board on which these products are mounted, with resin or other materials
- These products generate Joule heat when energized. Carefully position these products so that their heat will not affect the other components.
- Carefully position these products so that their temperatures will not exceed the category temperature range due to the effects of neighboring heat-generating components. Do not mount or place heat-generating components or inflammables, such as vinyl-coated wires, near these products.
- Note that non-cleaning solder, halogen-based highly active flux, or water-soluble flux may deteriorate the performance or reliability of the products.
- Carefully select a flux cleaning agent for use after soldering. An unsuitable agent may deteriorate the performance or reliability. In particular, when using water or a water-soluble cleaning agent, be careful not to leave water residues. Otherwise, the insulation performance may be deteriorated.

#### (2) Precautions for storage

The performance of these products, including the solderability, is guaranteed for a year from the date of arrival at your company, provided that they remain packed as they were when delivered and stored at a temperature of 5 °C to 35 °C and a relative humidity of 45 % to 85 %.

The performance of EMC Components is guaranteed for 6 months or a year after our delivery, provided that they are stored at a temperature of -5 °C to +40 °C and a relative humidity of 40 % to 60 %. Check the guarantee period in the specifications.

Even within the above guarantee periods, do not store these products in the following conditions. Otherwise, their electrical performance and/or solderability may be deteriorated, and the packaging materials (e.g. taping materials) may be deformed or deteriorated, resulting in mounting failures.

- 1. In salty air or in air with a high concentration of corrosive gas, such as Cl<sub>2</sub>, H<sub>2</sub>S, NH<sub>3</sub>, SO<sub>2</sub>, or NO<sub>2</sub>
- 2. In direct sunlight

#### <Package markings>

Package markings include the product number, quantity, and country of origin. In principle, the country of origin should be indicated in English.