


www.vishay.com

Vishay Semiconductors

Schottky Rectifier, 10 A






TO-220AC

PRODUCT SUMMARY					
Package	TO-220AC				
I _{F(AV)}	10 A				
V_{R}	35 V, 40 V, 45 V				
V _F at I _F	0.49 V				
I _{RM}	15 mA at 125 °C				
T _J max.	175 °C				
Diode variation	Single die				
E _{AS}	13 mJ				

FEATURES

- 175 °C T_J operation
- · Low forward voltage drop
- High frequency operation





FREE

- · Guard ring for enhanced ruggedness and long term reliability
- Compliant to RoHS Directive 2002/95/EC
- Designed and qualified according to JEDEC-JESD47
- Halogen-free according to IEC 61249-2-21 definition (-N3 only)

DESCRIPTION

The VS-10TQ... Schottky rectifier series has been optimized for low reverse leakage at high temperature. The proprietary barrier technology allows for reliable operation up to 175 °C junction temperature. Typical applications are in switching power supplies, converters, freewheeling diodes, and reverse battery protection.

MAJOR RATINGS AND CHARACTERISTICS								
SYMBOL CHARACTERISTICS VALUES UNITS								
I _{F(AV)}	Rectangular waveform	10	A					
V _{RRM}		35/45	V					
I _{FSM}	t _p = 5 μs sine	1050	А					
V _F	10 A _{pk} , T _J = 125 °C	0.49	V					
T _J	Range	- 55 to 175	°C					

VOLTAGE RATINGS									
PARAMETER	SYMBOL	VS- 10TQ035PbF	VS- 10TQ035-N3	VS- 10TQ040PbF	VS- 10TQ040-N3	VS- 10TQ045PbF	VS- 10TQ045-N3	UNITS	
Maximum DC reverse voltage	V_{R}								
Maximum working peak reverse voltage	V_{RWM}	35	35	40	40	45	45	V	

ABSOLUTE MAXIMUM RATINGS								
PARAMETER	SYMBOL	TEST COND	ITIONS	VALUES	UNITS			
Maximum average forward current See fig. 5	I _{F(AV)}	50 % duty cycle at T _C = 151 °C	10					
Maximum peak one cycle non-repetitive surge current	l=a	5 μs sine or 3 μs rect. pulse Following any rated load condition and with rated		1050	Α			
See fig. 7	IFSM	10 ms sine or 6 ms rect. pulse	V _{RRM} applied	280				
Non-repetitive avalanche energy	E _{AS}	$T_J = 25 ^{\circ}\text{C}, I_{AS} = 2 \text{A}, L = 6.5 \text{m}$	13	mJ				
Repetitive avalanche current	I _{AR}		Current decaying linearly to zero in 1 μ s Frequency limited by T _J maximum V _A = 1.5 x V _R typical					



VS-10TQ...PbF Series, VS-10TQ...-N3 Series

Vishay Semiconductors

ELECTRICAL SPECIFICATIONS						
PARAMETER	SYMBOL	TEST CO	NDITIONS	VALUES	UNITS	
		10 A	T 05.00	0.57	V	
Maximum forward voltage drop See fig. 1	V (1)	20 A	T _J = 25 °C	0.67		
	V _{FM} ⁽¹⁾	10 A	T 105 %C	0.49		
		20 A	T _J = 125 °C	0.61		
Maximum reverse leakage current	ı (1)	T _J = 25 °C	V _R = Rated V _R	2	A	
See fig. 2	I _{RM} ⁽¹⁾	T _J = 125 °C	V _R = nateu V _R	15	mA mA	
Maximum junction capacitance	C _T	V _R = 5 V _{DC} (test signal ran	900	pF		
Typical series inductance	L _S	Measured lead to lead 5 r	8.0	nH		
Maximum voltage rate of change	dV/dt	Rated V _R		10 000	V/µs	

Note

 $^{^{(1)}~}$ Pulse width < 300 $\mu s,~duty~cycle < 2~\%$

THERMAL - MECHANICAL SPECIFICATIONS						
PARAMETER		SYMBOL TEST CONDITIONS		VALUES	UNITS	
Maximum junction and storage temperature range		T _J , T _{Stg}		- 55 to 175	°C	
Maximum thermal resistance, junction to case Typical thermal resistance, case to heatsink		R _{thJC}	DC operation See fig. 4	2.0	°C/W	
		R _{thCS}	Mounting surface, smooth and greased	0.50	C/VV	
Approximate weight				2	g	
Approximate weight				0.07	OZ.	
Mounting torque	minimum			6 (5)	kgf · cm	
Mounting torque	maximum			12 (10)	(lbf · in)	
Marking device			Coop at the TO 220AC	10TC	2035	
			Case style TO-220AC	10TC	10TQ045	

Vishay Semiconductors




Fig. 1 - Maximum Forward Voltage Drop Characteristics




Fig. 2 - Typical Values of Reverse Current vs. Reverse Voltage




Fig. 3 - Typical Junction Capacitance vs. Reverse Voltage




Fig. 4 - Maximum Thermal Impedance Z_{thJC} Characteristics

Vishay Semiconductors




Fig. 5 - Maximum Allowable Case Temperature vs. Average Forward Current




Fig. 6 - Forward Power Loss Characteristics




Fig. 7 - Maximum Non-Repetitive Surge Current





Fig. 8 - Unclamped Inductive Test Circuit

VS-10TQ...PbF Series, VS-10TQ...-N3 Series

Vishay Semiconductors

ORDERING INFORMATION TABLE

Device code



1 - Vishay Semiconductors product

2 - Current rating (10 = 10 A)

3 - Package:

T = TO-220

4 - Schottky "Q" series

035 = 35 V

5 - Voltage ratings

040 = 40 V045 = 45 V

6 - Environmental digit

• PbF = Lead (Pb)-free and RoHS compliant

• -N3 = Halogen-free, RoHS compliant, and totally lead (Pb)-free

ORDERING INFORMATION (Example)								
PREFERRED P/N	QUANTITY PER T/R	MINIMUM ORDER QUANTITY	PACKAGING DESCRIPTION					
VS-10TQ035PbF	50	1000	Antistatic plastic tube					
VS-10TQ035-N3	50	1000	Antistatic plastic tube					
VS-10TQ040PbF	50	1000	Antistatic plastic tube					
VS-10TQ040-N3	50	1000	Antistatic plastic tube					
VS-10TQ045PbF	50	1000	Antistatic plastic tube					
VS-10TQ045-N3	50	1000	Antistatic plastic tube					


LINKS TO RELATED DOCUMENTS					
Dimensions <u>www.vishay.com/doc?95221</u>					
Part marking information	TO-220ACPbF	www.vishay.com/doc?95224			
Fait marking information	TO-220AC-N3	www.vishay.com/doc?95068			



Vishay Semiconductors

TO-220AC

DIMENSIONS in millimeters and inches



SYMBOL	MILLIM	IETERS	INCHES		NOTES
STIVIBUL	MIN.	MAX.	MIN.	MAX.	NOTES
Α	4.25	4.65	0.167	0.183	
A1	1.14	1.40	0.045	0.055	
A2	2.56	2.92	0.101	0.115	
b	0.69	1.01	0.027	0.040	
b1	0.38	0.97	0.015	0.038	4
b2	1.20	1.73	0.047	0.068	
b3	1.14	1.73	0.045	0.068	4
С	0.36	0.61	0.014	0.024	
c1	0.36	0.56	0.014	0.022	4
D	14.85	15.25	0.585	0.600	3
D1	8.38	9.02	0.330	0.355	
D2	11.68	12.88	0.460	0.507	6
Е	10.11	10.51	0.398	0.414	3, 6

SYMBOL	MILLIMETERS INCHES		HES	NOTES	
STINIBUL	MIN.	MAX.	MIN.	MAX.	NOTES
E1	6.86	8.89	0.270	0.350	6
E2	-	0.76	-	0.030	7
е	2.41	2.67	0.095	0.105	
e1	4.88	5.28	0.192	0.208	
H1	6.09	6.48	0.240	0.255	6, 7
L	13.52	14.02	0.532	0.552	
L1	3.32	3.82	0.131	0.150	2
L3	1.78	2.13	0.070	0.084	
L4	0.76	1.27	0.030	0.050	2
ØΡ	3.54	3.73	0.139	0.147	
Q	2.60	3.00	0.102	0.118	
θ	90° to 93°		90° t	o 93°	

Notes

- (1) Dimensioning and tolerancing as per ASME Y14.5M-1994
- (2) Lead dimension and finish uncontrolled in L1
- (3) Dimension D, D1 and E do not include mold flash. Mold flash shall not exceed 0.127 mm (0.005") per side. These dimensions are measured at the outermost extremes of the plastic body
- (4) Dimension b1, b3 and c1 apply to base metal only
- (5) Controlling dimension: inches
- (6) Thermal pad contour optional within dimensions E, H1, D2 and E1
- (7) Dimension E2 x H1 define a zone where stamping and singulation irregularities are allowed
- (8) Outline conforms to JEDEC TO-220, D2 (minimum) where dimensions are derived from the actual package outline



Legal Disclaimer Notice

Vishay

Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and / or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Except as expressly indicated in writing, Vishay products are not designed for use in medical, life-saving, or life-sustaining applications or for any other application in which the failure of the Vishay product could result in personal injury or death. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.

Revision: 13-Jun-16 1 Document Number: 91000