

Zack marker strip - ZB 5,LGS:FORTL.ZAHLEN - 1050017

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Zack marker strip, Strip, white, labeled, Printed horizontally: Consecutive numbers 1 - 10, 11 - 20, etc. up to 491 - 500, Mounting type: Snap into tall marker groove, for terminal block width: 5.2 mm, Lettering field: 5.15 x 10.5 mm

The illustration shows a combination of versions, ZB 5 UNPRINTED, ZB 5 SO/CMS, as well as ZB 5 LGS- ZB 7,5 LGS CONSEC.NOS

Why buy this product

- Other pitches available on request
- The multi-section marking strips are easy to fit and can be easily separated if required
- Labeling service: Phoenix Contact can custom-label all zack marker strip markers according to your requirements
- The ZB zack marker strip system is a marking solution for modular terminal blocks and electronics modules with tall marker grooves
- Unlabeled marking strips can be custom-labeled with a plotter or by hand

Key Commercial Data

| | |
|--------------------------------------|----------|
| Packing unit | 10 STK |
| Minimum order quantity | 10 STK |
| Weight per Piece (excluding packing) | 1.300 g |
| Custom tariff number | 49119900 |
| Country of origin | Germany |

Technical data

Dimensions

| | |
|-----------|------|
| Width (a) | 5 mm |
|-----------|------|

Ambient conditions

| | |
|---------------------------------|-------------------|
| Ambient temperature (operation) | -40 °C ... 100 °C |
|---------------------------------|-------------------|

General

| | |
|-------|---|
| Note | For labeling according to customer requirement, please select 0824962 product |
| Color | white |

Zack marker strip - ZB 5,LGS:FORTL.ZAHLEN - 1050017

Technical data

General

| | |
|--|---|
| Components | free from silicone and halogen |
| Flammability rating according to UL 94 | V2 |
| Material | PA |
| Wipe resistance | DIN EN 61010-1 (VDE 0411-1) |
| | DIN VDE 0611 |
| Printing direction | Printed horizontally |
| Printing | Consecutive numbers 1 - 10, 11 - 20, etc. up to 491 - 500 |
| Number of individual labels | 10 |
| Number of individual labels per row | 10 |
| Number of marker strips | 10 |
| Marking mounting type | Snap into tall marker groove |

Standards and Regulations

| | |
|--|-----------------------------|
| Wipe resistance | DIN EN 61010-1 (VDE 0411-1) |
| | DIN VDE 0611 |
| Flammability rating according to UL 94 | V2 |