


# Optocoupler, Phototransistor Output, AC Input, 5300 V<sub>RMS</sub>



#### **DESCRIPTION**

The SFH620AA, SFH620AGB features a high current transfer ratio, low coupling capacitance and high isolation voltage. These couplers have a GaAs infrared emitting diode emitter, which is optically coupled to a silicon planar phototransistor detector, and is incorporated in a plastic DIP-4 package.


The coupling devices are designed for signal transmission between two electrically separated circuits.

The couplers are end-stackable with 2.54 mm lead spacing. This version complies with IEC 60950 (DIN VDE 0805) for reinforced insulation up to an operation voltage of 400  $\rm V_{RMS}$  or DC.

#### **FEATURES**

- High current transfer ratios
  - at 5 mA: 50 to 600 %
  - at 1.0 mA: 45 % typical (> 13)
- Low CTR degradation
- Good CTR linearity depending on forward current






- High collector emitter voltage, V<sub>CEO</sub> = 70 V
- Low saturation voltage
- · Fast switching times
- Temperature stable
- Low coupling capacitance
- End stackable, 0.100" (2.54 mm) spacing
- High common mode interference immunity (unconnected base)
- SMD option, see SFH620A, SFH6206 datasheet
- Material categorization: for definitions of compliance please see <a href="https://www.vishay.com/doc?99912"><u>www.vishay.com/doc?99912</u></a>

#### **AGENCY APPROVALS**

- UL1577, file no. E52744 system code H, double protection
- CSA 93751
- BSI IEC 60950; IEC 60065
- VDE 0884-5, DIN EN 60747-5-5, available with option 1



ABSOLUTE MAXIMUM RATINGS (T <sub>amb</sub> = 25 °C, unless otherwise specified)								
PARAMETER	TEST CONDITION	SYMBOL	VALUE	UNIT				
INPUT								
DC forward current		I <sub>F</sub>	± 60	mA				
Surge forward current	$t_p \le 1.0 \ \mu s$	I <sub>FSM</sub>	± 2.5	Α				
Total power dissipation		P <sub>diss</sub>	100	mW				
OUTPUT								
Collector emitter voltage		V <sub>CE</sub>	70	V				
Emitter collector voltage		V <sub>EC</sub>	7	V				
Collector current		I <sub>C</sub>	50	mA				
	$t_p \le 1.0 \text{ ms}$	I <sub>C</sub>	100	mA				
Power dissipation	_	P <sub>diss</sub>	150	mW				

Rev. 1.8, 19-Nov-14 **1** Document Number: 83676



<b>ABSOLUTE MAXIMUM RATINGS</b> (T <sub>amb</sub> = 25 °C, unless otherwise specified)						
PARAMETER	TEST CONDITION	SYMBOL	VALUE	UNIT		
COUPLER						
Isolation test voltage between emitter and detector		V <sub>ISO</sub>	5300	V <sub>RMS</sub>		
Creepage distance			≥ 7	mm		
Clearance distance			≥ 7	mm		
Insulation thickness between emitter and detector			≥ 0.4	mm		
Comparative tracking index per DIN IEC 112/VDE 0303 part 1		СТІ	≥ 175			
Isolation resistance	$V_{IO} = 500 \text{ V}, T_{amb} = 25 ^{\circ}\text{C}$	R <sub>IO</sub>	≥ 10 <sup>12</sup>	Ω		
Isolation resistance	V <sub>IO</sub> = 500 V, T <sub>amb</sub> = 100 °C	R <sub>IO</sub>	≥ 10 <sup>11</sup>	Ω		
Storage temperature		T <sub>stg</sub>	-55 to +150	°C		
Ambient temperature		T <sub>amb</sub>	-55 to +100	°C		
Junction temperature		Tj	100	°C		
Soldering temperature (1)	max. 10 s, dip soldering distance to seating plane ≥ 1.5 mm	T <sub>sld</sub>	260	°C		

#### **Notes**

- Stresses in excess of the absolute maximum ratings can cause permanent damage to the device. Functional operation of the device is not
  implied at these or any other conditions in excess of those given in the operational sections of this document. Exposure to absolute
  maximum ratings for extended periods of the time can adversely affect reliability.
- (1) Refer to reflow profile for soldering conditions for surface mounted devices (SMD). Refer to wave profile for soldering conditions for through hole devices (DIP).

<b>ELECTRICAL CHARACTERISTICS</b> (T <sub>amb</sub> = 25 °C, unless otherwise specified)							
PARAMETER	TEST CONDITION	PART	SYMBOL	MIN.	TYP.	MAX.	UNIT
INPUT							
Forward voltage	$I_F = \pm 60 \text{ mA}$		$V_{F}$		1.25	1.65	V
Capacitance	V <sub>R</sub> = 0 V, f = 1 MHz		Co		50		pF
Thermal resistance			R <sub>thja</sub>		750		K/W
OUTPUT							
Collector emitter capacitance	V <sub>CE</sub> = 5 V, f = 1 MHz		C <sub>CE</sub>		6.8		pF
Thermal resistance			R <sub>thja</sub>		500		K/W
COUPLER							
Collector emitter saturation voltage	$I_F = \pm 10 \text{ mA}, I_C = 2.5 \text{ mA}$		V <sub>CEsat</sub>		0.25	0.4	V
Coupling capacitance			C <sub>C</sub>		0.2		pF
Callantar are the relation of a comment	V 10.V	SFH620AA	I <sub>CEO</sub>		10	100	nA
Collector emitter leakage current	V <sub>CE</sub> = 10 V	SFH620AGB	I <sub>CEO</sub>		10	100	nA

#### Note

• Minimum and maximum values are testing requirements. Typical values are characteristics of the device and are the result of engineering evaluation. Typical values are for information only and are not part of the testing requirements.

CURRENT TRANSFER RATIO (T <sub>amb</sub> = 25 °C, unless otherwise specified)							
PARAMETER TEST CONDITION PART SYMBOL MIN. TYP. MAX. UNI							UNIT
1.71	1 - + 5 m \ \ \ - 5 \ \	SFH620AA	CTR	50		600	%
I <sub>C</sub> /I <sub>F</sub>	$I_F = \pm 5 \text{ mA}, V_{CE} = 5 \text{ V}$	SFH620AGB	CIN	100		600	%




Fig. 1 - Switching Times (Typical Values) Linear Operation (Saturated)

<b>SWITCHING CHARACTERISTICS</b> (T <sub>amb</sub> = 25 °C, unless otherwise specified)						
PARAMETER	TEST CONDITION	SYMBOL	MIN.	TYP.	MAX.	UNIT
Turn-on time	$I_F=\pm~5~mA,~R_L=1.9~k\Omega,~V_{CC}=5~V$	t <sub>on</sub>		2		μs
Turn-off time	$I_F = \pm 5 \text{ mA}, R_L = 1.9 \text{ k}\Omega, V_{CC} = 5 \text{ V}$	t <sub>off</sub>		25		μs

SAFETY AND INSULATION RATINGS							
PARAMETER	TEST CONDITION	SYMBOL	MIN.	TYP.	MAX.	UNIT	
Climatic classification (according to IEC 68 part 1)				55/100/21			
Comparative tracking index		CTI	175		399		
V <sub>IOTM</sub>			10000			V	
V <sub>IORM</sub>			890			V	
P <sub>SO</sub>					400	mW	
I <sub>SI</sub>					275	mA	
T <sub>SI</sub>					175	°C	
Creepage distance	standard DIP-4		7			mm	
Clearance distance	standard DIP-4		7			mm	
Insulation thickness, reinforced rated	per IEC 60950 2.10.5.1		0.4			mm	

#### Note

 As per IEC 60747-5-5, this optocoupler is suitable for "safe electrical insulation" only within the safety ratings. Compliance with the safety ratings shall be ensured by means of protective circuits.

## TYPICAL CHARACTERISTICS (T<sub>amb</sub> = 25 °C, unless otherwise specified)




Fig. 2 - Current Transfer Ratio (CTR) vs. Temperature




Fig. 3 - Output Characteristics (Typ.) Collector Current vs. Collector Emitter Voltage






Fig. 4 - Diode Forward Voltage (Typ.) vs. Forward Current




Fig. 5 - Transistor Capacitance (Typ.) vs. Collector Emitter Voltage




Fig. 6 - Permissible Pulse Handling Capability Forward Current vs. Pulse Width




Fig. 7 - Permissible Power Dissipation vs. Ambient Temperature






Fig. 8 - Permissible Diode Forward Current vs.
Ambient Temperature

### **PACKAGE DIMENSIONS** in millimeters



## PACKAGE MARKING (example of SFH620AGB-X001)



### Note

• The VDE logo is only marked on option1 parts.



## **Legal Disclaimer Notice**

Vishay

## **Disclaimer**

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and / or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Except as expressly indicated in writing, Vishay products are not designed for use in medical, life-saving, or life-sustaining applications or for any other application in which the failure of the Vishay product could result in personal injury or death. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.

Revision: 13-Jun-16 1 Document Number: 91000