


2183Y (Har. code H03VV-F3)

Three-Core Round 300/300V

pro-POWER



Application:

Power supply wire, suitable for indoor small electrical instrument, or general in portable tool

Construction:

Conductor:

Material : Stranded plain annealed copper wire

Insulation:

Material : PVC

Colours : Blue, brown and yellow / green stripe

Sheath:

Material : PVC

Colour : Any

Physical Properties:

Operating temperature : -15°C to +70°C

Electrical Properties:

Voltage Test : Core to core : 1,500 V AC/1 min

Voltage Rating : 300/300V

Specification Table

Part Number	Conductor Stranding (mm (mm ²))	Insulation Nominal Inner Diameter (mm)	Sheath Nominal Outer Diameter (mm)	Min. Bend Radius (mm)	Nominal DC Resistance (Ω/km)	Current Rating (A)
2183Y-0.50MMWHT50M	16/0.2 (0.5)	2	5.6	56	39	3
2183Y-0.50MMWHT100M						
2183Y-0.50MMBLK50M						
2183Y-0.50MMBLK100M						
2183Y-0.50MMGRY100M						
2183Y-0.75MMWHT50M	24/0.2 (0.75)	2.2	6.1	61	26	6
2183Y-0.75MMWHT100M						
2183Y-0.75MMBLK50M						
2183Y-0.75MMBLK100M						
2183Y-0.75MMGRY100M						


Dimensions: Millimetres

www.element14.com
www.farnell.com
www.newark.com
www.cpc.co.uk

pro-POWER

2183Y (Har. code H03VV-F3) Three-Core Round 300/300V

pro-POWER



Part Number Table

Description	Reel Length	Part Number
Cable, Flex, White, 0.5mm ²	50m	2183Y-0.50MMWHT50M
Cable, Flex, White, 0.5mm ²	100m	2183Y-0.50MMWHT100M
Cable, Flex, Black, 0.5mm ²	50m	2183Y-0.50MMBLK50M
Cable, Flex, Black, 0.5mm ²	100m	2183Y-0.50MMBLK100M
Cable, Flex, Grey, 0.5mm ²	100m	2183Y-0.50MMGRY100M
Cable, Flex, White, 0.75mm ²	50m	2183Y-0.75MMWHT50M
Cable, Flex, White, 0.75mm ²	100m	2183Y-0.75MMWHT100M
Cable, Flex, Black, 0.75mm ²	50m	2183Y-0.75MMBLK50M
Cable, Flex, Black, 0.75mm ²	100m	2183Y-0.75MMBLK100M
Cable, Flex, Grey, 0.75mm ²	100m	2183Y-0.75MMGRY100M

Important Notice : This data sheet and its contents (the "Information") belong to the members of the Premier Farnell group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. pro-POWER is the registered trademark of the Group. © Premier Farnell Limited 2016.

www.element14.com
www.farnell.com
www.newark.com
www.cpc.co.uk

pro-POWER