Panasonic

NEW

Amplifier Built-in

Ultra-minute Photoelectric Sensor

EX-ZSERIES








EX-Z SERIES

Ultra-minute Photoelectric Sensor Amplifier Built-in


The World's Smallest* Size



Small-object sensing capability

Capable of sensing an extremely small ø0.3 mm n object without slit EX-Z11

A slit is provided on the front side of the main sensor body. The sensor can detect a Ø0.3 mm Ø0.012 in object (the smallest-object sensing capability in the industry*) without using an optional slit. * Among photoelectric sensors with built-in amplifier, as of June 2015 (survey by our company)



Capability to sense a small ø1.0 mm ø0.039 in object over long distance EX-Z130

Ø0.3 mm Ø0.012 in opaque object

The high-brightness 4-element red LED provides strong light emission stably over a long period of time. In spite of the extremely small size, both front sensing and side sensing units can sense a small ø1.0 mm ø0.039 in object from a long distance of 500 mm 19.685 in. Since the spotlight is clearly visible, the sensing position can be easily confirmed.



A wide range of applications

Inflection resistant cable type available for all models

Inflection resistant cable type with improved flex resistance is available for all models. Select the model suitable for your specific application. The standard type comes with lead wires with the same diameter as previous models, but the outside diameter of the cable is 2.0 mm 0.079 in and thinner than the cables of the **EX-10** series. This facilitates cable routing.



IP67 protective structure

The sensors features an IP67 protective structure to allow their use in process lines where water is used or splashed.

Rust-resistant stainless steel sensor mounting brackets and screws are available.

Note: If water splashes on the sensor during sensing operation, it may sense water as an object.







Options

A variety of mounting brackets are available!


A spacer for mounting at the back (1 type) for through-wall sensing and sensor mounting brackets (3 types) are available to meet a diversity of sensor installation needs.



Examples of applications



Detection of parts in parts feeder



Detection of LED lead

ORDER GUIDE

Tymo		A	0 :	Model No. (Note)		Output
	Туре	Appearance	Sensing range	NPN output	PNP output	operation
			50 mm 1.969 in	EX-Z11FA	EX-Z11FA-P	Light-ON
				EX-Z11FB	EX-Z11FB-P	Dark-ON
			200 mm 7.874 in	EX-Z12FA	EX-Z12FA-P	Light-ON
				EX-Z12FB	EX-Z12FB-P	Dark-ON
	б		500 mm 19.685 in	EX-Z13FA	EX-Z13FA-P	Light-ON
	ensir			EX-Z13FB	EX-Z13FB-P	Dark-ON
	Front sensing cable		50 mm 1.969 in	EX-Z11FA-R	EX-Z11FA-P-R	Light-ON
	Fre Fre			EX-Z11FB-R	EX-Z11FB-P-R	Dark-ON
	Front Inflection resistant cable			EX-Z12FA-R	EX-Z12FA-P-R	Light-ON
	n res		200 mm 7.874 in	EX-Z12FB-R	EX-Z12FB-P-R	Dark-ON
_	ectio		500 mm 19.685 in	EX-Z13FA-R	EX-Z13FA-P-R	Light-ON
Thru-beam	Infle			EX-Z13FB-R	EX-Z13FB-P-R	Dark-ON
				EX-Z11A	EX-Z11A-P	Light-ON
			50 mm 1.969 in	EX-Z11B	EX-Z11B-P	Dark-ON
			200 mm 7.874 in	EX-Z12A	EX-Z12A-P	Light-ON
			200 11111 7.874 111	EX-Z12B	EX-Z12B-P	Dark-ON
			F00 40 005 :	EX-Z13A	EX-Z13A-P	Light-ON
	ensin		500 mm 19.685 in	EX-Z13B	EX-Z13B-P	Dark-ON
	Side sensing			EX-Z11A-R	EX-Z11A-P-R	Light-ON
	Si si t cal		50 mm 1.969 in	EX-Z11B-R	EX-Z11B-P-R	Dark-ON
	istar		200 - 7074	EX-Z12A-R	EX-Z12A-P-R	Light-ON
	u res		200 mm 7.874 in	EX-Z12B-R	EX-Z12B-P-R	Dark-ON
	ection		500 mm 19.685 in	EX-Z13A-R	EX-Z13A-P-R	Light-ON
	l light			EX-Z13B-R	EX-Z13B-P-R	Dark-ON

Note: Mounting bracket is not supplied with the sensor. Please select from the range of optional sensor mounting brackets (MS-EXZ-□).

Note: The model No. with "E" shown on the label affixed to the thru-beam type sensor is the emitter, "D" shown on the label is the receiver.


OPTIONS

Designation	Model No.	Description
	MS-EXZ-1	L-shaped mounting bracket (SUS304) for front sensing and side sensing types (2 sets are required)
Sensor mounting bracket	MS-EXZ-2	Mounting bracket (SUS304) for front sensing type (2 sets are required)
	MS-EXZ-3	Mounting bracket (SUS304) for side sensing type (2 sets are required)
Spacer for mounting at the back	MS-EXZ-4	Spacer for mounting at the back (polyacetal) for front sensing type

(SUS304)


Sensor mounting bracket

• MS-EXZ-1




Material: Stainless steel (SUS304)

Two M2 (length 4 mm 0.157 in) pan head screws and two M2 (length 8 mm 0.315 in) pan head screws are attached. • MS-EXZ-2



• MS-EXZ-3



Material: Stainless steel (SUS304) Two M2 (length 8 mm 0.315 in) pan head screws are attached.

Spacer for mounting at the back

• MS-EXZ-4



Material: Polyacetal M2 (length: 10 mm 0.394 in) screws, nuts, spring washers and flat washers are attached. (20 pieces each)

SPECIFICATIONS

		Туре	Thru-beam						
			Front sensing	Side sensing	Front sensing	Side sensing	Front sensing	Side sensing	
	Model No.	Light-ON	EX-Z11FA(-P)(-R)	EX-Z11A(-P)(-R)	EX-Z12FA(-P)(-R)	EX-Z12A(-P)(-R)	EX-Z13FA(-P)(-R)	EX-Z13A(-P)(-R)	
Item	(Note 2)	Dark-ON	EX-Z11FB(-P)(-R)	EX-Z11B(-P)(-R)	EX-Z12FB(-P)(-R)	EX-Z12B(-P)(-R)	EX-Z13FB(-P)(-R)	EX-Z13B(-P)(-R)	
Sens	Sensing distance		50 mm 1.969 in		200 mm 7.874 in		500 mm 19.685 in		
Mini	Minimum sensing object		(Completely beam Setting distance	ø0.3 mm ø0.012 in opaque object (Completely beam interrupted object) (Setting distance between emitter and receiver: 50 mm 1.969 in		ø0.5 mm ø0.02 in opaque object (Completely beam interrupted object) (Setting distance between emitter and receiver: 200 mm 7.874 in		ø1.0 mm ø0.039 in opaque object (Completely beam interrupted object) (Setting distance between emitter and receiver: 500 mm 19.685 in)	
Hyst	eresis								
	Repeatability (Perpendicular to sensing axis)		0.02 mm 0.0	01 in or less	0.03 mm 0.0	0.001 in or less 0.05 mm 0.002 in or less		02 in or less	
Supp	Supply voltage		12 to 24 V DC ±10 % Ripple P-P 10 % or less						
Curr	ent consum	ption	Emitter: 10 mA or less, Receiver: 10 mA or less						
Outp	Output		<npn output="" type=""> NPN open-collector transistor Maximum sink current: 20 mA Applied voltage: 30 V DC or less (between output and 0 V) Residual voltage: 1.5 V or less (at 20 mA sink current) <pnp output="" type=""> PNP open-collector transistor Maximum source current: 20 mA Applied voltage: 30 V DC or less (between output and +\ Residual voltage: 1.5 V or less (at 20 mA source current) </pnp></npn>						
Short-circuit protection			Incorporated						
Res	Response time		0.5 ms or less						
Ope	ration indica	itor	Orange LED (Lights up when the sensing output is ON)						
Stab	Stability indicator		Green LED (Lights up under the stable light received condition or the stable dark condition)						
	Protection		IP67 (IEC)						
nce	Ambient te	mperature	-10 to +55 °C 14 to +131 °F (No dew condensation or icing allowed), Storage: -30 to +70 °C -22 to +158 °F						
Environment resistance	Ambient h	umidity	35 to 85 % RH, Storage: 35 to 85 % RH						
ıt re	Ambient ill	uminance	Incandescent light: 5,000 tx at the light-receiving face						
ıme	Voltage wi	thstandability	1,000 V AC for one min. between all supply terminals connected together and enclosure						
viror	Insulation	resistance	20 MΩ or more, with 250 V DC megger between all supply terminals connected together and enclosu				nclosure		
п	Vibration re	esistance	10 to 500 Hz frequency, 3 mm 0.118 in amplitude in X, Y and Z directions for two hours each				ach		
	Shock resi	stance		500 m/s ² accelerat	n (50 G approx.) in X, Y and Z directions for three times each				
Ligh	t emitting el	ement	Red LED (Peak emission wavelength: 650 nm 0.026 mil, modulated)						
Grou	Grounding		Floating						
Mate	Material		Enclosure: PBT, Lens: Polycarbonate, Metallic part: Stainless steel (SUS304) (SUS301 for rear side of front sensing type)						
Cabl	Cable (Note 3)		0.1 mm ² 3-core (emitter: 2-core) cabtyre cable, 2 m 6.562 ft long						
Cabl	Cable extension		Extension up to total 50 m 164 ft is possible with 0.3 mm², or more, cable (both emitter and receiver).						
Weight		Net weight (each emitter and receiver): 15 g approx., Gross weight: 35 g approx.							
Acce	essories		M2 mounting screws: 1 set (front sensing type: 6 mm 0.236 in in length; side sensing type: 10 mm 0.394 in in length)						

Notes: 1) Where measurement conditions have not been specified precisely, the conditions used were an ambient temperature of +23°C 73°F.

- 2) Model Nos. having the "-P" are PNP output type and model Nos. having the "-R" are inflection resistant cable type.
- 3) The inflection resistant cable type has a 0.1 mm² 3-core (thru-beam type emitter: 2-core) flexible cabtyre cable, 2 m 6.562 ft long.


PRECAUTIONS FOR PROPER USE



- Never use this product as a sensing device for personnel protection.
- In case of using sensing devices for personnel protection, use products which meet laws and standards, such as OSHA, ANSI or IEC etc., for personnel protection applicable in each region or country.


Mounting

• In case of mounting on tapped holes (Unit: mm in)



The tightening torque should be 0.2 N·m or less.

• In case of using attached screws and nuts (Unit: mm in)



The tightening torque should be 0.2 N·m or less.


Other

• Do not use during the initial transient time (0.5 sec. approx.) after the power supply is switched on.

I/O CIRCUIT DIAGRAMS

NPN output type

I/O circuit diagram



Note: The emitter does not incorporate the output.


Symbols ... D1: Reverse supply polarity protection diode D2: Reverse output polarity protection diode ZD: Surge absorption zener diode Tr: NPN output transistor

> 10 0.394

Left ← Center ← Right Operating position ℓ (mm in)

PNP output type

I/O circuit diagram





Note: The emitter does not incorporate the output.


Symbols ... D1: Reverse supply polarity protection diode D2: Reverse output polarity protection diode ZD: Surge absorption zener diode Tr: PNP output transistor

SENSING CHARACTERISTICS (TYPICAL)









Setting distance L (mm in) →

60

40 1575

> 0 20 0.787

20 Emitter


10 0.394

DIMENSIONS (Unit: mm in)


The CAD data can be downloaded from the website.

EX-Z11F EX-Z12F EX-Z13F

Sensor



Sensor




MS-EXZ-1

Sensor mounting bracket (Optional)


MS-EXZ-2

Sensor mounting bracket (Optional)



Material: Stainless steel (SUS304)

Two M2 (length 4 mm $0.157~{\rm in}$) pan head screws and two M2 (length 8 mm $0.315~{\rm in}$) pan head screws are attached.



Material: Stainless steel (SUS304)

Two M2 (length 4 mm 0.157 in) pan head screws are attached.

DIMENSIONS (Unit: mm in)


The CAD data can be downloaded from the website.

MS-EXZ-3

Sensor mounting bracket (Optional)


MS-EXZ-4

Spacer for mounting at the back (Optional)



Material: Stainless steel (SUS304)

Two M2 (length 8 mm 0.315 in) pan head screws are attached.



Material: Polyacetal
Set of 10 pieces
M2 (length: 10 mm 0.394 in) screws, nuts, spring washers
and flat washers are attached. (20 pieces each)

EX Family Products



Ultra-thin dimension

- Only 3.5 mm 0.138 in thick
- Long sensing range of 1 m 3.281 ft
- · High speed response of 0.5 ms

Ultra-compact Photoelectric Sensor Amplifier Built-in EX-20 SERIES Ver.2

Easy installation with M3 screws

- Equipped with sensitivity adjuster
- \bullet Long sensing range of 2 m 6.562 ft
- Red spotlight for easy confirmation of sensing point



One-point mounting

- Simple design with sensing axis corresponding with mounting hole
- Can be installed using the same thread size (M4 for thru-beam type, M6 for reflective type) as that of standard fiber

Disclaimer

The applications described in the catalog are all intended for examples only. The purchase of our products described in the catalog shall not be regarded as granting of a license to use our products in the described applications. We do NOT warrant that we have obtained some intellectual properties, such as patent rights, with respect to such applications, or that the described applications may not infringe any intellectual property rights, such as patent rights, of a third party.

Please contact:

Panasonic Industrial Devices SUNX Co., Ltd.

2431-1 Ushiyama-cho, Kasugai-shi, Aichi, 486-0901, Japan Global Sales Department

■Telephone: +81-568-33-7861 ■Facsimile: +81-568-33-8591 panasonic.net/id/pidsx/global



All Rights Reserved © Panasonic Industrial Devices SUNX Co., Ltd. 2015